

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**PROPOWER ANTI STATIC SPRAY**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Against electro-static charge

### 1.3. Details of the supplier of the safety data sheet

PROPOWER Premier Farnell plc  
150 Armley Road  
LEEDS LS12 2QQ  
Tel. : +44 (0) 870 129 8608  
Fax

### 1.4. Emergency telephone number

+44 (0) 870 202530

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to 67/548/EEC or 1999/45/EC:

<b>Health:</b>	R36: Irritating to eyes. R67: Vapours may cause drowsiness and dizziness.
<b>Physical:</b>	R12: Extremely flammable. EXTREMELY FLAMMABLE
<b>Environment:</b>	not classified

### 2.2. Label elements

**Warning symbol(s) :** EXTREMELY FLAMMABLE



Xi : IRRITANT

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431



<b>Risk-phrase(s) :</b>	R12: Extremely flammable. R36: Irritating to eyes. R67: Vapours may cause drowsiness and dizziness.
<b>Safety-phrase(s) :</b>	S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S23: Do not breathe vapours/spray. S25: Avoid contact with eyes. S26: In case of contact with eyes, rinse immediately with plenty of water and seek medical advice. S51: Use only in well-ventilated areas.
<b>Extra label elements according to Aerosol Dispenser Directive 75/324/EC:</b>	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.

### 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	30-60	F,Xi	11-36-67	B
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	30-60	F+	12	K
<b>Explanation notes</b>						
B : substance with national established workplace exposure limit						
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol		67-63-0	200-661-7	30-60	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225.H319.H336	B
<b>Explanation notes</b>							
B : substance with national established workplace exposure limit							
(* Explanation phrases : see chapter 16)							

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Contact with eyes :** If substance has got into eyes, immediately wash out with water for at least 15

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

	minutes Seek medical advice
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
<b>Inhalation :</b>	Remove patient to fresh air Keep warm and at rest, in a half upright position. Loosen clothing Seek medical attention if ill effects occur
<b>Ingestion :</b>	Ingestion is unlikely to occur If swallowed accidentally, do not induce vomiting and seek medical advice.

#### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

#### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

#### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

**Productname :** PROPOWER ANTI STATIC SPRAY      **Creationdate :** 29.09.11 Version : 1.0  
**Ref.Nr.:** UDS000221\_3\_20110929      **Replaces:** UK10431

## 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

## 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

## 6.4. Reference to other sections

For further information see section 8

# SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/?/equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

## 7.3. Specific end use(s)

Against electro-static charge

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

		STEL	500 ppm	
--	--	------	---------	--

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	Wear suitable protective gloves (nitrile)
<b>eyes :</b>	Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Colourless to yellow.
<b>odour :</b>	Alcohol.
<b>pH :</b>	Not available.
<b>Boiling point/range :</b>	82 °C <b>Flash</b>
<b>point :</b>	12 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	12 %
<b>lower limit :</b>	1.8 %
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.785 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Miscible with water
<b>Auto-ignition :</b>	460 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

#### 10.4. Conditions to avoid

Avoid overheating

#### 10.5. Incompatible materials

Strong oxidising agent

#### 10.6. Hazardous decomposition products

CO,CO2

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** May cause gastrointestinal disturbances  
**Skin contact :** May cause irritation.  
**Eye contact :** Irritating to eyes

#### Toxicological data :

Hazardous ingredient	CAS-nr.	method	LD50
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	oral rat	LC50 >2000 mg/kg
		inhal.rat	>20 mg/l
		LD50 derm.rabit	>2000 mg/kg

### SECTION 12: Ecological information

#### 12.1. Toxicity

not classified

#### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	>100 mg/l
		LC50 fish	>100 mg/l
		EC50 daphnia	>100 mg/l

#### 12.2. Persistence and degradability

No information available

#### 12.3. Bioaccumulative potential

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

No information available

#### 12.4. Mobility in soil

Miscible with water

#### 12.5. Results of PBT and vPvB assessment

No information available

#### 12.6. Other adverse effects

No information available

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

### SECTION 14: Transport information

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS, flammable

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

**Productname :** PROPOWER ANTI STATIC SPRAY  
**Ref.Nr.:** UDS000221\_3\_20110929

**Creationdate :** 29.09.11 Version : 1.0  
**Replaces:** UK10431

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode:	(D)
IMDG - Ems:	F-D,S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO	203

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1907/2006 (REACH)

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

*Explanation risk-phrases:	R11: Highly flammable. R12: Extremely flammable. R36: Irritating to eyes. R67: Vapours may cause drowsiness and dizziness.
*Explanation hazard statements:	H225 : Highly flammable liquid and vapour. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.



