



# Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

## 1 Identification of substance:

- **Product details:**
- **Trade name: Cramolin EMV-Lack**
- **Article number:** 124
- **Application of the substance / the preparation:** Effective Shielding from Electromagnetic Waves.
- **Manufacturer/Supplier:**  
ITW Chemische Produkte GmbH & Co. KG  
Mühlacker Str. 149  
D-75417 Mühlacker  
Tel: +49 7041 96340  
Fax: +49 7041 963429  
E-Mail: info@itwcp.de  
Internet: www.itwcp.de
- **Informing department:** Product safety department
- **Emergency information:**  
ITW Chemische Produkte GmbH & Co. KG  
Tel: +49 7041 96340    Mo - Do 8:00 - 16:30    Fr 8:00 - 14:00

## 2 Hazards identification

- **Hazard designation:**



Xi Irritant  
F+ Extremely flammable

- **Information pertaining to particular dangers for man and environment**

The marking is valid for all pressurized container up to 50ml carrying capacity.

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

At long or repeated contact with skin it may cause dermatitis due to the degreasing effect of the solvent.

Warning! Pressurized container.

Has a narcotizing effect.

R 12 Extremely flammable.

R 36 Irritating to eyes.

R 66 Repeated exposure may cause skin dryness or cracking.

R 67 Vapours may cause drowsiness and dizziness.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C.

Do not pierce or burn, even after use.

100.0 % by mass of the contents are flammable

Keep out of the reach of children

- **Classification system**

The classification is in line with current EC lists. It is expanded, however, by information from technical literature and by information furnished by supplier companies.

GB

(Contd. on page 2)



## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

**Trade name: Cramolin EMV-Lack**

(Contd. of page 1)

### 3 Composition/information on ingredients

- **Chemical characterization**
- **Description:** Mixture of the substances listed below with harmless additions.

- **components:**

CAS: 115-10-6 EINECS: 204-065-8	dimethyl ether	F+; R 12	25-<50%
	Pigment in solvents	Xi,  F; R 11-36-66-67	25-<50%
CAS: 67-64-1 EINECS: 200-662-2	acetone	Xi,  F; R 11-36-66-67	2.5-<10%
CAS: 123-86-4 EINECS: 204-658-1	n-butyl acetate	R 10-66-67	2.5-<10%
CAS: 107-98-2 EINECS: 203-539-1	1-methoxypropan-2-ol	R 10	< 2.5%

- **Additional information** For the wording of the listed risk phrases refer to section 16.

### 4 First aid measures

- **General information** Instantly remove any clothing soiled by the product.
- **After inhalation**  
Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.  
In case of unconsciousness bring patient into stable side position for transport.
- **After skin contact**  
Instantly wash with water and soap and rinse thoroughly.  
If skin irritation continues, consult a doctor.
- **After eye contact**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult doctor.
- **After swallowing**  
Do not induce vomiting; instantly call for medical help.  
A person vomiting while lying on their back should be turned onto their side.

### 5 Fire fighting measures

- **Suitable extinguishing agents** CO<sub>2</sub>, sand, extinguishing powder. Do not use water.
- **For safety reasons unsuitable extinguishing agents** Water.
- **Special hazards caused by the material, its products of combustion or resulting gases:**  
Formation of toxic gases is possible during heating or in case of fire.  
Store in a cool place. Heat will increase pressure and may lead to the container exploding.
- **Protective equipment:**  
Wear self-contained breathing apparatus.  
Do not inhale explosion gases or combustion gases.
- **Additional information** Cool endangered containers with water spray jet.

GB

(Contd. on page 3)



## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

**Trade name: Cramolin EMV-Lack**

(Contd. of page 2)

### 6 Accidental release measures

- **Person-related safety precautions:**  
Wear protective equipment. Keep unprotected persons away.  
Ensure adequate ventilation  
Keep away from ignition sources  
Avoid contact with the eyes and skin.
- **Measures for environmental protection:**  
Do not allow to enter drainage system, surface or ground water.
- **Measures for cleaning/collecting:**  
Ensure adequate ventilation.  
Do not flush with water or aqueous cleansing agents  
Absorb liquid components with liquid-binding material.  
Dispose of the material collected according to regulations.
- **Additional information:** See Section 7 for information on safe handling

### 7 Handling and storage

- **Handling**
- **Information for safe handling:**  
Store in cool, dry place in tightly closed containers.  
Keep away from heat and direct sunlight.  
Ensure good ventilation/exhaustion at the workplace.  
Open and handle container with care.
- **Information about protection against explosions and fires:**  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.  
Beware: Container is pressurized. Keep away from direct sun exposure and temperatures over 50°C. Do not open by force or throw into fire even after use.  
Do not spray on flames or red-hot objects.
- **Storage**
- **Requirements to be met by storerooms and containers:**  
Store in cool location.  
Store only in the original container.  
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Store away from foodstuffs.
- **Further information about storage conditions:**  
Store in cool, dry conditions in well sealed containers.  
Protect from heat and direct sunlight.

### 8 Exposure controls and personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Components with limit values that require monitoring at the workplace:**

**115-10-6 dimethyl ether (25-<50%)**

WEL (Great Britain)	Short-term value: 958 mg/m <sup>3</sup> , 500 ppm Long-term value: 766 mg/m <sup>3</sup> , 400 ppm
IOELV (European Union)	Long-term value: 1920 mg/m <sup>3</sup> , 1000 ppm

(Contd. on page 4)



## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

**Trade name: Cramolin EMV-Lack**

(Contd. of page 3)

**67-64-1 acetone (2.5-<10%)**

WEL (Great Britain)	Short-term value: 3620 mg/m <sup>3</sup> , 1500 ppm Long-term value: 1210 mg/m <sup>3</sup> , 500 ppm
IOELV (European Union)	Long-term value: 1210 mg/m <sup>3</sup> , 500 ppm

**123-86-4 n-butyl acetate (2.5-<10%)**

WEL (Great Britain)	Short-term value: 966 mg/m <sup>3</sup> , 200 ppm Long-term value: 724 mg/m <sup>3</sup> , 150 ppm
---------------------	---

**107-98-2 1-methoxypropan-2-ol (< 2.5%)**

WEL (Great Britain)	Short-term value: 560 mg/m <sup>3</sup> , 150 ppm Long-term value: 375 mg/m <sup>3</sup> , 100 ppm Sk
IOELV (European Union)	Short-term value: 568 mg/m <sup>3</sup> , 150 ppm Long-term value: 375 mg/m <sup>3</sup> , 100 ppm Skin

- **Additional information:** The lists that were valid during the compilation were used as basis.
- **Personal protective equipment**
- **General protective and hygienic measures**

The usual precautionary measures should be adhered to general rules for handling chemicals.  
Keep away from foodstuffs, beverages and feed.  
Take off immediately all contaminated clothing  
Wash hands during breaks and at the end of the work.  
Avoid contact with the eyes and skin.
- **Breathing equipment:** Use breathing protection in case of insufficient ventilation.
- **Protection of hands:** Protective gloves.
- **Material of gloves**

Butyl rubber, BR

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Tightly sealed safety glasses.

### 9 Physical and chemical properties:

**General Information**

<b>Form:</b>	Aerosol
<b>Colour:</b>	Copper coloured
<b>Odour:</b>	Solvent-like

**Change in condition**

<b>Melting point/Melting range:</b>	Not determined
<b>Boiling point/Boiling range:</b>	-24°C

<b>Flash point:</b>	-42°C
---------------------	-------

(Contd. on page 5)

GB



## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

**Trade name: Cramolin EMV-Lack**

(Contd. of page 4)

· <b>Ignition temperature:</b>	235°C
· <b>Self-inflammability:</b>	Product is not self igniting.
· <b>Danger of explosion:</b>	Product is not explosive. However, formation of explosive air/steam mixtures is possible.
· <b>Critical values for explosion:</b>	
<b>Lower:</b>	1.2 Vol %
<b>Upper:</b>	18.6 Vol %
· <b>Vapour pressure at 20°C:</b>	5200 hPa
· <b>Density at 20°C</b>	0.6 g/cm <sup>3</sup>
· <b>Solubility in / Miscibility with Water:</b>	Not miscible or difficult to mix
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	100.0 %

### 10 Stability and reactivity

- **Thermal decomposition/ Conditions to be avoided:** Protect from heat and direct sunlight.
- **Dangerous reactions** Danger of bursting
- **Dangerous products of decomposition:** none

### 11 Toxicological information

- **Acute toxicity:**
- **LD/LC50 values that are relevant for classification:** no data available.
- **Primary irritant effect:**
- **on the skin:** Frequent and/ or persistent contact with skin may cause skin irritation.
- **on the eye:** Irritant effect.
- **Additional toxicological information:**  
The product shows the following dangers according to the calculation method of the General EC Classification Guidelines for Preparations as issued in the latest version:  
Irritant
- **Sensitisation** No sensitising effect known.

### 12 Ecological information:

- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water.  
Do not allow product to reach ground water, water bodies or sewage system.

GB

(Contd. on page 6)

## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

Trade name: Cramolin EMV-Lack

(Contd. of page 5)

### 13 Disposal considerations

- **Product:**
- **Recommendation** Disposal must be made according to official regulations.

- **European waste catalogue**

16 05 04	gases in pressure containers (including halons) containing dangerous substances
----------	---

- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

### 14 Transport information

- **Land transport ADR/RID (cross-border)**



- **ADR/RID-GGVS/E Class:** 2 5F Gases.
- **Kemler Number:** -
- **UN-Number:** 1950
- **Packaging group:** -
- **Label** 2.1
- **Designation of goods:** 1950 AEROSOLS (DIMETHYL ETHER, ACETONE)

- **Maritime transport IMDG:**



- **IMDG Class:** 2.1
- **UN Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **EMS Number:** F-D,S-U
- **Marine pollutant:** No
- **Correct technical name:** AEROSOLS (DIMETHYL ETHER, ACETONE)

- **Air transport ICAO-TI and IATA-DGR:**



- **ICAO/IATA Class:** 2.1
- **UN/ID Number:** 1950
- **Label** 2.1
- **Packaging group:** -
- **Correct technical name:** AEROSOLS, flammable (DIMETHYL ETHER, ACETONE)

GB

(Contd. on page 7)

## Safety Data Sheet according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

Trade name: Cramolin EMV-Lack

(Contd. of page 6)

### 15 Regulatory information

\* **Designation according to EC guidelines:**

The product has been classified and labelled in accordance with EC Directives and the Ordinance on Hazardous Materials (GefStoffV).

**Code letter and hazard designation of product:**



Xi Irritant  
F+ Extremely flammable

**Risk phrases:**

- 12 Extremely flammable.
- 36 Irritating to eyes.
- 66 Repeated exposure may cause skin dryness or cracking.
- 67 Vapours may cause drowsiness and dizziness.

**Safety phrases:**

- 3 Keep in a cool place.
- 9 Keep container in a well-ventilated place.
- 16 Keep away from sources of ignition - No smoking.
- 23 Do not breathe fumes/aerosol.
- 24 Avoid contact with skin.
- 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- 33 Take precautionary measures against static discharges.
- 43 In case of fire, use sand, carbon dioxide or powdered extinguishing agent. Never use water.
- 51 Use only in well-ventilated areas.
- 60 This material and its container must be disposed of as hazardous waste.

**Special designation of certain preparations:**

- Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C.
- Do not pierce or burn, even after use.
- 100.0 % by mass of the contents are flammable
- Keep out of the reach of children

**National regulations**

- Water hazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.

GB

(Contd. on page 8)



## Safety Data Sheet

according to 1907/2006/EC, Article 31

Printing date 28.09.2010

V - 5

Revision: 28.09.2010

**Trade name: Cramolin EMV-Lack**

(Contd. of page 7)

### 16 Other information:

Information is based on our current knowledge but does not establish a promise of product characteristics and does not substantiate any contractual legal relationship.

· **Relevant R-phrases**

10 Flammable.

11 Highly flammable.

12 Extremely flammable.

36 Irritating to eyes.

66 Repeated exposure may cause skin dryness or cracking.

67 Vapours may cause drowsiness and dizziness.

· **Contact:** ITW Chemische Produkte GmbH & Co. KG, D-75417 Mühlacker

· \* **Data compared to the previous version altered.** .

GB