

Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

GALVA'PACK BRILLANT
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja as.	00358/(19)32.921	00358/(19)383.676
CRC Industries France	ZI du Val d'Argent B.P.90028, 12, Bld des Martyrs de Chateaubriant, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to 67/548/EEC or 1999/45/EC:**

Health: not classified
Physical: EXTREMELY FLAMMABLE
Environment: R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606

Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

the aquatic environment.

2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Risk-phrase(s) : R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety-phrase(s) :
 S2: Keep out of the reach of children.
 S16: Keep away from sources of ignition - No smoking.
 S23: Do not breathe vapours/spray.
 S35: This material and its container must be disposed of in a safe way.
 S51: Use only in well-ventilated areas.

Extra label elements according to Aerosol Dispenser Directive 75/324/EC: Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
 Without adequate ventilation formation of explosive mixtures may be possible.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
dimethyl ether	115-10-6	204-065-8	30-60	F+	12	A
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	265-185-4	5-15	Xn	65	B,P
ethyl acetate	141-78-6	205-500-4	5-10	F,Xi	11-36-66-67	B
Naphtha (petroleum), hydrotreated light	64742-49-0	265-151-9	5-10	Xn	65	B,P
n-butyl acetate	123-86-4	204-658-1	1-5		10-66-67	
aluminium powder (stabilized)	7429-90-5	231-072-3	1-5	F	11-15	A
1,2,4-trimethylbenzene	95-63-6	202-436-9	<1	Xn,N	10-20-36/37/38-51/53	A
mesitylene1,3,5-trimethylbenzene	108-67-8	203-604-4	<1	Xi,N	10-37-51/53	A
zinc oxide	1314-13-2	215-222-5	0.25-2.5	N	50/53	B
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	202-496-6	<0.1	Xn	21-40-41-43	B

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606

Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether		115-10-6	204-065-8	30-60	Flam. Gas 1, Press. Gas	H220	A
ethyl acetate		141-78-6	205-500-4	5-10	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	B
n-butyl acetate		123-86-4	204-658-1	1-5	Flam. Liq. 3, STOT SE 3	H226, H336	
aluminium powder (stabilized)		7429-90-5	231-072-3	1-5	Water-react. 2, Flam. Sol. 1	H261, H228	A
mesitylene 1,3,5-trimethylbenzene		108-67-8	203-604-4	<1	Flam. Liq. 3, STOT SE 3, Aquatic Chronic 2	H226, H335, H411	A
1,2,4-trimethylbenzene		95-63-6	202-436-9	<1	Flam. Liq. 3, Acute Tox. 4, Eye Irrit. 2, STOT SE 3, Skin Irrit. 2, Aquatic Chronic 2	H226, H332, H319, H335, H315, H411	A
zinc oxide		1314-13-2	215-222-5	0.25-2.5	Aquatic Acute 1, Aquatic Chronic 1	H400, H410	B
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime		96-29-7	202-496-6	<0.1	Carc. 2, Acute Tox. 4, Eye Dam. 1, Skin Sens. 1	H351, H312, H318, H317	B
Explanation notes							
A : substance with Community workplace exposure limit							
B : substance with national established workplace exposure limit							

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	Ingestion is unlikely to occur If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures**5.1. Extinguishing media**

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/??/equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep in a cool, dry, well ventilated place
 Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
mesitylene1,3,5-trimethylbenzene	108-67-8	TWA	20 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
1,2,4-trimethylbenzene	95-63-6	TWA	20 ppm
National established exposure limits, United Kingdom			
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm

8.2. Exposure controls

Control procedures : Ensure adequate ventilation
 Keep away from heat and sources of ignition
 Take precautionary measures against static discharges



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606

Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

Personal protection : Take precautions to avoid contact with skin and eyes when handling the product.
Ensure adequate ventilation

inhalation : In case of insufficient ventilation, wear suitable respiratory equipment.
Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)

hands and skin : Wear suitable protective gloves
(nitrile)

eyes : Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state : DME propelled liquid.
colour : Grey.
odour : Solvent.
pH : Not applicable.
Boiling point/range : Not available.
Flash point : < 0 °C
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0.969 g/cm³ (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : Not applicable.

9.2. Other information

No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis
 Repeated exposure may cause skin dryness or cracking.
Eye contact : May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	LD50 oral rat	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrodesulfurized heavy	64742-82-1	IC50 algae	1 - 10 mg/l
		LC50 fish	10 - 100 mg/l
		EC50 daphnia	10 - 100 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS, flammable

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No



Productname : GALVA'PACK BRILLANT
Ref.Nr.: BDS000216_3_20110606
Creationdate : 06.06.11 Version : 1.0
Replaces: AB307400

IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D,S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases:

- R10: Flammable.
- R11: Highly flammable.
- R12: Extremely flammable.
- R15: Contact with water liberates extremely flammable gases.
- R20: Harmful by inhalation.
- R21: Harmful in contact with skin.
- R36: Irritating to eyes.
- R37: Irritating to respiratory system.
- R40: Limited evidence of a carcinogenic effect.
- R41: Risk of serious damage to eyes.
- R43: May cause sensitization by skin contact.
- R65: Harmful: may cause lung damage if swallowed.
- R66: Repeated exposure may cause skin dryness or cracking.
- R67: Vapours may cause drowsiness and dizziness.
- R36/37/38: Irritating to eyes, respiratory system and skin.
- R50/53
- R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R51/53



Productname :	GALVA'PACK BRILLANT	Creationdate :	06.06.11 Version : 1.0
Ref.Nr.:	BDS000216_3_20110606	Replaces:	AB307400

*Explanation hazard statements:

- H220 : Extremely flammable gas.
- H225 : Highly flammable liquid and vapour.
- H226 : Flammable liquid and vapour.
- H228 : Flammable solid.
- H261 : In contact with water releases flammable gases.
- H312 : Harmful in contact with skin.
- H315 : Causes skin irritation.
- H317 : May cause an allergic skin reaction.
- H318 : Causes serious eye damage.
- H319 : Causes serious eye irritation.
- H332 : Harmful if inhaled.
- H335 : May cause respiratory irritation.
- H336 : May cause drowsiness or dizziness.
- H351 : Suspected of causing cancer .
- H400 : Very toxic to aquatic life.
- H410 : Very toxic to aquatic life with long lasting effects.
- H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

