

MATERIAL SAFETY DATA SHEET



Name of Company	:	Power Glory Battery Tech (HK) Co., Ltd
Address	:	Room E2B, 14 Floor, Hoi Bun Industrial Building,
		6 Wing Yip Street, Kwun Tong, Kowloon,
		Hong Kong
Department	:	Lithium Battery Development & Engineering Dept.
Tel	:	(852) 3427 5537
Fax	:	(852) 3427 5526
Contact Person	:	Jeremy Leung
UN 38.3 Report No.	:	RZUN2010-0521
Issued	:	January 03, 2011

The batteries are exempt articles and are not subject to the OSHA Hazard Communication Standard Requirement. This sheet is provided as technical information only. The information and recommendations set forth are made in good faith and are believed to be accurate as of the date of preparation. However, Power Glory makes no warranty expressed or Implied.

Section 1-Product and Company Identification

Product Name Lithium Metal Batteries	Type No: CR2450	Volts: 3V	Date of preparation: Jan. 03 2011
CHEMICAL SYSTEM: Lithium Manganese Dioxide	Approximate Weight: 6.7g		Designed for Recharge: NO
Company: Power Glory Battery Tech (Shenzhen) Co., Ltd.			Telephone Numbers: 86- (0)755-27543060 27543061
Address (Number, Street, City, State, and ZIP Code): Dong Keng Industrial Zone, Dong Keng Village, GongMing Town, Shenzhen China			Fax Numbers: 86- (0)755-27543062

Section 2- Composition/Information on Ingredients

Ingredient	CAS NO.	Content (wt%)
Lithium	7439-93-2	2.7
Propylene Carbonate	108-32-7	8.0
Manganese dioxide	1313-13-9	34.0
1,2-Dimethoxyethane	110-71-4	5.3
Lithium perchlorate	7791-03-9	1.0
Graphite	7782-72-5 1333-86-4	5.0

Section 3 – Hazards Identification

This contains lithium, organic solvent, and other combustible materials. For this reason, Improper handling of the battery could lead to distortion, leakage*, overheating, explosion of fire and cause human injury or equipment trouble. Please strictly observe safety instruction.

(*Leakage is defined as an unintended escape of liquid from a battery.)

Section 4 – First Aid Measures

None unless internal materials exposure. If contents are leaked out, observe following Instructions

Inhalation	Fumes can cause respiratory irritation . Remove to fresh air and consult a physician.
Skin	Immediately flush skin plenty of water. If itch or irritation by chemical bum persists, consult a physician.
Eyes	Immediately flush eye with plenty of water for at least 15 minutes. Consult a physician immediately
Ingestion	If a battery is swallowed, consult a physician immediately. If contents come into mouth, immediately rinse by plenty of water and consult a physician.

Section 5-Fire Fighting Measures

Extinguishing Media	Extinguisher for alkaline metal fire is effective. Plenty of cold water is also effective to cool the surrounding area and control the spread fire. But hydrogen gas may be evolved by the reaction of water and lithium and it can form an explosive mixture. Therefore in the case that lots of lithium batteries are burning in a confined space ,use a smothering agent.
Fire fighting procedure	Use self-contained breathing apparatus and full protective gear . Do not to inhale harmful gas .

Section 6-Accidental Release Measures

Accidental Releases: Do not breathe vapors or touch liquid with bare hands (see section 4).

Waste Disposal Methods: Evacuate area. If possible, a trained person should attempt to stop or contain the leak by neutralizing spill with soda lime or baking soda. A NIOSH Approved Acid Gas Filter Mask or Self-Contained Breathing Apparatus should be worn. Seal leaking battery and soda lime or baking soda in a plastic bag and dispose of as hazardous waste.

Other: Follow North American Emergency Response Guide (NAERG)#138 for cells involved in an accident, cells that have vented, or have exploded.



Section 7-Handling and Storage

1) Handling

Never swallow. Never reverse the positive and negative terminals when mounting . Never short-circuit the battery. Never heat. Never expose to open flame. Never disassemble. Never weld the terminal or wire to the body of the battery directly. Never touch the liquid leaked out of battery . Never bring fire close to battery liquid. Never touch battery for an extended period of time.

2) Storage

Never let the battery come into contact with water. Never store the battery in hot and high humid place.

Section 8 – Exposure Controls, Personal Protection

Respiratory Protection	NA
Ventilation	Local Exhaust NA
	Mechanical NA
	Special NA
	Other NA
Eye Protection	NA
Protective Gloves	NA
Other protective clothing	NA

Section 9 – Physical/Chemical Characteristics

Boiling Point:	1,2-Dimethoxyethane : 83°C
Vapor Pressure:	1,2-Dimethoxyethane :6.40(20°C)
Vapor Density:	1,2-Dimethoxyethane : 3.11
Solubility in Water:	1,2-Dimethoxyethane : :diffluence contact with water
Specific Gravity:	1,2-Dimethoxyethane :1.63
Melting Point:	1,2-Dimethoxyethane :-67°C
Evaporation Rate:	N/A
Water Reactive:	1,2-Dimethoxyethane : :diffluence contact with water

Appearance & Odor: 1,2-Dimethoxyethane : achromatic liquid; slight ether odor.

Section 10 – Stability and Reactivity

Stability	Stable
Incompatibility	Water
Hazardous polymerization	Will not occur.
Condition to avoid	See section 7.
Hazardous Decomposition or Byproducts	Hydrogen



Section 11 – Toxicological Information

Acute Toxicity:

1,2-Dimethoxyethane:

LC₅₀ (Inhalation): N/A

LD₅₀ : N/A

Eye Effects: Corrosive

Skin Effects: Corrosive



Section 12 –Ecological Information

Aquatic Toxicity: Do not let internal components enter marine environments. Avoid releases into waterways, wastewater or groundwater.

Section 13 – Disposal condition

The battery may be regulated by national or local regulation. Please follow the instructions of proper regulation. As electric capacity is left in a discarded battery and it comes into contact With other metals, it could lead to distortion, leakage, overheating, or explosion, so make sure to cover the (+) and (-) terminals with friction tape or some other insulator before disposal.

Section 14 – Transportation Information

Lithium battery model CR2450 is considered as “Not Restricted” cargo because they complied UN Recommendations.

Shipping Name Lithium Metal Batteries

Organizations governing the transport of lithium batteries

Area	Method	Organization	Special Provision
International	Air	IATA,ICAO	Best Practice 009
International	Water	IMO	188
U.S.A	Air, Rail, Highway, Water	DOT	49 CFR Section 173.185

These regulations are based on the UN Recommendations . Each special provision provides specifications on exceptions for shipping lithium batteries. All Power Glory’s batteries meet all special provisions

If all of following 2 requirements is satisfied, lithium metal batteries can be transported as “Not Restricted” cargo.

- 1) Lithium weight or equivalent lithium content must be less than value in table.

	Lithium Cell/Battery (Lithium weight)
Cell	1g or less
Battery	2g or less

*Equivalent lithium content (g) is calculated as 0.3 (g/Ah) times the rated capacity (Ah) .

- 2) Each cell or battery is of the type proven to meet the requirements of each test in the UN Manual of Tests and Criteria, Part III, section 38.3 Cells

Because the consignor has to take the responsibility, the customer has to confirm the exception conditions when shipping.

Section 15-Regulatory Information

EC Labeling : None

Risk Phrases :None

Safety Phrases : None

Labeling is not required because batteries are classified as “articles” under the Dangerous Preparations Directive and as such are exempt from the requirements of the Directive.

Section 16-Other Information

If you want further information, please contact:

Technology Manager

Wang Baojun

Dong Keng Industrial Zone,Dong keng Village,Gongming Town,Shenzhen,518106 P.R.China

Tel:+86-0755-27543061 Fax:+86-0755-27543062 <http://www.szlijia.com>



Last data revised 2011.01.03