









Connectors according to DIN 41612 / IEC 60603-2

Type C

Female connector



No. of contacts	Contact arrangement	Press-fit technology – Performance level II		
		Termination length		
				
Part number				
32		104-60014-xx	104-65015-xx	104-65016-xx
48		104-60044-xx	104-65045-xx	104-65046-xx
64		304-60054-02	304-65055-03	304-65056-04
96		304-60064-02	304-65065-03	304-65066-04

Note
– * Rear mating zone performance level II

Options
– Without flange
– Contact arrangement (see page 162)

Cross reference
– Type C with switching function (see page 155)
– VMEx (see page 152)
– Type C with IDC (see page 157)

Accessories


- Press-fit tool (see page 208)
- Support tool (see page 209)
- Coding accessories (see page 160)
- Shroud (see page 158)










On request

- Performance levels I + III or customer-specific
- Special contact length
- Alternative surface Sn, e. g. for WireWrap

Ordering note

- Only for 104
- PCB 1.5 to 2.0 mm = xxx-xxxx-01 with termination length = 3.2 mm
 - PCB 2.0 to 2.8 mm = xxx-xxxx-02 with termination length = 4.6 mm
 - PCB > 2.8 mm = xxx-xxxx-03 with termination length = 4.6 mm



No. of contacts	Contact arrangement	Solder technology – Performance level II				
		Termination length				
						Manual soldering with solder lug 
Part number						
32		104-40014	–	–	104-40016	–
48		104-40044	–	–	104-40046	–
64		304-40054-05 in THTR* 304-40054-05TH	304-40054-01 in THTR* 304-40054-01TH	304-40054-02 in THTR* 304-40054-02TH	304-40055-03	104-40115
96		304-40064-05 in THTR* 304-40064-05TH	304-40064-01 in THTR* 304-40064-01TH	304-40064-02 in THTR* 304-40064-02TH	304-40065-03	104-40075

Accessories – Coding accessories (see page 160)	On request – Performance levels I + III or customer-specific – Special contact length – Other termination lengths in THTR	Options – Board lock (see page 159) – Contact arrangement (see page 162)
Cross reference – Type C with switching function (see page 155) – VMEx (see page 152) – Type C with IDC (see page 157)	Note – * THTR (Through Hole Technology Reflow)	