



Patchcord, Fibre, Duplex, ST-ST, OM1



Specifications

		Port A	Port B
Connector Type		ST/MM	ST/MM
Connector Body	Material	Zn Alloy	Zn Alloy
	Colour	-	-
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 um	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 x 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
	Cable Colour	Orange	
Ferrule	Diameter	2.5 mm	2.5 mm
	Type	MM	MM
	Material	ZrO2 (Ceramic)	ZrO2 (Ceramic)
Connection at Cable		Crimp	Crimp
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		Twist - Lock Bayonet	Twist - Lock Bayonet
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3


Patchcord, Fibre, Duplex, SC-ST, OM1



Specifications

		Port A	Port B
Connector Type		SC/MM	ST/MM
Connector Body	Material	Plastic	Zn Alloy
	Colour	Beige	-
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 um	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 x 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
Ferrule	Cable Colour	Orange	
	Diameter	2.5 mm	2.5 mm
	Type	MM	MM
		ZrO2 (Ceramic)	ZrO2 (Ceramic)
Connection at Cable		Crimp	Crimp
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		Plug - In	Twist - Lock Bayonet
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3

Patchcord, Fibre, Duplex, SC-SC, OM1




Dimensions : Millimetres

Specifications

		Port A	Port B
Connector Type		SC/MM	SC/MM
Connector Body	Material	Plastic	Plastic
	Colour	Beige	Beige
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 um	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 x 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
	Cable Colour	Orange	
Ferrule	Diameter	2.5 mm	2.5 mm
	Type	MM	MM
	Material	ZrO2 (Ceramic)	ZrO2 (Ceramic)
Connection at Cable		Crimp	Crimp
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		Plug - In	Plug - In
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3

Patchcord, Fibre, Duplex, LC-LC, OM1




Dimensions : Millimetres

Specifications

		Port A	Port B
Connector Type		LC/MM	LC/MM
Connector Body	Material	Plastic	Plastic
	Colour	Beige	Beige
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 μ m	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 x 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
	Cable Colour	Orange	
Ferrule	Diameter	1.25 mm	1.25 mm
	Type	MM	MM
	Material	ZrO ₂ (Ceramic)	ZrO ₂ (Ceramic)
Connection at Cable		Crimp and Heat Shrinkable Tubing	Crimp and Heat Shrinkable Tubing
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		RJ45 Style	RJ45 Style
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3


Patchcord, Fibre, Duplex, LC-SC, OM1



Specifications

		Port A	Port B
Connector Type		LC/MM	SC/MM
Connector Body	Material	Plastic	Plastic
	Colour	Beige	Beige
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 um	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 x 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
Ferrule	Diameter	1.25 mm	2.5 mm
	Type	MM	MM
	Material	ZrO2 (Ceramic)	ZrO2 (Ceramic)
Connection at Cable		Crimp and Heat Shrinkable Tubing	Crimp
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		RJ45 Style	Plug - In
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3

Patchcord, Fibre, Duplex, LC-ST, OM1



Specifications

		Port A	Port B
Connector Type		LC/MM	ST/MM
Connector Body	Material	Plastic	Zn Alloy
	Colour	Beige	-
Connector Boot	Material	Plastic	Plastic
	Colour	Red and Black	Red and Black
Patchcord Length (Metre)		Customized	
Optical Cable	Fibre Type	OM1 62.5 / 125 µm	
	Fibre Count	2	
	Outer Sheath	LSZH	
	Cable Outer Diameter	2 × 2 mm	
	Strength Member	DuPont Kevlar	
	Outer Sheath	LSZH	
	Cable Colour	Orange	
Ferrule	Diameter	1.25 mm	2.5 mm
	Type	MM	MM
	Material	ZrO2 (Ceramic)	ZrO2 (Ceramic)
Connection at Cable		Crimp and Heat Shrinkable Tubing	Crimp
Connection at Fibre		353ND Glue	353ND Glue
Connection at Adapter		RJ45 Style	Twist - Lock Bayonet
Polishing		PC	PC
Insertion Loss (dB)		< 0.3	< 0.3

Part Number Table

Description	Part Number
Patchcord, Fibre, Duplex, ST-ST, OM1, 1M	PS11366
Patchcord, Fibre, Duplex, ST-ST, OM1, 2M	PS11367
Patchcord, Fibre, Duplex, ST-ST, OM1, 3M	PS11368
Patchcord, Fibre, Duplex, ST-ST, OM1, 5M	PS11369
Patchcord, Fibre, Duplex, ST-ST OM1, 10M	PS11370
Patchcord, Fibre, Duplex, SC-ST, OM1, 1M	PS11376
Patchcord, Fibre, Duplex, SC-ST, OM1, 2M	PS11377
Patchcord, Fibre, Duplex, SC-ST, OM1, 3M	PS11378
Patchcord, Fibre, Duplex, SC-ST, OM1, 5M	PS11379
Patchcord, Fibre, Duplex, SC-ST OM1, 10M	PS11380
Patchcord, Fibre, Duplex, SC-SC, OM1, 1M	PS11386
Patchcord, Fibre, Duplex, SC-SC, OM1, 2M	PS11387
Patchcord, Fibre, Duplex, SC-SC, OM1, 3M	PS11388
Patchcord, Fibre, Duplex, SC-SC, OM1, 5M	PS11389
Patchcord, Fibre, Duplex, SC-SC OM1, 10M	PS11390
Patchcord, Fibre, Duplex, LC-LC, OM1, 1M	PS11396
Patchcord, Fibre, Duplex, LC-LC, OM1, 2M	PS11397
Patchcord, Fibre, Duplex, LC-LC, OM1, 3M	PS11398
Patchcord, Fibre, Duplex, LC-LC, OM1, 5M	PS11399
Patchcord, Fibre, Duplex, LC-LC OM1, 10M	PS11400
Patchcord, Fibre, Duplex, LC-SC, OM1, 1M	PS11406
Patchcord, Fibre, Duplex, LC-SC, OM1, 2M	PS11407
Patchcord, Fibre, Duplex, LC-SC, OM1, 3M	PS11408
Patchcord, Fibre, Duplex, LC-SC, OM1, 5M	PS11409
Patchcord, Fibre, Duplex, LC-SC OM1, 10M	PS11410
Patchcord, Fibre, Duplex, LC-ST, OM1, 1M	PS11416
Patchcord, Fibre, Duplex, LC-ST, OM1, 2M	PS11417
Patchcord, Fibre, Duplex, LC-ST, OM1, 3M	PS11418
Patchcord, Fibre, Duplex, LC-ST, OM1, 5M	PS11419
Patchcord, Fibre, Duplex, LC-ST OM1, 10M	PS11420

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2011.