# EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire HS10; Ecoloy ® TSC

Date of issue: 01.05.2006 Revised on: 23.11.2011 Date of print: 25.11.2011 Page: 1(3)

#### 1. Identification of the substance/preparation and of the company/undertaking

Information on the product

Trade name: Solder-wire HS10; Ecoloy ® TSC Usage of the product / preparation Solder wire for soft soldering

Identification of the manufacturer / supplier

Address: Stannol GmbH

Oskarstr. 3 -7 42283 Wuppertal

 Phone:
 0202 585 0

 Fax:
 0202 585 155

**Emergency call:** 0202 585 119 (only during trading hour (8:00 h – 17:00 h)

E-mail: werner.kruppa@stannol.de

#### 2. Hazards identification

Not a composition for the purposes of the Dangerous Substances Regulations, but nevertheless observe items 4-16

#### Additional hazards for human health and environment:

May cause occupational asthma

### 3. Composition/Information on ingredients;

Chemical characterization: Tin-Silver-Copper alloy , with flux max. 3,5 % rosin; halide activated

Composition according to EC 1907/2006:

Contents	CAS No.	EINECS No.	Symbols	R-phrases:	Substance
0,5-0,9%	7440-50-8	231-159-6	-	-	copper
3,6-4,0%	7440-22-4	231-131-3			silver
remainder	7440-31-5	231-141-8			Tin
<3,5%	8050-09-7	232-475-7	Xi	43	rosin

#### The wording of the R-phrases stated is indicated in Section 16

#### 4. First Aid measures

General information: If casualty is unconscious but breathing, place in the recovery position. If breathing

has stopped apply artificial resuscitation or give oxygen by mask

After inhalation: Remove patient to fresh air. If irritation resists, obtain medical attention.

After skin contact: If any skin irritation develops seek medical attention

After eye contact: Flush immediately with plenty of water. In cases where spitting flux has entered the

eye seek medical attention.

After ingestion: Rinse mouth immediately and drink plenty of water. Seek medical advice.

Hints for doctors.

Inhalation of the flux fumes given off at soldering temperatures will irritate the nose,

throat and respiratory system. Repeated or prolonged exposure to flux fumes may

cause shortness of breath and cough..

Physician's information

**Treatment:** Decontamination, treatment of symptoms.

### 5. Fire fighting measures

Suitable extinguishing media: Use extinguishing media appropriate to surrounding fire conditions

Special protective equipment for fire fighting Wear self-contained breathing apparatus and protective clothing to prevent contact

with skin and eyes.

#### Accidental release measures

Pick up and place in appropriate container

#### 7. Handling and storage

The fumes produced during soldering should be extracted away from the breathing zone of the operators. Ensure the area is well

ventilated. Wash hands with soap and warm water after handling, particularly before eating, drinking or smoking.

The product should be stored in a cool, dry area.

# EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire HS10; Ecoloy ® TSC

Date of issue: 01.05.2006 Revised on: 23.11.2011 Date of print: 25.11.2011 Page: 2(3)

#### 8. Exposure controls and personal protection

Additional information on system design:

Local exhaust or dilution ventilation and control of process conditions are suitable methods..

Substances with limit values to be monitored at the working place:

Danger to health at the working place:

Peak limit category:

Working place limit values according to TRGS 900 from Section 2 for Germany:

 Product name
 CAS No.
 ml/m³ (ppm)
 mg/m³
 Type

 Tin
 7440-31-5
 2
 MAK (NL)

 Copper
 7440-50-8
 1
 MAK (DFG)

 Silver
 7440-22-4
 0,1
 MAK (DFG)

Working place limit values according to EH40/2005 of the UK:

Product name CAS No. ml/m³ (ppm) mg/m³ mg/m³ mg/m³ 8h TWA reference period 15 min STEL reference period

 Tin
 7440-31-5
 2

 Copper
 7440-50-8
 1

 Silver
 7440-22-4
 0,1

 Positive boood colder
 9050-00-7
 0.0

Rosin-based solder 8050-09-7 0,05 0,15

flux fume

Skin resorption / Sensitization: Skin resorption ---- Sensitization: S (rosin)

**General protection and hygiene measures** Avoid direct contact with eyes, the skin and clothing.

Personal protection

**Respiratory protection:** If concentrations are over the exposure limit, use a supplied air respirator.

Hand protection:

Eye protection:

Personal protection:

Use heat resistant gloves if required.
Operators should wear goggles
Light protective clothing

#### 9. Physical and chemical properties

Form: Tin-Silver-Copper Solder

 Melting Point:
 217 °C

 Vapour Pressure:
 n.a.
 n.a.

 Density(20°C):
 7-8 g/cm³

# 10. Stability and reactivity

Reaction with substances: Possible with oxidising agents.

Hazardous combustion or none

decomposition products:

### 11. Toxicological information

The toxicological classification of the product is based on the results of the calculation procedure of the general preparation directive 1999/45/EC.

#### Acute Effects:

Acute intoxication by ingestion of skin contact with lead is inprobable. High doses nevertheless lead to symptoms of poisoning. Inhalation of fumes can irritate the respiratory tract and eyes.. May cause occupational asthma

None toxic metal.

#### 12. Ecological information

General information: No effect to environment known

### 13. Disposal considerations

**Disposal information** 

**Product:** Contact a licensed professional waste disposal service to dispose of this material. **Further information:** Observe all federal, state and local environmental regulations. Collect metal for recycling

Waste identity number: Waste identity number EAK-code: 120104

# EC Safety Data Sheet according to Directive 1907/2006

Trade name: Solder-wire HS10; Ecoloy ® TSC

Date of issue: 01.05.2006 Revised on: 23.11.2011 Date of print: 25.11.2011 Page: 3(3)

# 14. Transport information

GGVSEB/ADR: The product is not classified as hazardous for transport

### 15. Regulatory information;

Labelling information: The product is classified and labelled according to the EC Directives.

Not subject to current legislation WGK 1 (weakly water-endangering)

Classification according to the TA Luft: Organic materials class III; whole-carbon-concentration: Max. acceptable

Emission50 mg/m<sup>3</sup> (mass-flow-rate >= 0,5 kg/h)

Ingredients: Tin, silver; copper, rosin

#### 16.Other information

R-phrases point 3: R 43 May cause of sensitization by skin contact.

n.a. not applicable n.k. not known Other information

Water hazard class:

This statement is based on our current knowledge and offers no assurance of product properties.

**Department issueing the data sheet** Stannol GmbH/Quality Assurance/Laboratory

**Contact person** Dr. Kruppa