

60EN 362 5C

Revision: 03.08.2011
printing date: 02.11.2011

SECTION 1: Identification of the substance/mixture and of the company/undertaking

Product identifier:

60EN 362 5C

Relevant identified uses of the substance or mixture and uses advised against:

Intended use:
Solder Wire

Details of the supplier of the safety data sheet:

MULTICOMP Premier Farnell plc
150 Armley Road
LEEDS LS12 2QQ
Tel. : +44 (0) 870 129 8608
Fax

Emergency Telephone Number:

+44 (0) 870 202530

SECTION 2: Hazards identification

Classification of the substance or mixture:

Classification (DPD):

Substances and preparations marketed in a specific form or within specific containers need not to be classified in accordance with 67/548/EEC and 1999/45/EC for chemical substances and preparations.

Label elements (DPD):

Contains lead which may harm your health. Lead can cause birth defects and other reproductive harm.
Regulations forbid the use of lead solder in any private or public drinking water supply system.
Avoid breathing fumes given out during soldering.
Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).
After handling solder wash hands with soap and water before eating, drinking or smoking.
Keep out of reach of children.
Substances and preparations marketed in a specific form or within specific containers need not to be classified in accordance with 67/548/EEC and 1999/45/EC for chemical substances and preparations.

Other hazards:

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs. Prolonged or repeated exposure to flux fumes may result in sensitisation in sensitive workers.

SECTION 3: Composition/information on ingredients

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Rosin 8050-09-7	232-475-7	1- 5 %	Skin sensitizer 1 H317

Only dangerous ingredients for which a CLP classification is already available are displayed in this table.

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Tin 7440-31-5	231-141-8	50 - 60 %	
Lead 7439-92-1	231-100-4 01-2119513221-59	30 - 40 %	
Rosin 8050-09-7	232-475-7	1 - 5 %	R43

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

Description of first aid measures:**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Obtain medical attention if irritation persists.

Eye contact:

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

Ingestion:

Do not induce vomiting.
Seek medical advice.

Most important symptoms and effects, both acute and delayed:

No particular measures required.

Indication of any immediate medical attention and special treatment needed:

See section: Description of first aid measures

SECTION 5: Firefighting measures

Combustion behaviour:

The product itself does not burn. Any fire extinguishing action should be appropriate to the surroundings.

Extinguishing media:**Suitable extinguishing media:**

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

Do not use water on fires where molten metal is present.

Special hazards arising from the substance or mixture:

High temperatures may produce heavy metal dust, fumes or vapours.
The flux medium will give rise to irritating fumes.

Advice for firefighters:

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures**Personal precautions, protective equipment and emergency procedures:**

Wear protective equipment.

Environmental precautions:

Do not empty into drains / surface water / ground water.

Methods and material for containment and cleaning up:

Scrape up spilled material and place in a closed container for disposal.

Reference to other sections:

See advice in chapter 8

SECTION 7: Handling and storage**Precautions for safe handling:**

Extraction is necessary to remove fumes evolved during reflow.
When using do not eat, drink or smoke.
Wash hands before breaks and immediately after handling the product.
See advice in chapter 8

Hygiene measures:

Good industrial hygiene practices should be observed.
Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.

Conditions for safe storage, including any incompatibilities:

Ensure good ventilation/extraction.
Store in a cool, dry place.

Specific end use(s):

Solder Wire

SECTION 8: Exposure controls/personal protection

Control parameters:

Valid for
Great Britain

Ingredient	ppm	mg/m ³	Type	Category	Remarks
TIN (INORGANIC COMPOUNDS AS SN) 7440-31-5		2	Time Weighted Average (TWA):	Indicative	ECLTV
INORGANIC LEAD AND ITS COMPOUNDS 7439-92-1		0,15	Time Weighted Average (TWA):		EU_OEL
LEAD AND ITS IONIC COMPOUNDS 7439-92-1			Biological Limit Value:		EU_OEL_II
LEAD AND LEAD COMPOUNDS, OTHER THAN LEAD ALKYL (AS PB) 7439-92-1		0,15	Time Weighted Average (TWA):		EH40 WEL
ROSIN-BASED SOLDER FLUX FUME 8050-09-7		0,05	Time Weighted Average (TWA):		EH40 WEL
ROSIN-BASED SOLDER FLUX FUME 8050-09-7		0,15	Short Term Exposure Limit (STEL):		EH40 WEL

Colophony (Rosin) and derivatives: Rosin-based flux fume as total resin acids.

Exposure controls:

Engineering controls:

Extraction is necessary to remove fumes evolved during reflow.
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.
Ensure good ventilation/extraction.

Respiratory protection:

In case of dust formation, we recommend wearing of appropriate respiratory protection equipment with particle filter P.
This recommendation should be matched to local conditions.
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Filter type: A

Hand protection:

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.
The use of chemical resistant gloves such as Nitrile are recommended.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties:

Appearance	solid
Odor	grey None
pH	not applicable
Initial boiling point	Not determined
Flash point	not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density (20 °C (68 °F))	8,5 g/cm ³

Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	183,0 - 188,0 °C (361.4 - 370.4 °F)
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

Other information:

No data available / Not applicable

SECTION 10: Stability and reactivity**Reactivity:**

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.
Reacts with strong oxidants.

Chemical stability:

Stable under recommended storage conditions.

Possibility of hazardous reactions:

See section reactivity

Conditions to avoid:

No decomposition if stored and applied as directed.

Incompatible materials:

None if used properly.

Hazardous decomposition products:

Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11: Toxicological information**General toxicological information:**

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

Harmful if swallowed.

Inhalative toxicity:

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs. Prolonged or repeated exposure to flux fumes may result in sensitisation in sensitive workers.

Dermal toxicity:

May cause sensitization by skin contact.

Skin irritation:

Fumes emitted during soldering may irritate the skin.

Eye irritation:

Fumes emitted during soldering may irritate the eyes.

Other remarks:

Chronic overexposure to lead may result in damage to the blood forming, nervous, urinary and reproductive systems. Severe lead toxicity will cause sterility, abortion and neonatal mortality and morbidity.

SECTION 12: Ecological information

General ecological information:

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Ecotoxicity:

May cause long-term adverse effects in the aquatic environment.

Mobility:

The product is insoluble and sinks in water.

Bioaccumulative potential:

Octanol/Water distribution coefficient: Not applicable

Toxicity:

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Rosin 8050-09-7	LC50	> 1.000 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Rosin 8050-09-7	EC50	911 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Rosin 8050-09-7	EC50	> 100 mg/l	Algae	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	

Persistence and degradability:

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Rosin 8050-09-7		aerobic	36 - 46 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)

SECTION 13: Disposal considerations

Waste treatment methods:
Product disposal:

Wherever possible unwanted solder alloy should be recycled for recovery of metal.
Otherwise dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of as unused product.

Waste code

16 03 03 - inorganic wastes containing dangerous substances

SECTION 14: Transport information

General information:

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture:

VOC content < 1 %

National regulations/information (Great Britain):

Remarks	<p>The Health & Safety at Work Act 1974.</p> <p>The Control of Lead at Work Regulations. L132:Control of Lead at Work: Approved Code of Practice and Guidance.</p> <p>The Control of Substances Hazardous to Health Regulations. L5:General Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to control chemicals.</p> <p>IND (G)248L:Solder fume and you. IND(G)249L:Controlling health risks from rosin (colophony) based solder fluxes.</p> <p>Employees should be under medical surveillance if the risk assessment made under the Control of Lead at Work Regulations indicates they are likely to be exposed to significant concentrations of lead, or if an Employment Medical Advisor or appointed doctor so certifies.</p> <p>A woman employed on work which exposes her to lead should notify her employer as soon as possible if she becomes pregnant. The Employment Medical Advisor / Appointed Doctor should be informed of the pregnancy.</p> <p>Under the Management of Health and Safety at Work Regulations, employers are required to assess the particular risks to health at work of pregnant workers and workers who have recently given birth or who are breast feeding.</p>
---------	--

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

R43 May cause sensitisation by skin contact.

H317 May cause an allergic skin reaction.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.

Substances and preparations marketed in a specific form or within specific containers need not to be classified in accordance with 67/548/EEC and 1999/45/EC for chemical substances and preparations.