

Loctite 638

Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 11

sds no.: 153473

V002.2 Revision: 25.08.2011

printing date: 08.11.2011

SECTION 1: Identification of the substance/mixture and of the company/undertaking

Product identifier:

Loctite 638

Relevant identified uses of the substance or mixture and uses advised against:

Intended use:

Joint sealant, acrylate

Details of the supplier of the safety data sheet:

Henkel Limited Technologies House Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (0)1442 278000 Fax-no.: +44 (0)1442 278071

ua-productsafety.uk@uk.henkel.com

Emergency Telephone Number:

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

Classification of the substance or mixture:

Classification (DPD):

Sensitizing

R43 May cause sensitisation by skin contact.

Xi - Irritant

R37/38 Irritating to respiratory system and skin.

R41 Risk of serious damage to eyes.

MSDS-No.: 153473 Loctite 638 Page 2 of 11

V002.2

Label elements (DPD):

Xi - Irritant



Risk phrases:

R37/38 Irritating to respiratory system and skin.

R41 Risk of serious damage to eyes.

R43 May cause sensitisation by skin contact.

Safety phrases:

S24/25 Avoid contact with skin and eyes.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S28 After contact with skin, wash immediately with plenty of water and soap.

S37/39 Wear suitable gloves and eye/face protection.

S51 Use only in well-ventilated areas.

Additional labeling:

For consumer use only: S2 Keep out of the reach of children

S46 If swallowed, seek medical advice immediately and show this container or label.

Contains:

Hydroxypropyl methacrylate,

Acrylic acid

Other hazards:

May produce an allergic reaction.

Non corrosive to skin in accordance with the invitro test method, B40 skin corrosion - Human skin model assay, specified in Part B of Annex V to Directive 67/548/EEC.

SECTION 3: Composition/information on ingredients

General chemical description:

Methacrylate resin based product containing Acrylic Acid

Base substances of preparation:

Methacrylates

MSDS-No.: 153473 Loctite 638 Page 3 of 11

V002.2

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Acrylic acid	201-177-9	>= 5-< 10 %	Acute toxicity 4; Oral
79-10-7			H302
			Skin corrosion 1A
			H314
			Flammable liquids 3
			H226
			Acute toxicity 4; Dermal H312
			Acute hazards to the aquatic environment 1 H400
			Acute toxicity 4; Inhalation
			H332
Cumene hydroperoxide	201-254-7	>= 1-< 2,5 %	Acute toxicity 4; Dermal
80-15-9		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	H312
			Specific target organ toxicity - repeated
			exposure 2
			H373
			Acute toxicity 3; Inhalation
			H331
			Acute toxicity 4; Oral
			H302
			Organic peroxides E
			H242
			Chronic hazards to the aquatic environment 2 H411
			Skin corrosion 1B
			H314
Methacrylic acid	201-204-4	>= 1-< 5 %	Acute toxicity 4; Oral
79-41-4			H302
			Skin corrosion 1A
			H314
			Acute toxicity 4; Dermal
			H312
2-Hydroxyethyl methacrylate	212-782-2	>= 0,1-< 1 %	Serious eye irritation 2
868-77-9	01-2119490169-29		H319
			Skin irritation 2
			H315
			Skin sensitizer 1
			H317
Cumene	202-704-5	>= 0-< 2,5 %	Flammable liquids 3
98-82-8			H226
			Aspiration hazard 1
			H304
			Specific target organ toxicity - single
			exposure 3
			H335
			Chronic hazards to the aquatic environment 2
			H411

Only dangerous ingredients for which a CLP classification is already available are displayed in this table. For full text of the H - statements and other abbreviations see section 16 "Other information". Substances without classification may have community workplace exposure limits available.

MSDS-No.: 153473 Loctite 638 Page 4 of 11

V002.2

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Hydroxypropyl methacrylate 27813-02-1	248-666-3	>= 25 - < 50 %	Xi - Irritant; R36, R43
Acrylic acid 79-10-7	201-177-9	>= 5 - < 10 %	Xn - Harmful; R20/21/22 R10 C - Corrosive; R35 N - Dangerous for the environment; R50
Cumene hydroperoxide 80-15-9	201-254-7	>= 1 -< 2,5 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 O - Oxidizing; R7 C - Corrosive; R34 N - Dangerous for the environment; R51/53
Methacrylic acid 79-41-4	201-204-4	>= 1 - < 5 %	C - Corrosive; R35 Xn - Harmful; R21/22
2-Hydroxyethyl methacrylate 868-77-9	212-782-2 01-2119490169-29	>= 0,1 - < 1 %	Xi - Irritant; R36/38 R43
Cumene 98-82-8	202-704-5	>= 0 -< 2,5 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51/53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'. Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

Description of first aid measures:

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.

Seek medical advice.

Most important symptoms and effects, both acute and delayed:

SKIN: Redness, inflammation.

EYE: Irritation, conjunctivitis.

SKIN: Rash, Urticaria.

Indication of any immediate medical attention and special treatment needed:

See section: Description of first aid measures

SECTION 5: Firefighting measures

Extinguishing media:

Suitable extinguishing media:

Carbon dioxide, foam, powder

Special hazards arising from the substance or mixture:

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

Sulphur oxides

MSDS-No.: 153473 Loctite 638 Page 5 of 11

V002.2

Advice for firefighters:

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures:

Avoid skin and eye contact.

Environmental precautions:

Do not let product enter drains.

Methods and material for containment and cleaning up:

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Conditions to avoid on disposal:

No information.

Reference to other sections:

See advice in chapter 8

SECTION 7: Handling and storage

Precautions for safe handling:

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Hygiene measures:

Good industrial hygiene practices should be observed.

Conditions for safe storage, including any incompatibilities:

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

Specific end use(s):

Joint sealant, acrylate

SECTION 8: Exposure controls/personal protection

Control parameters:

Valid for

Great Britain

Ingredient	ppm	mg/m ³	Туре	Category	Remarks
METHACRYLIC ACID 79-41-4	40	143	Short Term Exposure Limit (STEL):		EH40 WEL
METHACRYLIC ACID 79-41-4	20	72	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	25	125	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):		EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	ECTLV
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):	Indicative	ECTLV
CUMENE 98-82-8	20	100	Time Weighted Average (TWA):	Indicative	ECTLV

MSDS-No.: 153473 Loctite 638 Page 6 of 11

V002.2

Exposure controls:

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties:

Appearance liquid green
Odor irritating

pH No data available / Not applicable Initial boiling point > 100,0 °C (> 100,0 100,0 °C) Flash point > 93,3 °C (> 93,3 93,3 °C) Decomposition temperature No data available / Not applicable

Vapour pressure < 4,0000000 mbar

(20 °C (68 °F))

Density 1,0500 g/cm3

()
Bulk density
No data available / Not applicable
Viscosity
No data available / Not applicable
Viscosity (kinematic)
No data available / Not applicable
Explosive properties
No data available / Not applicable

Solubility (qualitative) Miscible

(Solvent: Acetone)

Solidification temperature No data available / Not applicable No data available / Not applicable Melting point No data available / Not applicable Flammability Auto-ignition temperature No data available / Not applicable No data available / Not applicable Explosive limits No data available / Not applicable Partition coefficient: n-octanol/water Evaporation rate No data available / Not applicable No data available / Not applicable Vapor density No data available / Not applicable Oxidising properties

Other information:

No data available / Not applicable

SECTION 10: Stability and reactivity

Reactivity:

Reaction with strong acids. Reacts with strong oxidants. MSDS-No.: 153473 Loctite 638 Page 7 of 11

V002.2

Chemical stability:

Stable under recommended storage conditions.

Possibility of hazardous reactions:

See section reactivity

Conditions to avoid:

Stable

SECTION 11: Toxicological information

General toxicological information:

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

May cause irritation to the digestive tract.

Inhalative toxicity:

Irritating to respiratory system

Skin irritation:

Irritating to the skin.

Eye irritation:

Risk of serious damage to eyes

Sensitizing:

May cause sensitization by skin contact.

Acute toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LD50 LC50 LD50	550 mg/kg 220 ppm 500 mg/kg	oral inhalation dermal	4 h	rat rat rat	
Methacrylic acid 79-41-4	LC50	7,1 mg/l	inhalation	4 h	rat	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Methacrylic acid 79-41-4	not sensitising	Buehler test	guinea pig	

MSDS-No.: 153473 Loctite 638 Page 8 of 11

V002.2

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Acrylic acid 79-10-7	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Cumene hydroperoxide 80-15-9	negative	dermal		mouse	
2-Hydroxyethyl methacrylate 868-77-9	negative bacterial rever positive mutation assay (e Ames test) in vitro mammalia chromosome aberration test		with and without with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay) OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

Precautions required with respect to Environmental Hazards of articles in which this product is used should be considered. The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

MSDS-No.: 153473 Loctite 638 Page 9 of 11

V002.2

Toxicity:

Hazardous components CAS-No.	Value type	Value	Acute Toxicity	Exposure time	Species	Method
Hydroxypropyl methacrylate	LC50	493 mg/l	Study Fish	48 h	Leuciscus idus melanotus	
27813-02-1 Acrylic acid 79-10-7	LC50	27 mg/l	Fish	96 h	Salmo gairdneri (new name: Oncorhynchus mykiss)	OECD Guideline 203 (Fish, Acute
Acrylic acid 79-10-7	EC50	47 mg/l	Daphnia	48 h	Daphnia magna	Toxicity Test) OECD Guideline 202 (Daphnia sp.
Acrylic acid	EC50	0,04 mg/l	Algae	72 h	Scenedesmus subspicatus (new	Acute Immobilisation Test) OECD Guideline
79-10-7	Leso	0,0 1 mg/1	riigue	,211	name: Desmodesmus subspicatus)	201 (Alga, Growth Inhibition Test)
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp.
Cumene hydroperoxide	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	Acute Immobilisation Test) OECD Guideline
80-15-9		, 2			1	201 (Alga, Growth Inhibition Test)
Methacrylic acid 79-41-4	LC50	100 - 180 mg/l	Fish	96 h	Brachydanio rerio (new name: Danio rerio)	OECD Guideline 203 (Fish, Acute Toxicity Test)
Methacrylic acid 79-41-4	EC50	> 130 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp.
						Acute Immobilisation Test)
Methacrylic acid 79-41-4	EC50	> 8,2 mg/l	Algae			OECD Guideline 201 (Alga, Growth
2-Hydroxyethyl methacrylate 868-77-9	LC50	227 mg/l	Fish	96 h	Pimephales promelas	Inhibition Test) OECD Guideline 203 (Fish, Acute
2-Hydroxyethyl methacrylate 868-77-9	EC50	380 mg/l	Daphnia	48 h	Daphnia magna	Toxicity Test) OECD Guideline 202 (Daphnia sp.
						Acute Immobilisation Test)
2-Hydroxyethyl methacrylate 868-77-9	EC50	345 mg/l	Algae	72 h	Selenastrum capricornutum (new name: Pseudokirchnerella	OECD Guideline
Cumene 98-82-8	LC50	4,8 mg/l	Fish	96 h	subcapitata) Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute
Cumene 98-82-8	EC50	4 mg/l	Daphnia	48 h	Daphnia magna	Toxicity Test) OECD Guideline 202 (Daphnia sp. Acute
Cumene	EC50	2,6 mg/l	Algae	72 h	Selenastrum capricornutum	Immobilisation Test) OECD Guideline
98-82-8	ECJU	2,0 mg/1	Aigae	/ 2 11	(new name: Pseudokirchnerella subcapitata)	

Persistence and degradability:

Hazardous components	Result	Route of	Degradability	Method
CAS-No.		application		

MSDS-No.: 153473 Loctite 638 Page 10 of 11

V002.2

Hydroxypropyl methacrylate 27813-02-1	readily biodegradable	aerobic	94,2 %	OECD Guideline 301 E (Ready biodegradability: Modified OECD Screening Test)
Acrylic acid 79-10-7	readily biodegradable	aerobic	81 %	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)
Cumene hydroperoxide 80-15-9			18 %	OECD Guideline 301 E (Ready biodegradability: Modified OECD Screening Test)
Methacrylic acid 79-41-4	readily biodegradable	aerobic	86 %	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)
2-Hydroxyethyl methacrylate 868-77-9	readily biodegradable	aerobic	98 %	OECD Guideline 301 E (Ready biodegradability: Modified OECD Screening Test)
Cumene 98-82-8		aerobic	86 %	

Bioaccumulative potential / Mobility in soil:

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Hydroxypropyl methacrylate 27813-02-1	0,97					
Acrylic acid 79-10-7	0,46				25 °C	OECD Guideline 107 (Partition Coefficient (noctanol / water), Shake Flask Method)
Cumene hydroperoxide 80-15-9		9,1				OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene hydroperoxide 80-15-9	2,16					,
Methacrylic acid 79-41-4	0,93					
Cumene 98-82-8		35,5		Carassius auratus		OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene 98-82-8	3,55				23 °C	OECD Guideline 107 (Partition Coefficient (noctanol / water), Shake Flask Method)

SECTION 13: Disposal considerations

Waste treatment methods:

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information

General information:

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture:

MSDS-No.: 153473 Loctite 638 Page 11 of 11

V002.2

VOC content (1999/13/EC)

< 5 %

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text

of all abbreviations indicated by codes in this safety data sheet are as follows:

R10 Flammable.

R20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

R21/22 Harmful in contact with skin and if swallowed.

R23 Toxic by inhalation.

R34 Causes burns.

R35 Causes severe burns.

R36 Irritating to eyes.

R36/38 Irritating to eyes and skin.

R37 Irritating to respiratory system.

R43 May cause sensitisation by skin contact.

R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.

R50 Very toxic to aquatic organisms.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R7 May cause fire.

H226 Flammable liquid and vapour.

H242 Heating may cause a fire.

H302 Harmful if swallowed.

H304 May be fatal if swallowed and enters airways.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H331 Toxic if inhaled.

H332 Harmful if inhaled.

H335 May cause respiratory irritation.

H373 May cause damage to organs through prolonged or repeated exposure.

H400 Very toxic to aquatic life.

H411 Toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and it's subsequent amendments, and Commission Directive 1999/45/EC.