



Specifications:

Approval category	: UL224
Standard	: CSA, LR54949
Approval bodies	: UL
Shrink ratio	: 2:1
Shrink temperature	: 100°C
Minimum operating temperature	: -55°C
Maximum operating temperature	: 135°C

Specification Table

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter	Fully Shrunk Diameter	Flammability Rating	External Length / Height (m)	Reel Length (m)	Part Number								
Irradiated polyolefin	Black	20	1.6	0.8	VW-1	150	150	SP16/RL/BLACK								
			3.2	1.6				SP32/RL/BLACK								
			4.8	2.4				SP48/RL/BLACK								
			6.4	3.2		75	75	SP64/RL/BLACK								
			9.5	4.7				SP95/RL/BLACK								
			12.7	6.3				SP127/RL/BLACK								
			19	9.5		60	60	SP190/RL/BLACK								
Polyolefin			Black	20		1.6	0.8	VW-1	1.2	-	SP16/1.2/BLACK					
						2.4	1.2				SP24/1.2/BLACK					
						3.2	1.6				SP32/1.2/BLACK					
4.8						2.4	SP48/1.2BLACK									
Irradiated polyolefin						Black	20				6.4	3.2	VW-1	1.2	-	SP64/1.2BLACK
											9.5	4.7				SP95/1.2/BLACK
											12.7	6.3				SP127/1.2/BLACK
	19	9.5			SP190/1.2/BLACK											
	38.1	19			SP381/1.2/BLACK											
	50.8	25.4			SP508/1.2/BLACK											
	9.5	4.7			5						-	SP95/5/BLACK				
	12.7	6.3										SP127/5/BLACK				

Dimensions : Millimetres (Unless Specified)

Specification Table

Material	Colour	Dielectric Strength (kV/mm)	Unshrunk Diameter	Fully Shrunk Diameter	Flammability Rating	External Length / Height (m)	Reel Length (m)	Part Number			
Irradiated polyolefin	Black	20	25.4	12.7	VW-1	5	-	SP254/5/BLACK			
Polyolefin	Clear		2.4	1.2	-	1.2		SP24/1.2/CLEAR			
Irradiated polyolefin			6.4	3.2				SP64/1.2/CLEAR			
Polyolefin			19	9.5				SP190/1.2/CLEAR			
Irradiated polyolefin			6.4	3.2				5	SP64/5/CLEAR		
			38.1	19		SP381/5/CLEAR					
			2.4	1.2		150		SP24/RL/CLEAR			
			3.2	1.6				SP32/RL/CLEAR			
			4.8	2.4				SP48/RL/CLEAR			
			Irradiated polyolefin	9.5		4.7		75	SP95/RL/CLEAR		
				12.7		6.3			SP127/RL/CLEAR		
				19		9.5		60	60	SP190/RL/CLEAR	
				38.1		19		30	30	SP381/RL/CLEAR	
			Polyolefin	Yellow		1.6		0.8	VW-1	1.2	-
2.4						1.2		SP24/1.2/YELLOW			
3.2						1.6		SP32/1.2/YELLOW			
4.8						2.4		SP48/1.2/YELLOW			
6.4						3.2		SP64/1.2/YELLOW			
9.5						4.7		SP95/1.2/YELLOW			
12.7	6.3				SP127/1.2/YELLOW						
19	9.5	SP190/1.2/YELLOW									
25.4	12.7	SP254/1.2/YELLOW									
38.1	19	SP381/1.2/YELLOW									
Polyolefin	50.8	25.4	SP508/1.2/YELLOW								
Irradiated polyolefin	1.6	0.8	5	SP16/5/YELLOW							

Dimensions : Millimetres (Unless Specified)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.