



## Main

|                           |  |
|---------------------------|--|
| Range of product          | Harmony XB4<br>Harmony XB5                   |
| Product or component type | Block for test light                         |
| Product compatibility     | BA 9s<br>Integral LED                        |
| Light block type          | Single block for test light function         |
| [Us] rated supply voltage | 12 V AC/DC<br>24...120 V AC/DC<br>24 V AC/DC |
| Electrical connection     | 1 wire                                       |

## Complementary

|                |         |
|----------------|---------|
| Product weight | 0.01 kg |
|----------------|---------|


## Environment

|  |   |
|--|---|
| Ambient air temperature for storage        | -40...70 °C   |
| Ambient air temperature for operation      | -25...70 °C   |
| Class of protection against electric shock | Class I for Harmony XB4 conforming to IEC 60536<br>Class II for Harmony XB5 conforming to IEC 60536   |
| Standards                                  | CSA C22-2 No 14<br>EN 60947-1<br>EN 60947-5-1<br>EN 60947-5-4<br>EN 60947-5-5<br>IEC 60947-1<br>IEC 60947-5-1<br>IEC 60947-5-4<br>IEC 60947-5-5<br>JIS C 4520<br>UL 508 |
| Product certifications                     | BV<br>CSA<br>DNV (Det Norske Veritas)<br>GL<br>LROS (Lloyds register of shipping)<br>RINA<br>UL listed  |
| Vibration resistance                       | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6   |
| Shock resistance                           | 30 gn for 18 ms conforming to IEC 60068-2-27<br>50 gn for 11 ms conforming to IEC 60068-2-27  |
| RoHS EUR conformity date                   | 0727  |
| RoHS EUR status                            | Compliant   |

## Blocks for “Test Light” Function

### Connections

#### ZBZ G156



#### ZBZ M156

