

Agilent U1610A/U1620A Handheld Digital Oscilloscope

Data Sheet



Features

- 5.7-inch VGA TFT LCD display with 3 selectable viewing modes (indoor, outdoor and night vision)
- 2 Mpts memory depth and 2 GSa/s sampling rate allows detailed analysis of captured glitches
- 100/200 MHz bandwidth with two isolated channels
- 10,000-count resolution on DMM display
- Channel-to-channel isolation with CAT III 600 V safety ratings
- Data logging capability to PC

Retool your expectations in the world's first handheld scope with three viewing modes on a VGA TFT LCD display

Agilent's U1610A/U1620A oscilloscope takes troubleshooting and maintenance task to a whole new level by being the world's first handheld scope with three viewing modes on a VGA TFT LCD display. Whether you're working in a poorly lit environment, or under the glaring sun, the revolutionary display ensures that you can analyze waveforms effortlessly under all lighting conditions by 3 selectable viewing modes (indoor, outdoor and night vision mode). Coupled with 2 Mpts memory depth, it enables you to capture long, non-repeating signals with excellent zooming capabilities onto selective glitches. Further complementing your viewing experience is the 5.7 inch screen that allows signal overviews to be analyzed on a wider viewing area.



Agilent Technologies

5.7-inch VGA display with 3 selectable viewing modes

Visualizing electrical waveforms has never been in such clarity. Our U1610A/U1620A oscilloscope comes with a 5.7-inch VGA TFT LCD display that enables clear viewing of measurements on-site and on the field. With the option of up to three viewing modes, users can now view waveforms under all lighting conditions, including in indoor, outdoor or dark environments. All three viewing modes have predefined contrast levels for customized lighting conditions and optimized battery life.

Indoor mode

The indoor mode has high contrast and brightness levels to clearly distinguish waveforms under an indoor light environment. Engineered with a VGA TFT LCD screen, users can now view the display across wide viewing angles for more efficient troubleshooting task.



Figure 1. Indoor mode for clear distinct readings

Outdoor mode

When performing field work in an outdoor environment, users can easily switch to this viewing mode via a set of accessible soft keys. This mode works in an anti-glare mechanism; it filters out excessive sunlight, hence reducing the risk of misreading or misinterpreting measurements.



Figure 2. Outdoor mode that is sunlight viewable

Night vision mode

The night vision mode is tailored to be viewable under subdued lighting by enabling high contrast levels between the screen background and waveforms. With a single press of button, this mode is activated and the screen automatically adjusts with proper colour correction-creating clear contrasts between the waveforms against the dark environment. This mode is useful when measuring high speed signals, particularly in non-repetitive signals.




Figure 3. Night vision mode for performing tasks in a poorly lit environment

2 Mpts memory depth and 2 GSa/s sampling rate allows detailed analysis of captured glitches

A good oscilloscope must be accompanied with even better specifications for an in-depth analysis of captured glitches. With deep memory of 2 Mpts and sampling rate of 2 GSa/s, non-repeating signals can be captured over a wider time base. What's more, its dual window zoom feature allows you to work more productively by simultaneously viewing signals captured over a period of time and zooming into the most subtle details.

Channel-to-channel isolation with CAT III 600 V safety ratings

The U1610/U1620A extends the maximum input rating to cater for high voltage measurement and transient voltages which are recordable via a handheld oscilloscope. Equipped with the most robust isolation topology, technicians can now measure signals in the field and perform floating measurements. This type of isolation enables each channel to be individually isolated from one another and from other non-isolated system components.

Front panel description



Figure 4. The U1620A as shown

Specifications

| | U1610A | U1620A |
|---|--|---|
| Specification | | |
| Vertical system | | |
| Bandwidth (-3 dB) ¹ | 100 MHz | 200 MHz |
| DC vertical gain accuracy ¹ | ± 4% of full scale | |
| | Full scale is equivalent to 8 div | |
| Dual cursor accuracy ¹ | ± {DC vertical gain accuracy + 0.4% full scale (~1 least significant bit (LSB))} | |
| | ± {4% full scale ± 0.4% full scale (~1 LSB)} | |
| Characteristic | | |
| Acquisition | | |
| Maximum sample rate | 1 GSa/s interleaved, 500 MSa/s per channel | 2 GSa/s interleaved, 1 GSa/s per channel |
| Maximum waveform memory depth | 120 Kpts/channel (interleave), 60 Kpts/channel (non-interleave) | 2 Mpts/channel (interleave), 1 Mpts/channel (non-interleave) |
| Vertical resolution | 8 bits | |
| Peak detection | > 10 ns | > 5 ns |
| Average | Selectable from 2 to 8192 in powers-of-2 increments | |
| Filter | 10 kHz and 20 MHz bandwidth limiters | |
| Interpolation | (Sin x)/x | |
| Vertical system | | |
| Analog channels | Channel 1 and Channel 2 simultaneous acquisition | |
| Calculated rise time | 3.50 ns typical | 1.75 ns typical |
| Vertical scale | 2 mV/div to 50 V/div | |
| Maximum input | CAT III 600 V (with 10:1 probe) | |
| | CAT III 300 V (direct) | |
| Offset (position) range | ± 4 div | |
| Dynamic range | ± 8 div | |
| Input impedance | 1 MΩ ± 1% ≈ 22 pF ± 3 Pf | |
| Coupling | DC, AC | |
| Bandwidth limit | 10 kHz and 20 MHz (selectable) | |
| Channel-to-channel isolation (with channels at the same V/div) | CAT III 600 V | |
| Probes | U1560-60002 1:1 passive probe | |
| | U1561-60002 10:1 passive probe | |
| | U1562-60002 100:1 passive probe | |
| Probe attenuation factors | 1x, 10x, 100x | |
| Probe compensation output | 5 V _{pp} , 1 kHz | |
| Noise peak-to-peak (typical) | 3% of full scale or 5 mV _{pp} , whichever greater | |
| DC vertical offset (position) accuracy | ± 0.1 div ± 2 mV ± 1.6% offset value | |
| Single cursor accuracy | ± {DC vertical gain accuracy + DC vertical offset accuracy + 0.2% full scale (~½ least significant bit (LSB))} | |
| | ± {4% full scale ± 0.1 div ± 2 mV ± 1.6% offset value + 0.2% full scale (~½ LSB)} | |

Specifications (continued)

| | U1610A | U1620A |
|-----------------------------------|---|---|
| Characteristic (continued) | | |
| Horizontal system | | |
| Range | 5 ns/div to 50 s/div | 2 ns/div to 50 s/div |
| Resolution | 100 ps for 5 ns/div | 40 ps for 2 ns/div |
| Timebase accuracy | 25 ppm | |
| Reference position | Left, center, right | |
| Delay range (pre-trigger) | 1 screen width or 120 μ s (whichever less) | 1 screen width or 1 ms (whichever less) |
| Delay range (post-trigger) | 50 ms to 500 s | 20 ms to 500 s |
| Delay resolution | 100 ps for 5 ns/div | 40 ps for 2 ns/div |
| Delay time measurement accuracy | Same channel: $\pm 0.0025\%$ reading $\pm 0.17\%$ screen width ± 60 ps Channel-to-channel: $\pm 0.0025\%$ reading $\pm 0.17\%$ screen width ± 120 ps | |
| Modes | Main, zoom, XY, roll | |
| Horizontal pan and zoom | Dual window zoom | |
| Trigger system | | |
| Sources | Channel 1, Channel 2, External | |
| Modes | Normal, Single, Auto | |
| Types | Edge, Glitch, TV, Nth Edge, CAN, LIN | |
| Autoscale | Finds or displays active channels, sets the edge trigger type on the highest numbered channel, and sets the vertical sensitivity on the scope channel timebase to display ~2 periods Requires > 10 mV _{pp} minimum voltage, 0.5% duty cycle, and > 50 Hz minimum frequency | |
| Holdoff time | 60 ns to 10 s | |
| Range | ± 6 div from center of screen | |
| Sensitivity | ≥ 10 mV/div: 0.5 div < 10 mV/div: greater of 1 div or 5 mV | |
| Trigger level accuracy | ± 0.6 div | |
| Coupling modes | AC (~10 Hz), DC, LF-Reject (~35 kHz), HF-Reject (~35 kHz) | |
| External trigger | | |
| • Input impedance | 1 M Ω \approx 10 pF | |
| • Maximum input | CAT III 300 V | |
| • Range | DC coupling: trigger level ± 5 V | |
| • Bandwidth | 100 kHz | |
| Measurement | | |
| Automatic measurements | Delay, duty cycle (+/-), fall/rise time, frequency, period, phase shift, T-max, T-min, width (+/-), amplitude, average, base, crest, cycle mean, maximum, minimum, overshoot, peak-to-peak, preshoot, standard deviation, top, Vrms (AC/DC), active/apparent/reactive power, power factor | |
| Waveform math functions | CH1 + CH2, CH1 - CH2, CH2 - CH1, CH1 \times CH2, CH1/CH2, CH2/CH1, d/dt (CH1), d/dt (CH2), \int (CH1)dt, \int (CH2)dt, FFT | |
| Cursors | Delta V: Voltage difference between cursors Delta T: Time difference between cursors | |
| FFT points | 1024 | |
| FFT windows | Rectangular, Hamming, Hanning, Blackman-Harris, Flattop | |

Specifications (continued)

| | U1610A | U1620A |
|------------------------------------|---|--------|
| Characteristic (continued) | | |
| Display system | | |
| Display | 5.7" TFT LCD VGA Color (outdoor readable) | |
| Resolution | VGA (screen area): 640 vertical by 480 horizontal | |
| Control | Vectors on/off, sin x/x interpolation on/off, infinite persistence on/off, backlight intensity, color scheme, clear display | |
| Real-time clock | Date and time (adjustable) | |
| Language | 10 languages (selectable) | |
| Built-in help system | Functional quick help displayed by pressing the [Help] button | |
| Storage system | | |
| Save/recall (non-volatile) | 10 setups and waveforms can be saved and recalled internally | |
| Storage mode | USB 2.0 full speed host port | |
| | Image formats: .bmp (8-bit, 24-bit) and .png (24-bit) | |
| | Data format: .csv | |
| I/O | USB 2.0 full-speed host, USB 2.0 full-speed client | |
| Printer compatibility ² | PCL Inkjet, PCL Laser | |

1. Denotes warranted specifications, all others are typical. Specifications are valid after a 30-minute warm-up period and within 23 ± 10 °C of last calibration temperature.

2. For a list of compatible printers, visit www.agilent.com/find/handheldscope-printers.

Digital multimeter specifications

- Accuracy is given as \pm (% of reading + counts of least significant digit) at $23\text{ }^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$, with relative humidity $< 80\text{ RH}$.
- AC V specifications are AC coupled, true RMS and are valid from 5% to 100% of range.

| Maximum reading | | | | | |
|--|--------------------------------|---|-----------------------------|---------------------------|--------------------|
| 10,000 counts with automatic polarity indication | | | | | |
| Voltage | | | | | |
| CAT II 1000 V or CAT III 600 V | | | | | |
| Function | Range | Resolution | Accuracy | Input impedance (nominal) | Test current |
| DCV | 1000.0 mV | 0.1 mV | 0.09% + 5 | 11.11 M Ω | |
| | 10.000 V | 0.001 V | 0.09% + 2 | 10.10 M Ω | |
| | 100.00 V | 0.01 V | | 10.01 M Ω | |
| | 1000.0 V ² | 0.1 V | 0.15% + 5 | | |
| ACV | 1000.0 mV | 0.1 mV | 1% + 5 (40 to 500 Hz) | 10.00 M Ω | |
| | | | 2% + 5 (500 Hz to 1 kHz) | | |
| | 10.000 V 100.00 V | 0.001 V 0.01V | 1% + 5 (40 to 500 Hz) | | |
| | | | 1% + 5 (500 Hz to 1 kHz) | | |
| | 1000.0 V ² | 0.1 V | 2% + 5 (1 to 2 kHz) | | |
| | | | 1% + 5 (40 to 500 Hz) | | |
| | | 1% + 5 (500 Hz to 1 kHz) | | | |
| ACV + DCV | 1000.0 mV | 0.1 mV | 1.1% + 10 (40 to 500 Hz) | 10.00 M Ω | |
| | | | 2.1% + 10 (500 Hz to 1 kHz) | | |
| | 10.000 V 100.00 V | 0.001 V 0.01 V | 1.1% + 7 (40 to 500 Hz) | | |
| | | | 1.1% + 7 (500 Hz to 1 kHz) | | |
| | 1000.00 V ² | 0.1 V | 2% + 5 (1 to 2 kHz) | | |
| | | | 1.2% + 10 (40 to 500 Hz) | | |
| | | 1.2% + 10 (500 Hz to 1 kHz) | | | |
| Diode ³ | 1 V | 0.001 V | 0.3% + 2 | | ~0.5 mA |
| | | | | | |
| Instant continuity ³ | | Continuous beep when resistance $< 10\ \Omega$ ⁸ | | | |
| Resistance | 1000.00 Ω ⁴ | 0.1 Ω | 0.3% + 3 | | 0.5 mA |
| | 10.000 k Ω ⁴ | 0.001 k Ω | | | 50 μA |
| | 100.00 k Ω | 0.01 k Ω | | | 4.91 μA |
| | 1000.0 k Ω | 0.1 k Ω | | | 447 nA |
| | 10.000 M Ω | 0.001 M Ω | | | 112 nA |
| | 100.00 M Ω ⁵ | 0.01 M Ω | | | 112 nA |
| Capacitance | 1000.0 nF | 0.1 nF | 1.2% + 4 ⁶ | | |
| | 10.000 μF | 0.001 μF | | | |
| | 100.00 μF | 0.01 μF | | | |
| | 1000.0 μF | 0.1 μF | | | |
| | 10.000 mF | 0.001 mF | 2% + 4 ⁶ | | |

Digital multimeter specifications (continued)

| Maximum reading | | 10,000 counts with automatic polarity indication | | | |
|--------------------------|----------------|--|----------------|-----------------------------|--------------|
| Voltage | | CAT II 1000 V or CAT III 600 V | | | |
| Function | Range | Resolution | Accuracy | Input impedance (nominal) | Test current |
| Temperature ³ | -50 to 1000 °C | 1 mV/°C | -50 to -21 °C | 2.5% + 2 °C ⁷ | |
| | | | -20 to 350 °C | 0.5% + 2 °C ⁷ | |
| | | | 351 to 500 °C | 1.75% + 2 °C ⁷ | |
| | | | 501 to 1000 °C | 2% + 2 °C ⁷ | |
| | -58 to 1832 °F | 1 mV/°F | -58 to -5.8 °F | 2.5% + 3.6 °F ⁷ | |
| | | | -4 to 662 °F | 0.5% + 3.6 °F ⁷ | |
| | | | 664 to 932 °F | 1.75% + 3.6 °F ⁷ | |
| | | | 933 to 1832 °F | 2% + 3.6 °F ⁷ | |
| Frequency ³ | 100.00 Hz | 0.01 Hz | 0.03% + 3 | | |
| | 1000.0 Hz | 0.1 Hz | | | |
| | 10.000 kHz | 0.001 kHz | | | |
| | 100.00 kHz | 0.01 kHz | | | |
| | 1000.0 kHz | 0.1 kHz | | | |

1. Only allowed to measure up to CAT III 600 V if referring to GND.
2. Only allowed for floating voltage.
3. Denotes typical specifications, all others are warranted.
4. The accuracy is specified after the Null function is used to subtract the test lead resistance and thermal effect.
5. RH is specified for < 60%. The temperature coefficient is 0.15 × specified accuracy as > 50 MΩ.
6. The accuracy is based on film capacitors or better and uses the Relative mode for residual values.
7. The accuracy is based on using the Null function to reduce the thermal effect.
8. Denotes characteristics.

General specifications

| Power supply | |
|------------------------|--|
| Power adapter | Line voltage range: 50/60 Hz, 100 to 240 VAC, 1.6 A Output voltage: 15 VDC, 4 A Installation Category II |
| Battery | Li-Ion rechargeable battery pack, 10.8 V Operating time: Up to 3 hours |
| Operating environment | |
| Temperature | 0 to 50 °C (with battery only) 0 to 40 °C (with power adapter) |
| Humidity | 0 to 80% RH (0 to 35 °C) 0 to 50% RH (35 to 40/50 °C) Altitude up to 2000 m Pollution degree 2 |
| Storage compliance | |
| Temperature | -20 to 70 °C |
| Humidity | 0 to 80% RH Altitude up to 15000 m |
| Shock | Tested to IEC 60068-2-27 |
| Vibration | Tested to IEC 60068-2-6, IEC 60068-2-64 |
| Safety compliance | IEC 61010-1:2001/EN 61010-1:2001 Canada: CAN/CSA-C22.2 No. 61010-1-04 USA: ANSI/UL 61010-1:2004 |
| EMC compliance | IEC 61326-1:2005/EN 61326-1:2006 Australia/New Zealand: AS/NZS CISPR 11:2004 Canada: ICES/NMB-001:ISSUE 4, June 2006 |
| IP rating | IP 41 ingress protection according to IEC 60529 |
| Dimensions (W × H × D) | 183 x 270 x 65 mm |
| Weight | < 2.5 kg |
| Warranty | 3 years for main unit 3 months for standard shipped accessories unless otherwise stated |

Ordering information

Standard shipped items

- Quick start guide, power adapter, Li-Ion battery pack, USB cable, test lead, 10:1 probe (2 sets).

Recommended accessories

| Item | Description |
|---|--|
| U1560B Scope probe x1 CAT III 300 V  | <ul style="list-style-type: none">• Include ground alligator clip and hook clip, rated CAT III 300 V |
| U1562B Scope probe x100 CAT III 600 V  | <ul style="list-style-type: none">• Include ground alligator clip and hook clip, rated CAT III 600 V |
| U1572A Li Polymer battery pack  | <ul style="list-style-type: none">• 4,800 mAh, 10.8• Compatible with U1610A/20A handheld oscilloscope |
| U1573A Desktop charger & Li Polymer battery pack  | <ul style="list-style-type: none">• 4,800 mAh, 10.8 V• Compatible with U1610A/20A handheld oscilloscope |
| U1575A Desktop charger  | <ul style="list-style-type: none">• 2-output 3 A battery charger• Dimensions: 6.89 x 4.89 x 2.30 inches |
| U1591A Soft carrying case  | <ul style="list-style-type: none">• Soft carrying case with backpack and shoulder strap |



Agilent Email Updates

www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.



www.axistandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Agilent is a founding member of the AXIe consortium.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Agilent is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.



Agilent Advantage Services is committed to your success throughout your equipment's lifetime. To keep you competitive, we continually invest in tools and processes that speed up calibration and repair and reduce your cost of ownership. You can also use Infoline Web Services to manage equipment and services more effectively. By sharing our measurement and service expertise, we help you create the products that change our world.

www.agilent.com/find/advantageservices



www.agilent.com

www.agilent.com/find/handheldscope

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

| | |
|---------------|----------------|
| Canada | (877) 894 4414 |
| Brazil | (11) 4197 3500 |
| Mexico | 01800 5064 800 |
| United States | (800) 829 4444 |

Asia Pacific

| | |
|--------------------|----------------|
| Australia | 1 800 629 485 |
| China | 800 810 0189 |
| Hong Kong | 800 938 693 |
| India | 1 800 112 929 |
| Japan | 0120 (421) 345 |
| Korea | 080 769 0800 |
| Malaysia | 1 800 888 848 |
| Singapore | 1 800 375 8100 |
| Taiwan | 0800 047 866 |
| Other AP Countries | (65) 375 8100 |

Europe & Middle East

| | |
|----------------|----------------------|
| Belgium | 32 (0) 2 404 93 40 |
| Denmark | 45 70 13 15 15 |
| Finland | 358 (0) 10 855 2100 |
| France | 0825 010 700* |
| | *0.125 €/minute |
| Germany | 49 (0) 7031 464 6333 |
| Ireland | 1890 924 204 |
| Israel | 972-3-9288-504/544 |
| Italy | 39 02 92 60 8484 |
| Netherlands | 31 (0) 20 547 2111 |
| Spain | 34 (91) 631 3300 |
| Sweden | 0200-88 22 55 |
| United Kingdom | 44 (0) 131 452 0200 |

For other unlisted countries:

www.agilent.com/find/contactus

Revised: June 8, 2011

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2011
Published in USA, December 5, 2011
5990-9523EN



Agilent Technologies