



# 5 POLE



WIDOK OD STRONY DRUTOW  
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	TERMINAL	-
2	TERMINAL	-
3	NIEBIESKI	BU
4	BRAZOWY	BN
5	ZIELONO/ZOLTY	GN/YE

## PART No MATRIX



## OPTIONS

Coupling Nut Material  
 Blank-Standard  
 1-Stainless Steel  
 5-Delrin

WIDOK OD STRONY CZOLA  
FRONT SIDE VIEW





Table of lenght tolerances/ Tablica tolerancji dlugosci mm		
Over/Od	Up to and including/ Do-wlacznie	Tolerance/Tolerancja +/-
100	1000	±20
1000	3000	±30
3000	5000	±40
5000	10000	±50
10000	15000	±100
15000	20000	±150
	>20000	L/100

UWAGI:

- DLUGOSCI CIECIA I SPECYFIKACJE NABIJANIA WG LISTY CIECIA.
- PRODUKOWAC ZGODNIE Z INSTRUKCJAMI: VVK1\_392\_zal4, VVK1\_392\_zal2.

NOTES:

- CUTTING LENGHT AND CRIMPING SPECIFICATION IN CUTTING LIST.
- USE INSTRUCTION No : VVK1\_392\_zal4, VVK1\_392\_zal2.

PINS 1&2 replaced EC NO: DRWIN:MEVYTSKY2009/10/01 CHKD: APPR:	DESCRIPTION REV: A1	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH	DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION
		4 PLACES ± ± 3 PLACES ± ± 2 PLACES ± ± 1 PLACE ± ±	DRAWN BY DATE MWOLSZCZAK 2008/10/30 CHECKED BY DATE	TITLE DIN/MMC-5P-24V -MM-ST-XXM			
		ANGULAR ± °	APPROVED BY DATE MDABROWSKA 2008/10/30	MOLEX INCORPORATED			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO. SEE PN KEY	DOCUMENT NO. E850B0XXXMXXX	SHEET NO. 1 OF 1		