


PCI-1711U/UL

Entry-level 100 kS/s, 12-bit, 16-ch
Universal PCI Multifunction Card



RoHS
COMPLIANT
2002/95/EC

FCC CE

Features

- 16-ch single-ended analog input
- 12-bit A/D converter, with up to 100 kHz sampling rate
- Programmable gain
- Automatic channel/gain scanning
- Onboard FIFO memory (1,024 samples)
- Two 12-bit analog output channels (PCI-1711U only)
- 16-ch digital input and 16-ch digital output
- Onboard programmable counter

Specifications

Analog Input

- **Channels** 16 single-ended
- **Resolution** 12 bits
- **Max. Sampling Rate** 100 kS/s
- **FIFO Size** 1,024 samples
- **Overvoltage Protection** 30 Vp-p
- **Input Impedance** 300 M Ω /5 pF
- **Sampling Modes** Software, onboard programmable pacer, or external
- **Input Range** (V, software programmable)

Bipolar	± 10	± 5	± 2.5	± 1.25	± 0.625
Accuracy (% of FSR ± 1 LSB)	0.1	0.1	0.2	0.2	0.4

Analog Output (PCI-1711U only)

- **Channels** 2
- **Resolution** 12 bits
- **Output Rate** Static update
- **Output Range** (V, software programmable)

Internal Reference	Unipolar	0 ~ +5V @ -5V 0 ~ +10V @ -10V
External Reference		0 ~ +x V @ -x V (-10 \leq x \leq 10)

- **Slew Rate** 10 V/ μ s
- **Driving Capability** 3 mA
- **Output Impedance** 6.8 Ω max
- **Operation Mode** Software polling
- **Accuracy** INLE: ± 0.5 LSB
DNLE: ± 0.5 LSB

Digital Input

- **Channels** 16
- **Compatibility** 5 V/TTL
- **Input Voltage** Logic 0: 0.8 V max.
Logic 1: 2.0 V min.

Digital Output

- **Channels** 16
- **Compatibility** 5 V/TTL
- **Output Voltage** Logic 0: 0.8 V
Logic 1: 2.0 V
- **Output Capability** Sink: 8.0 mA @ 0.8 V
Source: -0.4 mA @ 2.0 V

Pacer/Counter

- **Channels** 1
- **Resolution** 16 bits
- **Compatibility** 5 V/TTL
- **Max. Input Frequency** 10 MHz
- **Reference Clock** Internal: 10 MHz

General

- **Bus Type** Universal PCI V2.2
- **I/O Connector** 1 x 68-pin SCSI female connector
- **Dimensions (L x H)** 175 x 100 mm (6.9" x 3.9")
- **Power Consumption**
PCI-1711U Typical: 5 V @ 850 mA
Max.: 5 V @ 1.0 A
PCI-1711UL Typical: 5 V @ 700 mA
Max.: 5 V @ 1.0 A
- **Operating Temperature** 0 ~ 60° C (32 ~ 140° F) (refer to IEC 68-2-1, 2)
- **Storage Temperature** -20 ~ 70° C (-4 ~ 158° F)
- **Storage Humidity** 5 ~ 95% RH non-condensing (refer to IEC 68-2-3)

Ordering Information

- **PCI-1711U** Entry-level 100 kS/s, 12-bit Multifunction Card
- **PCI-1711UL** Entry-level 100 kS/s, 12-bit Multi. Card w/o AO

Accessories

- **PCLD-8710** DIN-rail Wiring Board w/ CJC
- **PCL-10168-1** 68-pin SCSI Shielded Cable, 1 m
- **PCL-10168-2** 68-pin SCSI Shielded Cable, 2 m
- **ADAM-3968** 68-pin DIN-rail SCSI Wiring Board