

## Raychem Brand S1006 adhesive, part A (all kits)

### 1. Identification of the substance/preparation and of the company/undertaking

#### 1.1 Identification of the substance or preparation:

Product name: Raychem Brand S1006 adhesive, part A (all kits)

#### 1.2 Use of the substance/preparation:

Adhesive

#### 1.3 Company/undertaking identification:

TYCO Electronics UK Ltd  
Faraday Road, Dorcan  
SN3 5HH Swindon, United Kingdom  
Tel: +44 1793 52 81 71  
Fax: +44 1793 57 25 16  
REACH-ADM@te.com

#### 1.4 Emergency telephone:

24h/24h:  
+32 14 58 45 45 (BIG)

### 2. Hazards identification

#### DSD/DPD

Classified dangerous in accordance with the criteria of Directives 67/548/EEC and 1999/45/EC  
Irritating to eyes and skin  
May cause sensitisation by skin contact  
Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment

#### Other hazards

Not readily biodegradable in water

### 3. Composition/information on ingredients

Name	CAS No EINECS/ELINCS	Conc.	Classification according to DSD/ DPD	Classification according to CLP	Note
reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)	25068-38-6 500-033-5	50<C<100	Xi; R36/38 R43 N; R51-53	Eye Irrit. 2; H319 Skin Irrit. 2; H315 Skin Sens. 1; H317 Aquatic Chronic 2; H411	(1)(2)

(1) For R-phrases and H-statements in full: see heading 16  
(2) Substance with a Community workplace exposure limit

### 4. First aid measures

#### 4.1 After inhalation:

Remove the victim into fresh air  
Respiratory problems: consult a doctor/medical service

#### 4.2 Skin contact:

Wash immediately with lots of water  
Soap may be used  
Take victim to a doctor if irritation persists

#### 4.3 Eye contact:

Rinse immediately with plenty of water  
Take victim to an ophthalmologist if irritation persists

#### 4.4 After ingestion:

Created by: Brandweerinformatiecentrum voor Gevaarlijke Stoffen vzw (BIG)  
Technische Schoolstraat 43 A, B-2440 Geel  
<http://www.big.be>  
Reason for revision: REACH  
Revision number: 0400

Edition date: 1999-07-26  
Date of revision: 2011-03-21

Product number: 28649

Reference number: 3002AE

1 / 8

# Raychem Brand S1006 adhesive, part A (all kits)

Rinse mouth with water  
Immediately after ingestion: give lots of water to drink  
Do not induce vomiting  
Consult a doctor/medical service if you feel unwell

## 5. Fire-fighting measures

### 5.1 Suitable extinguishing media:

Water spray  
Polyvalent foam  
BC powder  
Carbon dioxide

### 5.2 Unsuitable extinguishing media:

Solid water jet ineffective as extinguishing medium

### 5.3 Special exposure hazards:

On burning: release of toxic and corrosive gases/vapours (hydrogen chloride, carbon monoxide - carbon dioxide)

### 5.4 Instructions:

Dilute toxic gases with water spray  
Take account of environmentally hazardous firefighting water  
Use water moderately and if possible collect or contain it

### 5.5 Special protective equipment for fire-fighters:

Gloves  
Face-shield  
Protective clothing  
Heat/fire exposure: compressed air/oxygen apparatus

## 6. Accidental release measures

### 6.1 Personal precautions:

See heading 8.2

### 6.2 Environmental precautions:

Contain released substance, pump into suitable containers  
Dam up the liquid spill  
Prevent soil and water pollution  
Prevent spreading in sewers  
See heading 13

### 6.3 Methods for cleaning up:

Take up liquid spill into inert absorbent material  
Scoop absorbed substance into closing containers  
Carefully collect the spill/leftovers  
Clean contaminated surfaces with a soap solution  
Wash clothing and equipment after handling

## 7. Handling and storage

### 7.1 Handling:

Keep away from ignition sources/sparks  
Observe very strict hygiene - avoid contact  
Avoid contact with skin and eyes  
Avoid inhaling vapours/fumes which may be released during use  
Avoid inhaling dust when grinding/sanding/cutting cured material  
Keep container tightly closed  
Do not discharge the waste into the drain

### 7.2 Storage:

#### Safe storage requirements:

Store in a cool area  
Store in a dry area  
Keep container in a well-ventilated place

# Raychem Brand S1006 adhesive, part A (all kits)

Meet the legal requirements

Storage temperature: 23 °C

Max. storage time: See packaging

**Keep away from:**

oxidizing agents

(strong) acids

(strong) bases

## 7.3 Specific use(s):

See information supplied by the manufacturer for the identified use(s)

Refer to TE Connectivity product installation instructions

The curing process is exothermic (releases heat)

## 8. Exposure controls/Personal protection

### 8.1 Exposure limit values:

8.1.1 Occupational exposure:

If limit values are applicable and available these will be listed below.

8.1.2 Sampling methods:

Product name	Test	Number	Sampling method	Remark
No data available				

### 8.2 Exposure controls:

8.2.1 Occupational exposure controls:

Carry operations in the open/under local exhaust/ventilation or with respiratory protection

Curing ovens must be exhausted to outdoors or to suitable emission control device

Use local exhaust ventilation when grinding/sanding/cutting cured material

Personal protective equipment:

a) Respiratory protection:

Wear gas mask with filter type A if conc. in air > exposure limit

b) Hand protection:

Gloves

- butyl rubber

- nitrile rubber

- neoprene

c) Eye protection:

Safety glasses

Use personal protective equipment as required by the risk assessment

d) Skin protection:

Protective clothing

8.2.2 Environmental exposure controls:

See headings 6.2, 6.3 and 13

## 9. Physical and chemical properties

### 9.1 General information:

Physical form	Liquid
Odour	Mild odour
Colour	Light yellow

### 9.2 Important health, safety and environmental information:

Boiling point	> 200 °C
Flashpoint	> 200 °C
Vapour pressure (20°C)	< 0.0004 hPa
Relative density	1.17
Log Pow	> 3

### 9.3 Other information:

Auto-ignition temperature	> 400 °C
---------------------------	----------

## 10. Stability and reactivity

### 10.1 Conditions to avoid:

# Raychem Brand S1006 adhesive, part A (all kits)

## Possible fire hazard

heat sources

## Stability

Stable under normal conditions

## Reactions

Reacts exothermically with many compounds e.g.: with (strong) oxidizers and with (some) acids/bases

## 10.2 Materials to avoid:

oxidizing agents  
(strong) acids  
(strong) bases

## 10.3 Hazardous decomposition products:

On burning: release of toxic and corrosive gases/vapours (hydrogen chloride, carbon monoxide - carbon dioxide)

## 11. Toxicological information

### 11.1 Acute toxicity:

Raychem Brand S1006 adhesive, part A (all kits)

LD50 oral (rat)	> 5000 mg/kg
-----------------	--------------

### 11.2 Chronic toxicity:

Not listed in carcinogenicity class (IARC,EC,TLV,MAK)  
Not listed in mutagenicity class (EC,MAK)  
Not classified as toxic to reproduction (EC)

### 11.3 Acute effects/symptoms:

#### Inhalation:

Not a normal route of exposure  
Vapours evolved during heat curing processes, and dust formed when grinding/sanding/cutting cured material, can cause:  
Respiratory difficulties  
Irritation of the respiratory tract  
Dry/sore throat  
Irritation of the nasal mucous membranes

#### Skin contact:

Tingling/irritation of the skin

#### Eye contact:

Irritation of the eye tissue  
Lacrimation  
Visual disturbances

#### Ingestion:

No data available

### 11.4 Chronic effects:

ON CONTINUOUS/REPEATED EXPOSURE/CONTACT:  
Skin rash/inflammation

## 12. Ecological information

### 12.1 Ecotoxicity:

reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)

LC50 fishes

species	value	duration (h)	remarks
SALMO GAIRDNERI/ ONCORHYNCHUS MYKISS	1.5 - 7.7 mg/l	96 h	

EC50 Daphnia

species	value	duration (h)	remarks
DAPHNIA MAGNA	1.1 - 3.6 mg/l	24 h	

# Raychem Brand S1006 adhesive, part A (all kits)

## EC50 other aquatic organisms

species	value	duration (h)	remarks
CHLOROPHYTA	220 mg/l	96 h	

## Raychem Brand S1006 adhesive, part A (all kits)

## LC50 fishes

species	value	duration (h)	remarks
PISCES	1 - 10 mg/l	96 h	

## EC50 Daphnia

species	value	duration (h)	remarks
DAPHNIA MAGNA	1 - 10 mg/l	48 h	

### 12.2 Mobility:

Solubility in/reaction with water

Literature reports: insoluble in water

Ground water

Ground water pollutant

### 12.3 Persistence and degradability:

Not readily biodegradable in water

### 12.4 Bioaccumulative potential:

Log Pow

> 3

According to literature: bioaccumulative

### 12.5 Results of PBT assessment:

Not applicable, based on available data

### 12.6 Other adverse effects:

Not dangerous for the ozone layer (1999/45/EC)

## 13. Disposal considerations

### 13.1 Provisions relating to waste:

Waste material code (Directive 2008/98/EC, decision 2001/118/EC)

08 04 09\* : waste adhesives and sealants containing organic solvents or other dangerous substances

Depending on branch of industry and production process, also other EURAL codes may be applicable

Hazardous waste according to Directive 2008/98/EC

Not classified as hazardous waste when part A and part B are mixed and are fully cured

### 13.2 Disposal methods:

Remove to an authorized incinerator equipped with an afterburner and a flue gas scrubber with energy recovery

Remove waste in accordance with local and/or national regulations

Do not discharge into drains or the environment

### 13.3 Packaging/Container:

Waste material code packaging (Directive 2008/98/EC)

15 01 10\* : packaging containing residues of or contaminated by dangerous substances

## 14. Transport information

### ADR

Proper shipping name	Environmentally hazardous substance, liquid, n.o.s.
Techn./chem. name ADR	reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)
UN number	3082
Class	9
Packing group	III
Hazard identification number	90
Classification code	M6
Labels	9
Environmentally hazardous substance mark	yes

### RID

# Raychem Brand S1006 adhesive, part A (all kits)

Proper shipping name	Environmentally hazardous substance, liquid, n.o.s.
Techn./chem. name RID	reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)
UN number	3082
Class	9
Packing group	III
Classification code	M6
Labels	9
Environmentally hazardous substance mark	yes

## ADN

Proper shipping name	Environmentally hazardous substance, liquid, n.o.s.
Techn./chem. name ADN	reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)
UN number	3082
Class	9
Packing group	III
Classification code	M6
Labels	9
Environmentally hazardous substance mark	yes

## IMO

Proper shipping name	Environmentally hazardous substance, liquid, n.o.s.
Techn./chem. name IMO	reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)
UN number	3082
Class	9
Packing group	III
Labels	9
Marine pollutant	P
Environmentally hazardous substance mark	yes

## ICAO

Proper shipping name	Environmentally hazardous substance, liquid, n.o.s.
Techn./chem. name ICAO	reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)
UN number	3082
Class	9
Packing group	III
Labels	9
Environmentally hazardous substance mark	yes

## 15. Regulatory information

### 15.1 EU Legislation:

#### DSD/DPD

Classification according to directives 67/548/EEC, 1999/45/EC and 2006/8/EC



Irritant



Dangerous for the environment

Contains: reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <=700)

# Raychem Brand S1006 adhesive, part A (all kits)

## R-phrases

36/38	Irritating to eyes and skin
43	May cause sensitisation by skin contact
51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment

## S-phrases

24	Avoid contact with skin
37	Wear suitable gloves
61	Avoid release to the environment. Refer to special instructions/safety data sheets.

## Additional recommendations

	Contains epoxy constituents. See information supplied by the manufacturer.
--	----------------------------------------------------------------------------

## 15.2 National provisions:

## 15.3 Specific community rules:

REACH Annex XVII - Restriction

Contains component(s) included in Annex XVII of Regulation (EC) No. 1907/2006: restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles

## 16. Other information

The information in this safety data sheet is based on data and samples provided to BIG. The sheet was written to the best of our ability and according to the state of knowledge at that time. The safety data sheet only constitutes a guideline for the safe handling, use, consumption, storage, transport and disposal of the substances/preparations/mixtures mentioned under point 1. New safety data sheets are written from time to time. Only the most recent versions may be used. Old versions must be destroyed. Unless indicated otherwise word for word on the safety data sheet, the information does not apply to substances/preparations/mixtures in purer form, mixed with other substances or in processes. The safety data sheet offers no quality specification for the substances/preparations/mixtures in question.

Compliance with the instructions in this safety data sheet does not release the user from the obligation to take all measures dictated by common sense, regulations and recommendations or which are necessary and/or useful based on the real applicable circumstances. BIG does not guarantee the accuracy or exhaustiveness of the information provided. Use of this safety data sheet is subject to the licence and liability limiting conditions as stated in your BIG licence agreement. All intellectual property rights to this sheet are the property of BIG and its distribution and reproduction are limited. Consult your BIG licence agreement for details.

Users are advised that they may have additional disclosure obligations under other national and local laws. Users are advised to ensure that this information is brought to the attention of all employees, agents, and contractors handling this product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application and to establish safe handling and installation procedures. Distributors of this product are advised to forward this document, or the information contained herein, to every purchaser of this product.

TE Connectivity makes no warranties as to the accuracy or completeness of this information and disclaims any liability in connection with its use. TE Connectivity obligations shall be only as set forth in TE Connectivity standard terms and conditions of sale for this product. In no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of this product.

(\*) = INTERNAL CLASSIFICATION (NFPA)

PBT-substances = persistent, bioaccumulative and toxic substances

DSD Dangerous Substance Directive  
DPD Dangerous Preparation Directive  
CLP (EU-GHS) Classification, labelling and packaging (Globally Harmonised System in Europe)

Full text of any R-phrases referred to under headings 2 and 3:

R36/38	Irritating to eyes and skin
R43	May cause sensitisation by skin contact
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment

Full text of any H-statements referred to under headings 2 and 3:

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H411	Toxic to aquatic life with long lasting effects.

Full text of any classes referred to under headings 2 and 3:

Aquatic Chronic	Hazardous to the aquatic environment - chronic
Eye Irrit.	Eye irritation

# Raychem Brand S1006 adhesive, part A (all kits)

Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitization