


# Non EXAR Packages

Revised: January 14, 2010

Assembly-Packaging Engineering, Melissa Lee



- EXAR qualifies all package types according to the profile listed in JEDEC specification J-STD-020
- Subsequent 3 pages are extracted from JEDEC specification for easy and quick reference regarding important features, example:
  - Detail profile: ramp rate, hold time, cool down rate etc
  - Peak reflow temperature vs. package volume
  - Peak reflow temperature vs. standard solder & Pb-free packages
- Further information can be found in
  - Jedec spec# <u>J-STD-020D.1</u>
  - Jedec spec# J-Std.033B. 1



March 2008




Figure 5-1 Classification Profile (Not to scale)

Assembly-Packaging Engineering, Melissa Lee



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly		
Preheat/Soak Temperature Min (T <sub>smin</sub> ) Temperature Max (T <sub>smax</sub> ) Time (t <sub>s</sub> ) from (T <sub>smin</sub> to T <sub>smax</sub> )	100 °C 150 °C 60-120 seconds	150 °C 200 °C 60-120 seconds		
Ramp-up rate (T <sub>L</sub> to T <sub>p</sub> )	3 °C/second max.	3 °C/second max.		
Liquidous temperature (T <sub>L</sub> ) Time (t <sub>L</sub> ) maintained above T <sub>L</sub>	183 °C 60-150 seconds	217 °C 60-150 seconds		
Peak package body temperature (T <sub>p</sub> )	For users T <sub>p</sub> must not exceed the Classification temp in Table 4-1. For suppliers T <sub>p</sub> must equal or exceed the Classification temp in Table 4-1.	For users T <sub>p</sub> must not exceed the Classification temp in Table 4-2. For suppliers T <sub>p</sub> must equal or exceed the Classification temp in Table 4-2.		
Time (t <sub>p</sub> )* within 5 °C of the specified classification temperature (T <sub>c</sub> ), see Figure 5-1.	20* seconds	30* seconds		
Ramp-down rate (Tp to TL)	6 °C/second max.	6 °C/second max.		
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.		
* Tolerance for peak profile temperature (Tp) is defined as a supplier minimum and a user maximum.				

Table 5-2 Classification Reflow Profiles

Note 1: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow (e.g., live-bug). If parts are reflowed in other than the normal live-bug assembly reflow orientation (i.e., dead-bug), T<sub>p</sub> shall be within ± 2 °C of the live-bug T<sub>p</sub> and still meet the T<sub>c</sub> requirements, otherwise, the profile shall be adjusted to achieve the latter. To accurately measure actual peak package body temperatures refer to JEP140 for recommended thermocouple use.

Note 2: Reflow profiles in this document are for classification/preconditioning and are not meant to specify board assembly profiles. Actual board assembly profiles should be developed based on specific process needs and board designs and should not exceed the parameters in Table 5-2. For example, if T<sub>c</sub> is 260 °C and time t<sub>c</sub> is 30 seconds, this means the following for the supplier and the user.

For a supplier: The peak temperature must be at least 260 °C. The time above 255 °C must be at least 30 seconds.

For a user: The peak temperature must not exceed 260 °C. The time above 255 °C must not exceed 30 seconds.

- Note 3: All components in the test load shall meet the classification profile requirements.
- Note 4: SMD packages classified to a given moisture sensitivity level by using Procedures or Criteria defined within any previous version of J-STD-020, JESD22-A112 (rescinded), IPC-SM-786 (rescinded) do not need to be reclassified to the current revision unless a change in classification level or a higher peak classification temperature is desired.



Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

#### Table 4-2 Pb-Free Process - Classification Temperatures (To)

Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350 - 2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

- Note 1: At the discretion of the device manufacturer, but not the board assembler/user, the maximum peak package body temperature (T<sub>p</sub>) can exceed the values specified in Tables 4-1 or 4-2. The use of a higher T<sub>p</sub> does not change the classification temperature (T<sub>c</sub>).
- Note 2: Package volume excludes external terminals (e.g., balls, bumps, lands, leads) and/or nonintegral heat sinks.
- Note 3: The maximum component temperature reached during reflow depends on package thickness and volume. The use of convection reflow processes reduces the thermal gradients between packages. However, thermal gradients due to differences in thermal mass of SMD packages may still exist.
- Note 4: Moisture sensitivity levels of components intended for use in a Pb-free assembly process shall be evaluated using the Pb-free classification temperatures and profiles defined in Tables 4.2 and 5-2, whether or not Pb-free.
- Note 5: SMD packages classified to a given moisture sensitivity level by using Procedures or Criteria defined within any previous version of J-STD-020, JESD22-A112 (rescinded), IPC-SM-786 (rescinded) do not need to be reclassified to the current revision unless a change in classification level or a higher peak classification temperature is desired.