


Asia Pacific Region

Product Detail:

- Designation:** Energizer Intrinsically Safe™ 2D LED Flashlight
- Model:** MS2DLED
- Color:** Safety Orange and Black
- Power Source:** Two "D"
- ANSI/NEDA:** 13 Series
- Lamp:** One High Power LED
- Lamp Life (hr):** Lifetime
- Lamp Output (lumens):** 28
- Beam Distance (m):** 115
- Peak Beam Intensity (cd):** 3,306
- Run Time (h:mm):** 45
- Durability:** Survives 1-metre drop
- Typical Weight:** 162 grams without batteries
- Dimensions (mm):** 201.4 x 50.8 x 64.8

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
 ©Energizer / All Rights Reserved

MS2DLED

Asia Pacific Region

Approved by global safety agencies, the MS2DLED is ideal for work in harsh conditions. The light is waterproof, dustproof and survives a 1-metre drop test. In addition, the body is constructed from anti-static, chemical resistant polypropylene.

The carabiner belt clip makes for easy access, while the internationally approved orange safety color provides instant recognition..



- UL/CUL intrinsic safety for hazardous locations Class I Div. 1 Groups A,B,C, & D, Class II Div. 1 Groups E,F,&G, and Class III Div. 1; T4.
- MSHA for methane-air mixtures.
- ATEX intrinsically safe flashlight for IM2/II1G EEx ia I/II C T4
- IECEx intrinsically safe flashlight for Ex ia IIC T4
- -20°C to 40°C ambient operating range.
- 0539
- EN60529 ingress protection level IP67.

Before Using Your Flashlight:


Please read all instructions and cautionary markings on the package and light

INTRINSICALLY SAFE



- Approved by global agencies for intrinsically safe lights
- Division 1, Class 1 rated

WATERPROOF



- Meets IEC 60529 IPX7 standards – 1 m for 30 min

IMPACT RESISTANT



- Survives a 1-metre drop

RELIABLE



- 45 hour run time using Energizer® MAX® batteries