

ADAM-4050

ADAM-4051

ADAM-4052

15-ch Digital I/O Module
16-ch Isolated Digital Input Module with Modbus

8-ch Isolated Digital Input Module



ADAM-4050



ADAM-4051



ADAM-4052



Specifications

General

- **Connectors** 2 x plug-in terminal blocks (#14 ~ 22 AWG)
- **Power Consumption** 0.4 W @ 24 V_{DC}
- **Watchdog Timer** System (1.6 second)
- **Supported Protocols** ASCII command

Digital Input

- **Channels** 7
- **Input Level** Logic level 0: +1 V max.
Logic level 1: 3.5 ~ 30 V
Pull up current: 0.5 mA,
10 kΩ resistor to +5 V

Digital Output

- **Channels** 8
open collector to 30 V,
30 mA max. load
- **Power Dissipation** 300 mW

Specifications

General

- **Connectors** 2 x plug-in terminal blocks (#14 ~ 28 AWG)
- **Power Consumption** 1 W @ 24 V_{DC}
- **Watchdog Timer** System (1.6 second) & Communication
- **Supported Protocols** ASCII command and Modbus/RTU

LED Indicators

Yes

Digital Input

- **Channels** 16
- **Input Voltage** 50 V max
- **Input Level**
Dry contact: Logic level 0: open
Logic level 1: close to GND
Wet contact: Logic level 0: +3 V max
Logic level 1: +10 ~ 50 V
(Note: Digital Input levels 0 and 1 can be inverted)
- **Isolation Voltage** 2,500 V_{DC}
- **Input Resistance** 5.2 kΩ
- **Overvoltage Protection** 70 V_{DC}

Specifications

General

- **Connectors** 2 x plug-in terminal blocks (#14 ~ 22 AWG)
- **Power Consumption** 0.4 W @ 24 V_{DC}
- **Watchdog Timer** System (1.6 second)
- **Supported Protocols** ASCII command

Digital Input

- **Channels** 8
(6 fully independent isolated channels, 2 isolated channels with common ground)
- **Input Level** Logic level 0: +1 V max.
Logic level 1: +3 ~ 30 V
- **Isolation Voltage** 5,000 V_{RMS}
- **Input Resistance** 3 kΩ

Common Specifications

General

- **Power Input** Unregulated 10 ~ 30 V_{DC}

Environment

- **Humidity** 5 ~ 95% RH
- **Operating Temperature** -10 ~ 70° C (14 ~ 158° F)
- **Storage Temperature** -25 ~ 85° C (-13 ~ 185° F)

Ordering Information

- **ADAM-4050** 15-ch Digital I/O Module
- **ADAM-4051** 16-ch Isolated Digital Input Module with Modbus
- **ADAM-4052** 8-ch Isolated Digital Input Module