



EQ215

19" STEREO 15 BAND GRAPHIC EQUALIZER

The LD EQ215 is a stereo 15 band graphic equalizer in standard 19"/1U rack format designed for professional live and studio applications. It offers the most common features such as 2/3 octave bands, 20 mm faders, ISO frequency meters, a switchable 50 Hz low cut filter, a ± 12 dB input gain range and an EQ Bypass switch. The XLR and 6,3 mm jack Neutrik connectors provide flexibility and quality. The rugged construction of the unit (metal housing, high quality faders) will provide a long lasting and reliable operational life. The cost effective LD EQ215 gives you full control of your sound.

SPECIFICATIONS LD EQ215

Model name:	LDEQ215
Bandwidth:	20 Hz to 20 kHz, +0,5/-1 dB
Frequency Response:	< 10 Hz to < 50 kHz, +0,5/-3dB
Dynamic Range:	108 dB
Signal-to- Noise Ratio:	90 dB
THD + Noise:	< 0,004 %
Interchannel crosstalk:	<- 80 dB, 20 Hz to 20 kHz
Inputs:	jack 6,3 mm, XLR female
Outputs:	jack 6,3 mm, XLR male
Max. Input Level:	>+21 dBu balanced or unbalanced
Dimensions (W x H x D):	482 x 44,5 x 153 mm