

Multimeter

Digital



Specifications

Basic Functions	Range	Best Accuracy
DC Voltage	400 mV / 4 V / 40 V / 300 V	$\pm (0.8\% + 1)$
AC Voltage	4 V / 40 V / 300 V	$\pm (1.2\% + 3)$
Resistance	400 Ω / 4 k Ω / 40 k Ω / 400 k Ω / 4 M Ω / 40 M Ω	$\pm (1\% + 2)$
Capacitance	4 nF / 40 nF / 400 nF / 4 μ F / 40 μ F / 200 μ F	$\pm (4\% + 3)$
Frequency	10 Hz / 100 kHz	$\pm (0.5\% + 3)$
Special Functions		
Auto ranging	✓	
Duty cycle	0.1% to 99.9%	
Diode	✓	
Continuity buzzer	✓	
Relative mode	✓	
Data hold	✓	
Full icon display	✓	
Sleep mode	✓	
Low battery display	✓	
Input impedance for DC voltage measurement	Around 10 M Ω	
Maximum display	3999	



Multimeter

Digital



General Characteristics

Power	3 V battery (CR2032)
LCD size	43 × 22 mm
Product colour	Orange and grey
Product net weight	62 g
Product size	58 × 108 × 12 mm
Standard accessories	Test lead, battery, English manual, vinyl holder
Standard individual packing	Blister

Part Number Table

Description	Part Number
Multimeter, Digital, Pocket	72-7935

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA™ is the registered trademark of the Group. © Premier Farnell plc 2011.

