

**NYS321****NYS Product Range / DIN Connectors**

## TECHNICAL DATA

## Electrical

Rated Current: Depends on mating connector  
Contact Resistance: Depends on mating connector  
Insulation Resistance: > 1 G Ohm  
Dielectric strength: 500 dc

## Mechanical

Life Cycles: 5000  
Cable OD: 4-9 mm  
Solderability: IEC68-2-20  
Operating Temperature: -25° C to +70° C

## Material

Housing/Handle: Brass Ni/Au/black plated or Zinc Diecast  
Insulation: Thermoplastic  
Contacts: Brass Ni/Au plated  
Strain Relief: CRIMP type SnCe plated

**Copyright © 2005**  
**Neutrik® AG.**  
**All Rights Reserved.**



**NEUTRIK®**  
CONNECTING THE WORLD

**Neutrik® AG - Headquarters**

Im alten Riet 143  
9494 Schaan  
Principality of Liechtenstein  
**phone:** +423 2372424  
**fax:** +423 2325393  
**email:** [neutrik@neutrik.com](mailto:neutrik@neutrik.com)  
**net:** <http://www.neutrik.com>