

Cree® 5mm Round LED C503B-WAN Data Sheet

Round LEDs offer superior light output for excellent readability in sunlight and dependable performance. It provides extremely stable light output over long periods of time.

These lamps are made with an advanced optical grade epoxy offering superior high temperature and high moisture resistance performance in lighting and illumination applications.



FEATURES

- Size (mm): 5
- Color Temperatures (K): Cool White (4600 to 15000) / Typical (9000)
- Luminous Intensity (mcd) Cool White (14400-32900)
- Viewing angle: 15 degree
- Lead-Free
- RoHS Compliant

APPLICATIONS

- Torch
- Light Strip
- Channel Letter
- Retail Display Lighting



Absolute Maximum Ratings ($T_A = 25^{\circ}C$)

Items	Symbol	Absolute Maximum Rating	Unit		
Forward Current	I _F	25	mA		
Peak Forward Current Note	$\mathbf{I}_{_{\mathrm{FP}}}$	100	mA		
Reverse Voltage	rse Voltage V _R		V		
Power Dissipation	P _D	100	mW		
Operation Temperature	T _{opr}	-40 ~ +95	°C		
Storage Temperature	T _{stg}	-40 ~ +100	°C		
Lead Soldering Temperature	T _{sol}	Max. 260°C for 3 sec. max. (3 mm from the base of the epoxy bulb)			

Note: Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

Typical Electrical & Optical Characteristics $(T_A = 25^{\circ}C)$

Characteristics	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	V _F	I _F = 20 mA	V		3.2	4.0
Reverse Current	I _R	$V_{R} = 5 V$	μA			100
Luminous Intensity	I _v	$I_F = 20 \text{ mA}$	mcd	14400	18000	
Chromaticity Coordinates	х	$I_{F} = 20 \text{ mA}$			0.2877	
	У	$I_F = 20 \text{ mA}$			0.2831	
50% Power Angle	201/2	$I_{F} = 20 \text{ mA}$	deg		15	

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.53700 Fax: +1.919.313.5778 www.cree.com/ledlamps



Intensity Bin Limit ($I_F = 20 \text{ mA}$)

Cool White

Bin Code	Min.(mcd)	Max.(mcd)
Ab	14400	16800
Ba	16800	20150
Bb	20150	23500
Ca	23500	28200
Cb	28200	32900

 \bullet Tolerance of measurement of luminous intensity is $\pm 15\%$

Color Bin Limit ($I_F = 20 \text{ mA}$)

VF Bin Limit ($I_F = 20 \text{ mA}$)

Bin Code	Min.(V)	Max.(V)							
27	2.8	3.0							
28	3.0	3.2							
29	3.2	3.4							
2a	3.4	3.6							
2b	3.6	3.8							
2c	3.8	4.0							

• Tolerance of measurement of VF is ± 0.05 V.

Bin Code	Sub- bin	x	У		Bin Code	Sub- bin	x	У		Bin Code	Sub- bin	x	у
		0.2545	0.2480			Wj	0.2830	0.3050				0.3300	0.3600
	Wa	0.2633	0.2410		W3		0.2950	0.3210			Wt	0.3455	0.3725
		0.2545	0.2245				0.2998	0.3028			vvt	0.3443	0.3535
		0.2450	0.2290				0.2895	0.2905				0.3300	0.3390
		0.2633	0.2410			Wk	0.2895	0.2905			Wu	0.3300	0.3390
	Wb	0.2720	0.2340				0.2998	0.3028				0.3443	0.3535
	VVD	0.2640	0.2200				0.3045	0.2865				0.3430	0.3345
W1		0.2545	0.2245				0.2960	0.2760		W5		0.3300	0.3180
VVI		0.2545	0.2480		115		0.2950	0.3210				0.3455	0.3725
	Wc	0.2640	0.2670		Wm	0.3070	0.3370			Wv	0.3610	0.3850	
	VVC	0.2720	0.2575			VVIII	0.3100	0.3150			vvv	0.3585	0.3680
		0.2633	0.2410				0.2998	0.3028				0.3443	0.3535
		0.2633	0.2410				0.2998	0.3028			Ww	0.3443	0.3535
	Wd	0.2720	0.2575			Wn	0.3100	0.3150				0.3585	0.3680
	wu	0.2800	0.2480				0.3130	0.2970				0.3560	0.3510
		0.2720	0.2340				0.3045	0.2865				0.3430	0.3345
		0.2640	0.2670			Wp	0.3070	0.3370					
	We	0.2735	0.2860				0.3185	0.3485					
	we	0.2808	0.2740				0.3200	0.3270					
		0.2720	0.2575				0.3100	0.3150					
		0.2720	0.2575			Wq	0.3100	0.3150					
	Wf	0.2808	0.2740				0.3200	0.3270					
		0.2880	0.2620				0.3215	0.3075					
W2		0.2800	0.2480		W4		0.3130	0.2970					
		0.2735	0.2860				0.3185	0.3485					
	Wg	0.2830	0.3050			Wr	0.3300	0.3600					
Wg	9	0.2895	0.2905				0.3300	0.3390					
		0.2808	0.2740				0.3200	0.3270					
		0.2808	0.2740			Ws	0.3200	0.3270					
	Wh	0.2895	0.2905				0.3300	0.3390					
		0.2960	0.2760				0.3300	0.3180					
		0.2880	0.2620				0.3215	0.3075					


• Tolerance of measurement of the color coordinates is ± 0.01 .

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5370 Fax: +1.919.313.5778 www.cree.com/ledlamps



CIE Chromaticity Diagram



Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 Fax: +1.919.313.5778 www.cree.com/ledlamps



Order Code Table*

Color	Kit Number	Minuting Angle	Luminous In	tensity (mcd)		
Color	Kit Number	Viewing Angle	Min.	Max.	Color Bin Code	
Cool White	C503B-WAN-CAbBb151	15	14400	23500	W1,W2,W3,W4,W5	
Cool White	C503B-WAN-CAbBb231	15	14400	23500	W2,W3	
Cool White	C503B-WAN-CBaBb231	15	16800	23500	W2,W3	
Cool White	C503B-WAN-CCaCb151	15	23500	32900	W1,W2,W3,W4,W5	
Cool White	C503B-WAN-CCaCb231	15	23500	32900	W2,W3	

Notes:

1. The above Kit Numbers represent order codes which include multiple intensity bin and color bin codes. Only one intensity bin code and one color bin code will be shipped on each reel. And single intensity bin code, single color bin codes will not be orderable.

Important Bins Notes:


- Please refer to the "Cree LED Lamp Reliability Test Standards" document for reliability test conditions.
- Please refer to the "Cree LED Lamp Soldering & Handling" document for information about how to use this LED product safely.

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 Fax: +1.919.313.5778 www.cree.com/ledlamps



Graphs






FIG.6 FAR FIELD PATTERN

IV(%)

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.53700 Fax: +1.919.313.5778 www.cree.com/ledlamps




Mechanical Dimensions

All dimensions are in mm. Tolerance is ± 0.25 mm unless otherwise noted.

An epoxy meniscus may extend about 1.5 mm down the leads.

Burr around bottom of epoxy may be 0.5 mm max.



Notes

RoHS Compliance

The levels of environmentally sensitive, persistent biologically toxic (PBT), persistent organic pollutants (POP), or otherwise restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2002/95/EC on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), as amended through April 21, 2006.

Vision Advisory Claim

Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.


Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5778 www.cree.com/ledlamps



Kit Number System

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.


Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5778 Fax: +1.919.313.5778 www.cree.com/ledlamps



Package

Features:

- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- The Bulk Pack types of packaging.
- Max 500 pcs per bag.



Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree LED Light logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.53708 Fax: +1.919.313.5778 www.cree.com/ledlamps