

Productname : DÉGRAISSANT SÉCHAGE RAPIDE Creationdate : 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 Replaces: BDS000139_20110606

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

DÉGRAISSANT SÉCHAGE RAPIDE
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, B.P. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptongatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture**

Classification according to 67/548/EEC or 1999/45/EC:

Health: R38: Irritating to skin.
R67: Vapours may cause drowsiness and dizziness.
Physical: EXTREMELY FLAMMABLE
Environment: R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in



Productname : DÉGRAISSANT SÉCHAGE RAPIDE Creationdate : 23.12.11 Version : 1.1
 Ref.Nr.: BDS000139_3_20111223 Replaces: BDS000139_20110606

the aquatic environment.

2.2. Label elements

Warning symbol(s) :

EXTREMELY FLAMMABLE



Xi : IRRITANT



N : DANGEROUS FOR THE ENVIRONMENT



Risk-phrase(s) :

R38: Irritating to skin.
 R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
 R67: Vapours may cause drowsiness and dizziness.

Safety-phrase(s) :

S2: Keep out of the reach of children.
 S16: Keep away from sources of ignition - No smoking.
 S23: Do not breathe vapours/spray.
 S35: This material and its container must be disposed of in a safe way.
 S51: Use only in well-ventilated areas.

Extra label elements according to Aerosol Dispenser Directive 75/324/EC:

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
 Without adequate ventilation formation of explosive mixtures may be possible.

Other extra label elements:

Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	-	921-024-6	30-60	F,Xn,N	11-38-51/53-65-67	
Hydrocarbons, C7-C9, n-alkanes, isoalkanes, cyclics	-	920-750-0	10-30	F,Xn,N	11-51/53-65-66-67	



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
 Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclic	-	927-510-4	10-30	F,Xn,N	11-38-51/53-65-67	
carbon dioxide	124-38-9	204-696-9	5-10	-	-	A,G
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	<10	F,Xi	11-36-67	B
acetone; propan-2-one; propanone	67-64-1	200-662-2	<10	F,Xi	11-36-66-67	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a) of REACH Regulation No 1907/2006

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, < 5% n-hexane	01-2119475514-35	-	921-024-6	30-60	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225, H315, H336, H304, H411	
Hydrocarbons, C7-C9, n-alkanes, isoalkanes, cyclics	01-2119473851-33	-	920-750-0	10-30	Flam. Liq. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225, H336, H304, H411	
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclic	01-2119475515-33	-	927-510-4	10-30	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225, H315, H336, H304, H411	
carbon dioxide		124-38-9	204-696-9	5-10	Press. Gas	H280	A, G
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	<10	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	B
acetone; propan-2-one; propanone	01-2119471330-49	67-64-1	200-662-2	<10	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a) of REACH Regulation No 1907/2006

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical advice
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	Ingestion is unlikely to occur If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation : Excessive inhalation of solvent vapours may give rise to nausea, headaches



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

3 / 10

Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

	and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections



Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/?/equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
carbon dioxide	124-38-9	TWA	5000 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
National established exposure limits, United Kingdom			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm

8.2. Exposure controls



Productname :	DÉGRAISSANT SÉCHAGE RAPIDE	Creationdate :	23.12.11 Version : 1.1
Ref.Nr.:	BDS000139_3_20111223	Replaces:	BDS000139_20110606

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves (neoprene)
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	CO2 propelled liquid.
colour :	Colorless.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	55-120 °C
Flash point :	< 0 °C (Closed Cup)
Evaporation rate :	2.8 (Ether=1)
Explosion limits : upper limit :	Not available.
lower limit :	0.9 %
Vapour pressure :	Not available.
Relative density :	0.712 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

9.2. Other information

VOC: 685 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

6 / 10

Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	>2000 mg/kg
		LC50 inhal.rat	>20 mg/l
		LD50 derm.rabit	>2000 mg/kg
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	>100 mg/l



Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

		LC50 fish	>100 mg/l
		EC50 daphnia	>100 mg/l
acetone; propan-2-one; propanone	67-64-1	IC50 algae	> 100 mg/l
		LC50 fish	> 100 mg/l
		EC50 daphnia	> 100 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS, flammable(naphtha's)

14.3. Transport hazard class(es)



CRC Industries Europe bvba
Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

8 / 10

Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : DÉGRAISSANT SÉCHAGE RAPIDE **Creationdate :** 23.12.11 Version : 1.1
Ref.Nr.: BDS000139_3_20111223 **Replaces:** BDS000139_20110606

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D,S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R11: Highly flammable.
R36: Irritating to eyes.
R38: Irritating to skin.
R65: Harmful: may cause lung damage if swallowed.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in



Productname :	DÉGRAISSANT SÉCHAGE RAPIDE	Creationdate :	23.12.11 Version : 1.1
Ref.Nr.:	BDS000139_3_20111223	Replaces:	BDS000139_20110606

the aquatic environment.

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

