


picoPak™ Relay Modules



picoPak™ relay modules are compact - just 6mm or 8mm wide - and ideal for control applications where rail space is limited. There are several versions to choose from and all mount on both 32mm and 35mm DIN rails.

Versions include:

MC5R 1A: Dual input voltages and a 1 form A (SPST-NO), 4A contact, 6mm wide. **CSA Class 1 Div 2 approved.**

MC5R 1C: 24Vdc input and a 1 form C (SPDT), 6A contact, 6mm wide.

MC6R 1C: Dual 24V and 120V input, 1 form C, 0.5A contact. Gold flashed contact, perfect for interfacing to PLC inputs.

MC6RF: 24V or 120V input and 1 form A, 5A contact. User serviceable fuse on output. 120V input version includes leakage immunity up to 1,5mA - perfect for use with PLC triac outputs.

Other features:

- combifoot for mounting on 32mm and 35mm DIN rails
- input status LEDs
- CSA approved
- optional jumper comb for cross connections

United States

Weidmuller Inc.
821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Facsimile: (804) 379-2593
Email: info@weidmuller.com
Website: www.weidmuller.com



Canada

Weidmuller Ltd.
10 Spy Court
Markham, Ontario L3R 5H6
Telephone: (800) 268-4080
Facsimile: (905) 475-2798
Email: info1@weidmuller.ca
Website: www.weidmuller.ca

Mexico

Weidmuller, S.A. de C.V.
5 Sur No. 4311
Col. Huexotitla
72534 Puebla, Pue. Mexico
Telephone: (22) 37 2549
Facsimile: (22) 43 1981
Email: weidmull@acnet.net

picoPak™ Relay Modules



Rated data	MC5R 1A	MC5R 1C	MC6R	MC6RF
AC Input				
Nominal input voltage			120Vac	120Vac
Turn ON voltage (nominal @ 25°C)			60Vac @ 9mA	
Guaranteed ON Voltage			75Vac	95Vac
Turn OFF voltage (nominal @ 25°C)			15Vac @ 2.5mA	
Guaranteed OFF voltage/current			6Vac	1.5mA
Turn OFF voltage (nominal @ 0°C)			19Vac @ 3mA	
Maximum input voltage			135Vac	140Vac
Nominal input current			17mA @ 120Vac	20mA @ 120Vac
Nominal on time			65mS	30ms
Nominal off time			65mS	30ms
Nominal operating frequency			7Hz	
DC Input				
Nominal input voltage	12/24Vdc	24Vdc	24Vdc	24Vdc
Turn ON voltage (nominal)			18.5Vdc @ 7mA	
Guaranteed ON voltage			20Vdc	18Vdc
Turn OFF voltage (nominal @ 25°C)			7Vdc @ 2mA	
Guaranteed OFF voltage			6Vdc	
Nominal input current	14mA	7mA	9mA @ 24Vdc	20mA @ 24Vdc
Nominal on time	10ms	10ms	2mS	10mS
Nominal off time	5ms	5ms	1.5mS	10mS
Nominal operating frequency			20Hz	
Output				
Output current/voltage (CSA rating)	4A, 30Vdc 4A, 250Vac	6A, 30Vdc 6A, 250Vac	2A, 30Vdc 0.5A, 125Vac 0.5A, 110Vdc	5A, 24Vdc (fused) ²⁾ 5A, 120Vac (fused) ²⁾
		0.5A, 125Vdc	0.4A, 125Vdc	
Rating (resistive load)	max. power max. switch voltage Max. switch current	1000VA, 120W 250Vac, 150Vdc 5A	1500VA 240Vac, 30Vdc 6A (4A inductive)	600VA, 120W 120V 5A
Minimum switching	voltage current	100mV 0.1mA	100mV 10mV 0.1mA 10µA	100mV 0.1mA
General				
Operating life @rated load	10 ⁵	10 ⁵	10 ⁵	10 ⁵
Insulation input/output	2KV	4KV	1.5KV	1.5KV
Contact material	gold flashed silver alloy	silver nickel 90/10 or gold flashed silver alloy	gold flashed silver alloy	gold flashed silver alloy
Storage temperature	-40°C to +60°C	-40°C to +60°C	-40°C - 60°C	-40°C to +60°C
Operating temperature (non-condensing)	-20°C to +60°C	-20°C to +55°C	-15°C - 50°C	-10°C to +40°C
Wire size	22...12AWG (0.5...2.5mm ²)	22...12AWG (0.5...2.5mm ²)	22-12AWG (0.5...2.5mm ²)	22 -12AWG (0.5-2.5mm ²)
Height to top of rail	63mm	63mm	68mm	71mm
Length x width	78 x 6 mm	78 x 6 mm	89mm x 8mm	89mm x 8mm
Approvals				
Ordering Data				
TS32/35 mounting (C / 1)	Cat.No. 790154 0000 ¹⁾	CSA Standard Gold Plated 790162 0000 790685 0000	Cat.No. 991059	CSA 24Vdc 120Vac 792345 0024 792345 0120
Accessories				
End Plate (AP/DK6) 1.5mm	C9039986	C9039986	C9040396	C9040396

1) Other dual input voltage modules available-consult Weidmüller. 2) Fuse type: Wickmann type TE5