

MATERIAL SAFETY DATA SHEET ANTISTATIC GLASS AND SCREEN SOLUTION

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME	ANTISTATIC GLASS AND SCREEN SOLUTION
PRODUCT NO.	ASC EASC250ML
APPLICATION	Cleaning Product
SUPPLIER	H K WENTWORTH PTY LIMITED P.O. BOX 339 BROOKVALE, NSW 2100 AUSTRALIA TEL: 02 9938 1566 FAX: 02 9938 1467 GENERAL MANAGER
EMERGENCY TELEPHONE	Tel: 029938 1566 between 8.30am and 5.00pm EST
PROPER SHIPPING NAME	AEROSOLS

2 HAZARDS IDENTIFICATION

RISK PHRASES

NC Not classified.

SAFETY PHRASES

NC Not classified.

The above phrases are the risks associated with the product

STATEMENT OF HAZARDOUS NATURE

NON-HAZARDOUS SUBSTANCE (According to criteria of NOHSC). NON-DANGEROUS GOODS (According to ADG Code).

3 COMPOSITION/INFORMATION ON INGREDIENTS

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels Ingredients are registered on AICS

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Provide rest, warmth and fresh air.

INGESTION

Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

ANTISTATIC GLASS AND SCREEN SOLUTION

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

ENGINEERING MEASURES

No particular ventilation requirements.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

If risk of splashing, wear safety goggles or face shield.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid
ODOUR	Characteristic
BOILING POINT (°C)	>100 (212 F)
MELTING POINT (°C)	>0 (32 F)
RELATIVE DENSITY	>0.997 @ 20 °c (68 F)
BULK DENSITY	997 kg/m ³
VAPOUR PRESSURE	2.35 kPa @ 20 °c (68 F)
pH-VALUE, CONC. SOLUTION	5-7

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid excessive heat for prolonged periods of time.

MATERIALS TO AVOID

Strong oxidising substances.

11 TOXICOLOGICAL INFORMATION

HEALTH WARNINGS	No specific health warnings noted. No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.
-----------------	--

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

Name	PROPAN-2-OL
Toxic Dose 1 - LD 50	5045 mg/kg (oral rat)
Toxic Dose 2 - LD 50	3600 mg/kg (oral-mouse)
Toxic Conc. - LC 50	47-73 mg/l/4h (inh-rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Not regarded as dangerous for the environment.

Name	PROPAN-2-OL
LC 50, 96 Hrs, Fish mg/l	9600
EC 50, 48 Hrs, Daphnia, mg/l	10000

ANTISTATIC GLASS AND SCREEN SOLUTION

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

GENERAL	The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).
	No transport warning sign required.
PROPER SHIPPING NAME	AEROSOLS
ROAD TRANSPORT NOTES	Not Classified
SEA TRANSPORT NOTES	Not classified.
AIR TRANSPORT NOTES	Not classified.
ADG CLASS	Not classified for transportation
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.

15 REGULATORY INFORMATION

RISK PHRASES

NC Not classified.

SAFETY PHRASES

NC Not classified.

POISONS SCHEDULE NUMBER

NONE

NATIONAL REGULATIONS AND REFERENCES

National Model Regulations for the Control of Workplace Hazardous Substances.

National Code of Practice for the Control of Workplace Hazardous Substances.

National Code of Practice for the Labelling of Workplace Substances.

National Code of Practice for the Preparation of Material Safety Data Sheets.

Approved Criteria for Classifying Hazardous Substances.

Exposure Standards for Atmospheric Contaminants in the Occupational Environment.

Australian Dangerous Goods Code. The Standard for the Uniform Scheduling of Drugs and Poisons (SUSDP).

16 OTHER INFORMATION

ISSUED BY

Helen O'Reilly

REVISION DATE

NOVEMBER 2010

REV. NO./REPL. SDS

1

GENERATED

SDS NO.

10323

RISK PHRASES IN FULL

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.