



## SAFETY DATA SHEET SILICONE MOULD RELEASE

### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**PRODUCT NAME** SILICONE MOULD RELEASE  
**PRODUCT NO.** DAS  
EDAS400  
ZE  
**APPLICATION** Manufacture of electrical equipment  
**SUPPLIER** ELECTROLUBE. A division of  
HK WENTWORTH LTD  
ASHBY PARK, COALFIELD  
WAY,  
ASHBY DE LA ZOUCH,  
LEICESTERSHIRE LE65 1JF  
UNITED KINGDOM  
+44 (0)1530 419600  
+44 (0)1530 416640  
info@hkw.co.uk

### 2 HAZARDS IDENTIFICATION

Extremely flammable

Vapours may cause drowsiness and dizziness.

Irritating to skin.

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**CLASSIFICATION (1999/45)** Xi;R38. F+;R12. N;R51/53. R67.

#### ENVIRONMENT

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. Use appropriate containment to avoid environmental contamination. Avoid release to the environment. Refer to special instructions/safety data sheets. Dispose of waste and residues in accordance with local authority requirements.

#### PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

### 3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
BUTANE	203-448-7	106-97-8	30-60%	F+;R12
WHITE SPIRIT	265-151-9	64742-49-0	10-30%	Xn;R65. Xi;R38. N;R51/53. R67,R10.
d-LIMONENE	227-813-5	5989-27-5	< 1%	R10 R43 Xi;R38 N;R50/53

The Full Text for all R-Phrases is Displayed in Section 16

#### COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

### 4 FIRST-AID MEASURES

#### NOTES TO THE PHYSICIAN

Treat symptomatically

#### INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

## SILICONE MOULD RELEASE

### INGESTION

Rinse mouth thoroughly. Provide rest, warmth and fresh air.

### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

## 5 FIRE-FIGHTING MEASURES

### EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

### SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

## 6 ACCIDENTAL RELEASE MEASURES

### SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers.

## 7 HANDLING AND STORAGE

### USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact.

### STORAGE PRECAUTIONS

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

## 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3	

WEL = Workplace Exposure Limit.

### INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

### PROTECTIVE EQUIPMENT



### ENGINEERING MEASURES

All handling to take place in well-ventilated area. Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours.

### RESPIRATORY EQUIPMENT

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment.

### HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

### EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

### HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

## SILICONE MOULD RELEASE

### 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid
COLOUR	Colourless
ODOUR	Odourless
VOLATILITY DESCRIPTION	Volatile.
SOLUBILITY	Insoluble in water
BOILING POINT (°C)	55 (131 F)
RELATIVE DENSITY	0.750 @ 20 °C (68 F)
FLASH POINT (°C)	<40 (104 F) CC (Closed cup).
FLAMMABILITY LIMIT - LOWER(%)	1.9
FLAMMABILITY LIMIT - UPPER(%)	9.5

### 10 STABILITY AND REACTIVITY

#### STABILITY

Stable under normal temperature conditions.

#### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

#### HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

### 11 TOXICOLOGICAL INFORMATION

#### INHALATION

High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system.

#### SKIN CONTACT

Irritating to skin. May cause allergic contact eczema. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

#### EYE CONTACT

Irritating to eyes.

#### OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

#### ROUTE OF ENTRY

Inhalation.

Name	BUTANE
Toxic Conc. - LC 50	658 mg/l/4h (inh-rat)
Name	d-LIMONENE
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)
Name	WHITE SPIRIT
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)

### 12 ECOLOGICAL INFORMATION

#### ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	d-LIMONENE
EC 50, 48 Hrs, Daphnia, mg/l	12.3
Mobility	

The product has poor water-solubility.

### 13 DISPOSAL CONSIDERATIONS

#### DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

## SILICONE MOULD RELEASE

### 14 TRANSPORT INFORMATION



PROPER SHIPPING NAME	AEROSOLS (WHITE SPIRIT)
PROPER SHIPPING NAME	CONSUMER COMMODITY
UN NO. ROAD	1950
ADR CLASS NO.	2
ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A
TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
IMDG PACK GR.	N/A
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1
AIR PACK GR.	N/A

### 15 REGULATORY INFORMATION

#### LABELLING



Irritant



Extremely Flammable



Dangerous for the environment

#### RISK PHRASES

R12	Extremely flammable.
R38	Irritating to skin.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

#### SAFETY PHRASES

S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S24	Avoid contact with skin.
S37	Wear suitable gloves.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.
P14	Contains d-LIMONENE. May produce an allergic reaction.

#### UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

#### ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

#### EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

## SILICONE MOULD RELEASE

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

### APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

### GUIDANCE NOTES

Workplace Exposure Limits EH40.

## 16 OTHER INFORMATION

### REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

### ISSUED BY

Helen O'Reilly

**REVISION DATE** NOVEMBER 2010

**REV. NO./REPL. SDS** 4

### GENERATED

**SDS NO.** 10994

### RISK PHRASES IN FULL

R12	Extremely flammable.
R10	Flammable.
R65	Harmful: may cause lung damage if swallowed.
R38	Irritating to skin.
R43	May cause sensitisation by skin contact.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.