


TLS2200® / TLS PC Link™ Wire and Cable Marking



Wire Marking Labels

B-427 Self-laminating Vinyl
B-642 Self-laminating Tedlar®

Diagram	Order Reference	Labels Per Roll	Label Width A (mm)	Label Height B (mm)	Write-on Height C (mm)	Min. Wire Diameter	AWG	Max. Wire Diameter	AWG	Max. Char. Per Line For Font 2	Max. Lines of Text For Font 2
10 to 000 AWG Based on Type of Wire – Maximum Wire Diam 10.00 mm											
■	PTL-87-427	250	44.45	25.40	9.53	3.00	10	10.00	000	40	3
10 to 0 AWG Based on Type of Wire – Maximum Wire Diam 8.00 mm											
■	PTL-104-427	250	38.10	25.40	9.53	3.00	10	8.00	0	37	3
10 to 4 AWG Based on Type of Wire – Maximum Wire Diam 5.00 mm											
◆	BPTL-17-427	5 000	12.70	25.40	9.53	3.00	10	5.00	4	11	3
◆	PTL-17-427	500	12.70	25.40	9.53	3.00	10	5.00	4	11	3
◆	PTL-17-427-YL	500	12.70	25.40	9.53	3.00	10	5.00	4	11	3
◆	BPTL-18-427	2 500	19.05	25.40	9.53	3.00	10	5.00	4	18	3
◆	PTL-18-427	250	19.05	25.40	9.53	3.00	10	5.00	4	18	3
◆	PTL-18-427-YL	250	19.05	25.40	9.53	3.00	10	5.00	4	18	3
■	BPTL-19-427	2 500	25.40	25.40	9.53	3.00	10	5.00	4	24	3
■	PTL-19-427	250	25.40	25.40	9.53	3.00	10	5.00	4	24	3
■	PTL-19-427-YL*	250	25.40	25.40	9.53	3.00	10	5.00	4	24	3
■	PTL-19-642	250	25.40	25.40	9.53	3.00	10	5.00	4	24	3
■	PTL-96-427	250	25.40	19.05	9.53	3.00	10	5.00	4	24	3
■	PTL-102-427	250	12.70	31.75	9.53	3.00	10	5.00	4	11	3
■	PTL-102-427-YL	250	12.70	31.75	9.53	3.00	10	5.00	4	11	3
10 to 10 AWG Based on Type of Wire – Maximum Wire Diam 3.00 mm											
◆	PTL-10-427	750	6.35	19.05	9.53	3.00	10	3.00	10	5	3
◆	PTL-10-427-YL	750	6.35	19.05	9.53	3.00	10	3.00	10	5	3
◆	BPTL-11-427	5 000	12.70	19.05	9.53	3.00	10	3.00	10	11	3
◆	PTL-11-427	500	12.70	19.05	9.53	3.00	10	3.00	10	11	3
◆	PTL-11-427-YL	500	12.70	19.05	9.53	3.00	10	3.00	10	11	3
7 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 12.00 mm											
◆	BPTL-107-427	1000	50.80	38.10	12.70	4.00	7	12.00	0000	46	5
◆	PTL-107-427	100	50.80	38.10	12.70	4.00	7	12.00	0000	46	5
7 to 000 AWG Based on Type of Wire – Maximum Wire Diam 10.00 mm											
■	PTL-88-427	250	44.45	38.10	12.70	4.00	7	10.00	000	40	5
7 to 0 AWG Based on Type of Wire – Maximum Wire Diam 8.00 mm											
◆	PTL-28-427	750	6.35	38.10	12.70	4.00	7	8.00	0	5	5
◆	PTL-28-427-YL*	750	6.35	38.10	12.70	4.00	7	8.00	0	5	5
◆	BPTL-29-427	5 000	12.70	38.10	12.70	4.00	7	8.00	0	11	5
◆	PTL-29-427	500	12.70	38.10	12.70	4.00	7	8.00	0	11	5
◆	PTL-29-427-YL*	500	12.70	38.10	12.70	4.00	7	8.00	0	11	5
◆	BPTL-30-427	2 500	19.05	38.10	12.70	4.00	7	8.00	0	18	5
◆	PTL-30-427	250	19.05	38.10	12.70	4.00	7	8.00	0	18	5
◆	PTL-30-427-YL*	250	19.05	38.10	12.70	4.00	7	8.00	0	18	5
◆	BPTL-31-427	2 500	25.40	38.10	12.70	4.00	7	8.00	0	24	5
◆	PTL-31-427	250	25.40	38.10	12.70	4.00	7	8.00	0	24	5
◆	PTL-31-427-YL*	250	25.40	38.10	12.70	4.00	7	8.00	0	24	5
◆	PTL-31-642	250	25.40	38.10	12.70	4.00	7	8.00	0	24	5
◆	BPTL-32-427	1 000	38.10	38.10	12.70	4.00	7	8.00	0	37	5
◆	PTL-32-427	250	38.10	38.10	12.70	4.00	7	8.00	0	37	5
◆	PTL-32-427-YL*	250	38.10	38.10	12.70	4.00	7	8.00	0	37	5
◆	PTL-106-427	15.24 m	38.10	38.10	12.70	4.00	7	8.00	0	N/A	5
7 to 4 AWG Based on Type of Wire – Maximum Wire Diam 5.00 mm											
■	PTL-103-427	250	25.40	31.75	12.70	4.00	7	5.00	4	24	5
3 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 14.00 mm											
◆	BPTL-21-427	1 000	25.40	63.50	19.05	6.00	3	14.00	0000	24	8
◆	PTL-21-427	100	25.40	63.50	19.05	6.00	3	14.00	0000	24	8
◆	PTL-21-427-YL*	100	25.40	63.50	19.05	6.00	3	14.00	0000	24	8
◆	PTL-21-642	100	25.40	63.50	19.05	6.00	3	14.00	0000	24	8
3 to 000 AWG Based on Type of Wire – Maximum Wire Diam 10.00 mm											
■	PTL-74-427	100	12.70	55.88	19.05	6.00	3	10.00	000	5	18
1 to 0000 AWG Based on Type of Wire – Maximum Wire Diam 24.00 mm											
◆	BPTL-23-427	1 000	25.40	101.60	25.40	8.00	1	24.00	0000	24	10
◆	PTL-23-427	100	25.40	101.60	25.40	8.00	1	24.00	0000	24	10
◆	PTL-23-427-YL*	100	25.40	101.60	25.40	8.00	1	24.00	0000	24	10
◆	BPTL-33-427	500	38.10	101.60	25.40	8.00	1	24.00	0000	37	10
◆	PTL-33-427	100	38.10	101.60	25.40	8.00	1	24.00	0000	37	10
◆	PTL-33-427-YL*	100	38.10	101.60	25.40	8.00	1	24.00	0000	37	10