

Test Procedure for the NCP3063 Invert – DIP



8/29/2006




Figure 1: Test Setup DIP

Table 1: Required Equipment

Voltage Supply (5V, 3A)	Voltage Meter	Electronic Load or Current Source
-------------------------	---------------	-----------------------------------

Test Procedure:

- 1. Connect the test setup as shown in Figure 1.**
- 2. Apply an input voltage, $V_{cc} = 5V$**
- 3. Apply $I_{out} = 0mA$ load.**
- 4. Check that V_{out} is $-12V$ ($-11.5V - -12.5V$)**
- 5. Increase I_{out} load to $100mA$**
- 6. Check that V_{out} is $-12V$ ($-11.5V - -12.5V$)**
- 7. Power down the load**
- 8. Power down V_{cc}**
- 9. End of test**