



Liquidtight Flexible Shielding Conduit



TYPE - EMCS



Contact your local Sales Representative
[Click Here for Printable Version](#)

Trade Size	Type	Inside Bend Radius	Wt. (Lbs.)/100 Ft.	Carton Length	Footage Part #	Reel Length	Footage Part #	List Price
3/8"	EMCS-10	3.0"	27	100	78701	500	78703	
1/2"	EMCS-11	3.0"	35	100	78711	500	78713	
3/4"	EMCS-12	4.0"	43	100	78722	500	78724	
1"	EMCS-13	4.0"	85	100	78732	400	78734	
1-1/4"	EMCS-14	4.5"	101	50	78742	200	78744	
1-1/2"	EMCS-15	7.0"	140	50	78752	150	78754	
2"	EMCS-16	9.5"	180	50	78762	100	78764	

The graph below depicts a general comparative shielding effectiveness (attenuation in dBs) of all three types of SHIELD-FLEX conduit. The dotted line indicates a comparison to standard unshielded liquidtight flexible conduit Type LA. The spectrum of test frequency is from 1 MHz to 10 MHz Electric Field, to 100 MHz to 1 GHz Planewave Field and 2 GHz to 6 GHz Microwave Field. Tests were performed per MIL-STD-285 on 1" trade size conduit using standard liquidtight fittings from Thomas & Betts Series 5300. Results are based on controlled laboratory conditions and may vary in actual field installed conditions.



See [Chart for Dimensions and Tolerances](#).

TYPE - EMCS

Type EMCS is a hybrid of SLA and EMS. It utilizes the same bronze core and PVC jacket as EMS, but gets further screening protection from a tinned copper braid as found in the SLA product. Accepts standard metallic liquidtight fittings.

For a low-smoke, low flame spread, zero-halogen version, ask for HFEMCS.

Shield-Flex, SLA and HFSLA are trademarks of Electri-Flex Company, registered in the U.S. Patent and Trademark Office.

Tests Include:

[RoHS and WEEE Compliant](#)

STANDARD COLORS:

Black. [Other colors and jacketing materials available upon request](#)

For UL and CSA version, consult factory

WORKING TEMPERATURES:

-55°C to 105°C

Flexibility: [See the Flexibility Comparison Guide](#)

Metal Used: Bronze

Plastic Used: PVC [See the Chemical Resistance Guide](#)

High Mech. Strength	Listed For Direct Burial	Halogen Free	Low Fire Hazard	Accepts Standard Liquidtight Fittings	Self Extinguish	EMI/RFI Shielding	Oil Resistance	Acid Resistance
				X	X	X	X	X