## Product data sheet Characteristics

### **ZBRRA**

## Programmable receiver - 2 relays - 24..240 V AC/DC - 2 pusbuttons - 6 LEDs



#### Main Range of product Harmony Product or component Programmable receiver type Device short name **ZBRRA** Output type 2 relays Product specific Interface to actuators application Function of module Monostable Bi-stable Stop/Start Reset time 2 ms (time delay)

#### Complementary

Switching capacity in VA	1250 VA
Maximum switching current	5 A AC/DC
[Us] rated supply voltage	24240 V AC/DC 50/60 Hz - 1010 %
Utilisation category	AC-15 : B300 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1
Power consumption in W	<= 4 W AC/DC
Immunity to microbreaks	10 ms
Control circuit frequency	5060 Hz +/- 10 %
Width	35 mm
Output contacts	2 C/O
Nominal output current	3 A
Operating position	Any position without derating
Electrical connection	1 conductor cable 0.142.5 mm² - AWG26AWG14 - solid - without cable end conforming to IEC 60947-1 2 conductors cable 0.141.5 mm² - AWG26AWG16 - solid - without cable end conforming to IEC 60947-1 1 conductor cable 0.144 mm² - AWG26AWG12 - flexible - with cable end conforming to IEC 60947-1 2 conductors cable 0.141.5 mm² - AWG26AWG16 - flexible - with cable end conforming to IEC 60947-1
Tightening torque	0.51 N.m conforming to IEC 60947-1
Housing material	Self-extinguishing plastic
Status LED	1 LED green for power ON 2 LEDs green for relay ON 2 LEDs green for function mode 1 LED green and yellow for reception signal
Mounting support	35 mm symmetrical DIN rail conforming to EN/IEC 60715

#### Environment


Environment	
Standards	IEC 6100-4-2 IEC 6100-4-3 IEC 6100-4-4 IEC 6100-4-5 IEC 6100-4-6 IEC 6100-4-11
Product certifications	CSA C-Tick GOST UL ANATEL SRRC
Marking	CE
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-2555 °C
Relative humidity	90 % at 55 °C
Vibration resistance	+/- 6.2 mm (f= 511 Hz) conforming to IEC 60068-2-6 3 gn (f= 11150 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP20 on casing conforming to IEC 60529 IP20 on terminals
Pollution degree	2 conforming to IEC 60664-1
Overvoltage category	II conforming to IEC 60664-1
Insulation resistance	> 500 MOhm at 500 V DC conforming to NF C 20030
[Ui] rated insulation voltage	250 V conforming to IEC 60664-1
Electromagnetic compatibility	Conducted emission conforming conforming to EN/IEC 61000-6-2 Radiated emission conforming
Resistance to electrostatic discharge	8 kV in free air (in insulating parts) conforming to IEC 61000-4-2 6 kV on contact (on metal parts) conforming to IEC 61000-4-2
Resistance to electromagnetic fields	10 V/m, f = 802000 MHz conforming to IEC 60947-5-1 3 V/m, f = 802700 MHz, distance = 20 m conforming to IEC 60947-4-3
Resistance to fast transients	2 kV
Electrical durability	100000 cycles
Mechanical durability	1000000 cycles



# Product data sheet Dimensions Drawings

## **ZBRRA**


### Programmable Receiver



## Product data sheet Mounting and Clearance


## **ZBRRA**

#### Receiver Clearance



- Drive
- (1) (2) Power Supply or PLC

#### **Receiver Mounting**




## Product data sheet Connections and Schema

## **ZBRRA**

#### Programmable Receiver

#### Wiring Diagram



- (1) 400 mA fast-blow fuse
- (2) lmax = 3 A