

Productname : KONTAKT 60

Creationdate :

22.09.11 Version :

Ref.Nr.: BDS000534\_3\_20110922

Replaces:

1.0

AB27000

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier****KONTAKT 60**

Aerosol

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

Cleaners - Precision

**1.3. Details of the supplier of the safety data sheet****CRC Industries Europe bvba**

Touwslagerstraat 1

9240 Zele

Belgium

Tel.: +32(0)52/45.60.11

Fax.: +32(0)52/45.00.34

E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja as.	00358/(19)32.921	00358/(19)383.676
CRC Industries France	ZI du Val d'Argent B.P.90028, 12, Bld des Martyrs de Chateaubriant, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

**1.4. Emergency telephone number**

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture**

Classification according to 67/548/EEC or 1999/45/EC:

**CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium



Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

**1 / 10**

<b>Productname :</b>	KONTAKT 60	<b>Creationdate :</b>	22.09.11 Version : 1.0
<b>Ref.Nr.:</b>	BDS000534_3_20110922	<b>Replaces:</b>	AB27000

<b>Health:</b>	R36/38: Irritating to eyes and skin. R67: Vapours may cause drowsiness and dizziness.
<b>Physical:</b>	EXTREMELY FLAMMABLE
<b>Environment:</b>	R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

## 2.2. Label elements

<b>Warning symbol(s) :</b>	EXTREMELY FLAMMABLE  Xi : IRRITANT 
<b>Risk-phrase(s) :</b>	R36/38: Irritating to eyes and skin. R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R67: Vapours may cause drowsiness and dizziness.
<b>Safety-phrase(s) :</b>	S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S23: Do not breathe vapours/spray. S35: This material and its container must be disposed of in a safe way. S51: Use only in well-ventilated areas.
<b>Extra label elements according to Aerosol Dispenser Directive 75/324/EC:</b>	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material. Without adequate ventilation formation of explosive mixtures may be possible.

Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

## 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures



**CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium  
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

2 / 10

**Productname :** KONTAKT 60  
**Ref.Nr.:** BDS000534\_3\_20110922

**Creationdate :** 22.09.11 Version : 1.0  
**Replaces:** AB27000

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	25-50	F,Xi	11-36-67	B
Hydrocarbons, C6-C7, n-alkanes,isoalkanes,cyclics,	-	921-024-6	<25	F,Xn,N	11-38-51/53-65-67	
butan-2-ol	78-92-2	201-158-5	<20	Xi	10-36/37-67	B
white mineral oil (petroleum)	8042-47-5	232-455-8	5-10			B
carbon dioxide	124-38-9	204-696-9	1-5	-	-	A,G

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
propan-2-ol; isopropyl alcohol ;isopropanol		67-63-0	200-661-7	25-50	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225, H319, H336	B
Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics,	01-2119475514-35	-	921-024-6	<25	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225, H315, H336, H304, H411	
butan-2-ol		78-92-2	201-158-5	<20	Flam. Liq. 3, Eye Irrit. 2, STOT SE 3, STOT SE 3	H226, H319, H335, H336	B
carbon dioxide		124-38-9	204-696-9	1-5	Press. Gas	H280	A, G

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek immediate medical attention
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	Ingestion is unlikely to occur If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

**4.2. Most important symptoms and effects, both acute and delayed**

CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

3 / 10

<b>Productname :</b>	KONTAKT 60	<b>Creationdate :</b>	22.09.11 Version : 1.0
<b>Ref.Nr.:</b>	BDS000534_3_20110922	<b>Replaces:</b>	AB27000

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	Irritating to skin Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain, impaired vision

#### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

#### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

#### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

#### 6.3. Methods and material for containment and cleaning up



<b>Productname :</b>	KONTAKT 60	<b>Creationdate :</b>	22.09.11 Version : 1.0
<b>Ref.Nr.:</b>	BDS000534_3_20110922	<b>Replaces:</b>	AB27000

Absorb spillage in suitable inert material  
Place in appropriate container  
This material and/or its container must be disposed of as hazardous waste.

#### 6.4. Reference to other sections

For further information see section 8

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/?/equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

#### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

#### 7.3. Specific end use(s)

Cleaners - Precision

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

##### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
carbon dioxide	124-38-9	TWA	5000 ppm
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm



**Productname :** KONTAKT 60 **Creationdate :** 22.09.11 Version : 1.0  
**Ref.Nr.:** BDS000534\_3\_20110922 **Replaces:** AB27000

		STEL	500 ppm
<b>National established exposure limits, United Kingdom</b>			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm

## 8.2. Exposure controls

**Control procedures :** Ensure adequate ventilation  
Keep away from heat and sources of ignition  
Take precautionary measures against static discharges

**Personal protection :** Take precautions to avoid contact with skin and eyes when handling the product.  
Ensure adequate ventilation

**inhalation :** In case of insufficient ventilation, wear suitable respiratory equipment.  
Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)

**hands and skin :** Wear suitable protective gloves  
(nitrile)

**eyes :** Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**Apperance : physical state :** CO2 propelled liquid.  
**colour :** Red.  
**odour :** Solvent.  
**pH :** Not applicable.  
**Boiling point/range :** Not available.  
**Flash point :** < 0 °C (Closed Cup)  
**Evaporation rate :** Not available.  
**Explosion limits : upper limit :** Not available.  
**lower limit :** Not available.  
**Vapour pressure :** Not available.  
**Relative density :** 0.76 g/cm<sup>3</sup> (@ 20°C).  
**Solubility in water :** Miscible with water  
**Auto-ignition :** > 200 °C  
**Viscosity :** Not applicable.

### 9.2. Other information

**VOC:** 640 g/l

## SECTION 10: Stability and reactivity



**CRC Industries Europe bvba**

Touwslagerstraat 1, 9240 Zele – Belgium  
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – [www.crcind.com](http://www.crcind.com)

6 / 10

**Productname :** KONTAKT 60 **Creationdate :** 22.09.11 Version : 1.0  
**Ref.Nr.:** BDS000534\_3\_20110922 **Replaces:** AB27000

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
<b>Skin contact :</b>	Irritating to skin
<b>Eye contact :</b>	Irritating to eyes

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	>2000 mg/kg
		LC50 inhal.rat	>20 mg/l
		LD50 derm.rabit	>2000 mg/kg

## SECTION 12: Ecological information



**Productname :** KONTAKT 60 **Creationdate :** 22.09.11 Version :  
**Ref.Nr.:** BDS000534\_3\_20110922 **Replaces:** 1.0  
AB27000

### 12.1. Toxicity

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	>100 mg/l
		LC50 fish	>100 mg/l
		EC50 daphnia	>100 mg/l

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available

### 12.4. Mobility in soil

No experimental data available

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way.  
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number





<b>Productname :</b>	KONTAKT 60	<b>Creationdate :</b>	22.09.11 Version : 1.0
<b>Ref.Nr.:</b>	BDS000534_3_20110922	<b>Replaces:</b>	AB27000

UN-number : 1950

**14.2. UN proper shipping name**

Proper shipping name: AEROSOLS, flammable

**14.3. Transport hazard class(es)**Class: 2.1  
ADR/RID - Classification code: 5F**14.4. Packing group**

Packing group: Not applicable.

**14.5. Environmental hazards**ADR/RID - Environmentally  
hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally  
hazardous: No**14.6. Special precautions for user**ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D,S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1907/2006 (REACH)

**15.2. Chemical safety assessment****CRC Industries Europe bvba**Touwslagerstraat 1, 9240 Zele – Belgium  
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com**9 / 10**

**Productname :** KONTAKT 60**Creationdate :**

22.09.11 Version :

**Ref.Nr.:** BDS000534\_3\_20110922**Replaces:**

1.0

AB27000

No information available

**SECTION 16: Other information****\*Explanation risk-phrases:**

R10: Flammable.

R11: Highly flammable.

R36: Irritating to eyes.

R38: Irritating to skin.

R65: Harmful: may cause lung damage if swallowed.

R67: Vapours may cause drowsiness and dizziness.

R36/37: Irritating to eyes and respiratory system.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**\*Explanation hazard statements:** H225 : Highly flammable liquid and vapour.

H226 : Flammable liquid and vapour.

H280 : Contains gas under pressure; may explode if heated.

H304 : May be fatal if swallowed and enters airways.

H315 : Causes skin irritation.

H319 : Causes serious eye irritation.

H335 : May cause respiratory irritation.

H336 : May cause drowsiness or dizziness.

H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.