

## LDS100 Series

### LED Lighting Power Supply - Class 2

**Total Power:** 100 Watts  
**# of Outputs:** Single



### Special Features

- Constant Current & Constant Voltage operation
- Dimming options
- Free-Air rated - No forced air necessary for cooling

### Compliance

- Class 2 Outputs
- IP64 to IP67 Water Protection
- CISPR 15 / FCC Part 15 EMI Performance
- Class C Harmonics
- < 1.0 W No-load power
- > 0.9 Power Factor

### Safety

- EN 61347-2-13
- UL 1310 / 8750
- CSA C22.2 No. 107.1
- CE Mark (LVD)


## Electrical Specifications

Input	
Input range:	100 - 240 Vac (U models); 120-277 Vac (H models)
Input frequency:	47 - 63 Hz
Inrush current:	< 50 A max., cold start @ 25 °C
Leakage current:	750 µA, at 264 Vac 50/60 Hz
Input power (no-load):	< 1.0 W, at no load
Input power (max):	< 118 W, at full load
Input fusing:	Internally fused
EMI/RFI:	CISPR 15 FCC Part 15
Efficiency (typical):	90% - 230 Vac 89% - 115 Vac
Output	
Constant current:	Programmable current levels. Refer to model table for details
Constant voltage:	No load to Full load operation. Refer to model table for details
Output power:	100 W maximum. Class 2 rated outputs
Ripple voltage:	< 2%
Control and Protection	
Current limit:	Programmable. Refer to model table for details
Protection:	Short Circuit Overvoltage Overtemperature

## Environmental Specifications

Criteria	Specification	Reference
Power Factor	> 0.9	Energy Star
Harmonics	Class C	IEC 61000-3-2
THD - Input Current	< 20%	ANSI C82.11
Surge Immunity	Level 3 6 kV ring wave	IEC 61000-4-5 ANSI C62.41
EMC Compliance		IEC 61000-4-2, -3, -4, -5, -6, -8, -11
Temperature (case)	-40 °C to 90 °C	Operating
Ingress Protection	IP64 through IP66	Refer to model table for details

## Mechanical Drawing



## Mechanical Miscellaneous

Criteria	Specification	Reference
Input Wiring	300 mm	3-wire
Output Wiring	300 mm	4-wire
Weight	grams	

### Ordering Information

Model Number	Rated Output Voltage	Rated Output Current	Dimming Interface	IP Rating	Status
LDS100-24-U00	24 Vdc	4.1 Adc		IP67	Coming Soon
LDS100-24-H00	24 Vdc	4.1 Adc		IP67	Released
LDS100-24-H03	24 Vdc	4.1 Adc	0 - 10 V	IP67	Released
LDS100-31-H03	31 Vdc	3.16 Adc	0 - 10 V	IP67	Coming Soon

### Americas

5810 Van Allen Way  
Carlsbad, CA 92008  
USA  
Telephone: +1 760 930 4600  
Facsimile: +1 760 930 0698

### Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
Telephone: +44 (0) 1384 842 211  
Facsimile: +44 (0) 1384 843 355

### Asia (HK)

14/F, Lu Plaza  
2 Wing Yip Street  
Kwun Tong, Kowloon  
Hong Kong  
Telephone: +852 2176 3333  
Facsimile: +852 2176 3888

For global contact, visit:

[www.Emerson.com/EmbeddedPower](http://www.Emerson.com/EmbeddedPower)  
[techsupport.embeddedpower@emerson.com](mailto:techsupport.embeddedpower@emerson.com)

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

### Emerson Network Power.

The global leader in enabling business-critical continuity.

- AC Power
- Connectivity
- DC Power
- Embedded Computing
- **Embedded Power**
- Monitoring
- Outside Plant
- Power Switching & Controls
- Precision Cooling
- Racks & Integrated Cabinets
- Services
- Surge Protection

### EmersonNetworkPower.com

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.  
©2011 Emerson Electric Co.

## Current Adjust and Dimming Description

0 - 10 V Between Purple & Grey Wires (for model -H03 only)

