



### Main

Range of product	Harmony XB5
Product or component type	Wireless and batteryless transmitter
Device short name	XB5R
Bezel material	Plastic
Fixing collar material	Plastic
Mounting diameter	22 mm

### Complementary

Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Flush blue
Embedding depth	<= 42 mm
CAD overall height	41.5 mm
CAD overall width	30 mm
CAD overall depth	43 mm
Product weight	0.045 kg
Main group	Wireless pushbutton
Group of product	Flush push wireless
Station name	XALD 1...5 cut-outs XALK 2...5 cut-outs
Cap/Operator or lens colour	Blue
Marking	Unmarked

### Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP65 on front face conforming to IEC 60529 IP30 on back face conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 50102
Mechanical durability	1000000 cycles
Vibration resistance	5 gn (f= 11...500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms half sine wave acceleration) conforming to IEC 60068-2-27 50 gn (duration = 11 ms half sine wave acceleration) conforming to IEC 60068-2-27
Standards	CSA C22-2 No 14 EN/IEC 60947-5-1 UL 508 EN 300-440-1 EN 300-440-2 EN 301-489-1 EN 301-489-3

---

Product certifications

CE  
C-Tick  
FCC  
GOST  
ANATEL  
SRRC  
BT 2006/95/EC  
EMC directive 2004/108/EC  
R&TTE directive 1999/5/EC  
RSS


---

---

Wireless and Batteryless Pushbutton - Transmitter

---

With Plastic Pushbutton and Cap



e: panel thickness 1 to 6 mm / 0.039 to 0.24 in.