

TRIO-DIODE/48DC/2X10/1X20

Order No.: 2866527



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2866527>

Redundancy module with function monitoring, 48 V DC, 2x 10 A, 1x 20 A



Commercial data

EAN	 4 046356 562973
Pack	1
Customs tariff	85044082
Country of Origin	CN
Catalog page information	Page 629 (IF-2011)

Product notes

WEEE/RoHS-compliant since:
02/02/2010



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Product description

TRIO DIODE is the DIN-rail mountable redundancy module from the TRIO POWER product range.

Using the redundancy module, it is possible for two power supply units of the same type connected in parallel on the output side to increase performance or for redundancy to be 100% isolated from one another.

Redundant systems are used in systems that place particularly high demands on operational reliability. The connected power supply units must be large enough that the total current requirements of all loads can be met by one power supply unit. The redundant structure of the power supply therefore ensures long-term, permanent system availability.

In the event of an internal device fault or failure of the mains power supply on the primary side, the other device automatically takes over the entire power supply of the loads without interruption. The floating signal contact and LED immediately indicate the loss of redundancy.

Technical data

Input data

Nominal input voltage	48 V DC
DC input voltage range	30 V AC ... 56 V AC
Nominal input current I_N	2x 10 A (-25°C to +55°C) 1x 20 A (-25°C to +55°C)
Maximum current I_{max}	2x 15 A (-25°C to +40°C) 1x 30 A (-25°C to +40°C)

Output data

Nominal output voltage	0.5 V < DC input
Output current	20 A (Increasing power) 10 A (Redundancy)
Derating	55 °C ... 70 °C (2.5%/K)
Maximum power dissipation idling	7 W ($I_{OUT} = 10$ A)
Power loss nominal load max.	14 W ($I_{OUT} = 20$ A)

General data

Width	32 mm
Height	130 mm
Depth	115 mm
Net weight	0.37 kg
Efficiency	> 97 %
Degree of protection	IP20
Protection class	III
MTBF (IEC 61709, SN 29500)	> 10000000 h
Ambient temperature (operation)	-25 °C ... 70 °C (> 55° C derating)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, no condensation)
Mounting position	horizontal DIN rail NS 35, EN 60715
Assembly instructions	Can be aligned: Horizontally 0 mm, vertically 50 mm
Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Low Voltage Directive	Conformance with LV directive 2006/95/EC

Standard – Electrical equipment of machines	EN 60204
Standard - Electrical safety	EN 60950-1/VDE 0805 (SELV)
Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)
Standard – Safety extra-low voltage	IEC 60950-1 (SELV) and EN 60204 (PELV)
Standard - Safe isolation	DIN VDE 0100-410
	DIN VDE 0106-1010
Standard – Protection against electric shock	DIN 57100-410
Standard – Protection against shock currents, basic requirements for protective separation in electrical equipment	DIN VDE 0106-101
UL approvals	UL/C-UL listed UL 508
	UL/C-UL Recognized UL 60950

Connection data, input

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	9 mm
Screw thread	M2,5

Connection data, output

Connection method	Screw connection
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	10
Stripping length	14 mm

Signaling

Output name	Floating redundancy OK
-------------	------------------------

Output description	Contact closed when U_{IN1} & $U_{IN2} > 28\text{ V}$
Maximum switching voltage	30 V AC/DC
Maximum inrush current	$\leq 100\text{ mA}$ (short-circuit resistant)
Status display	LED redundancy OK
Note on status display	U_{IN1} & $U_{IN2} > 28\text{ V}$: LED lights up green
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Tightening torque, min	0.4 Nm
Tightening torque max	0.5 Nm
Screw thread	M2,5


Certificates



Certification CUL, CUL Listed, UL, UL Listed

Drawings

Block diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG, England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;