



SAFETY DATA SHEET

ISO 9001 version 2008

AIR DUSTER NON FLAMMABLE

Page : 1

Revised edition no : 4

Date : 15/4/2009

Supersedes : 29/3/2005

006910

www.lisam.com

Producer

ITW Spraytec
5 bis, rue Retrou
F-92600 Asnières sur Seine France
Tel : 01.40.80.32.32 - Fax : 01.40.80.32.30
infofds@itwpc.com

1 IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING

Trade name : AIR DUSTER NON FLAMMABLE
Identification of the product : Aerosol.
Type of product : Air duster.
Company identification : See producer.
Emergency phone nr : INRS : 01.45.42.59.59

2 HAZARDS IDENTIFICATION

Symptoms relating to use

- Inhalation : Overexposure to vapours may result in headache, nausea. Drowsiness.
- Skin contact : Repeated or prolonged skin contact may cause irritation progressing to a burn.
- Eye contact : Direct contact with liquefied gas may cause severe and possibly permanent eye injury due to frostbite from rapid liquid evaporation. Redness. Pain.
- Ingestion : May cause burns or irritation of the linings of the mouth, throat, and gastrointestinal tract.

3 COMPOSITION / INFORMATION ON INGREDIENTS

This product is not considered to be hazardous but contains hazardous components.

Substance name	Contents (%)	CAS No / EC No / Index No	Symbol(s)	R-Phrase(s)
<u>1,1,1,2-Tetrafluoroethane</u>	: 50 to 100 %	811-97-2 / 212-377-0 / -----		
<u>Dimethyl ether</u>	: 1 to 10 %	115-10-6 / 204-065-8 / 603-019-00-8	F+	12

4 FIRST AID MEASURES

First aid measures

- Inhalation : If overcome by exposure, remove victim to fresh air immediately. Allow the victim to rest. Seek medical advice.
- Skin contact : Wash skin thoroughly with mild soap and water.
- Eye contact : Rinse immediately with plenty of water. Seek medical attention if ill effect or irritation develops.
- Ingestion : Ingestion unlikely. Rinse mouth. Obtain medical attention.

5 FIRE-FIGHTING MEASURES

Specific hazards : When exposed to heat or if contaminated by certain impurities, may decompose to generate highly volatile gases which may over pressure and violently rupture closed containers. Thermal decomposition generates : Fluorhydric acid. Carbon monoxide. Carbon dioxide.

Extinguishing media

- Suitable extinguishing media : Powder. Carbon dioxide. Foam. Water fog.
- Unsuitable extinguishing media : Do not use a heavy water stream.

Protection against fire : Do not enter fire area without proper protective equipment, including respiratory protection.

Special procedures : Use water spray or fog for cooling exposed containers.



SAFETY DATA SHEET

ISO 9001 version 2008

AIR DUSTER NON FLAMMABLE

Page : 2

Revised edition no : 4

Date : 15/4/2009

Supersedes : 29/3/2005

006910

www.lisam.com

6 ACCIDENTAL RELEASE MEASURES

- Personal precautions : Respiratory protection equipment may be necessary.
Environmental precautions : Not expected to present a significant hazard under anticipated conditions of normal use.
Clean up methods : Remove ignition sources.

7 HANDLING AND STORAGE

- Precautions in handling and storage : Keep away from sources of ignition - No Smoking.
Storage : Protect from freezing. Keep at temperature not exceeding 50° C. Store in dry, cool, well-ventilated area. Store above 5°C
Storage - away from : Direct sunlight. Heat sources. Sparks. Open flame.
Handling : Handle in accordance with good industrial hygiene and safety procedures. Keep away from food, drink and animal feeding stuffs.

8 EXPOSURE CONTROLS / PERSONAL PROTECTION

- Respiratory protection : No special respiratory protection equipment is recommended under normal conditions of use with adequate ventilation.
- Hand protection : Not required.
- Skin protection : No special clothing/skin protection equipment is recommended under normal conditions of use.
- Eye protection : Eye protection should only be necessary where liquid could be splashed or sprayed.
Industrial hygiene : Provide adequate ventilation to minimize dust and/or vapour concentrations. When using, do not eat, drink or smoke.
Exposure controls : 1,1,1,2-Tetrafluoroethane : VME (ppm) : 1000
1,1,1,2-Tetrafluoroethane : VME (mg/m3) : 4420
Dimethyl ether : VME (mg/m3) : 1920
Dimethyl ether : VME (ppm) : 1000

9 PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : Liquid.
Colour : Colourless.
Odour : Ethereal.
Boiling point [°C] : /
Density : 1.13
Solubility in : Solvent.
Flash point [°C] : Sans

10 STABILITY AND REACTIVITY

- Hazardous decomposition products : None under normal conditions. Thermal decomposition generates : Carbon dioxide. Carbon monoxide. Fluorhydric acid.
Materials to avoid : Strong acids. Strong bases. Strong oxidizers.
Conditions to avoid : Heat. Direct sunlight. Open flame. Sparks.

11 TOXICOLOGICAL INFORMATION

- Toxicity information : No data available.
Acute toxicity : No data available.
Chronic toxicity :
- Inhalation : May cause burns or irritation of the linings of the mouth, throat, and gastrointestinal tract. Vapours may cause drowsiness and dizziness. Headache.
- Dermal : May cause a sensitization.
- Ocular : Direct contact with liquefied gas may cause severe and possibly permanent eye



SAFETY DATA SHEET

ISO 9001 version 2008

AIR DUSTER NON FLAMMABLE

Page : 3

Revised edition no : 4

Date : 15/4/2009

Supersedes : 29/3/2005

006910

www.lisam.com

11 TOXICOLOGICAL INFORMATION (continued)

- Ingestion : injury due to frostbite from rapid liquid evaporation.
: May cause burns or irritation of the linings of the mouth, throat, and gastrointestinal tract.

12 ECOLOGICAL INFORMATION

- On product : No data available.

13 DISPOSAL CONSIDERATIONS

- General : Container under pressure. Do not drill or burn even after use. When not empty dispose of this container at hazardous or special waste collection point. Dispose in a safe manner in accordance with local/national regulations. Do not empty into drains.

14 TRANSPORT INFORMATION

- Shipping name : UN1950 AÉROSOLS, 2.2, 5A
UN No. : 1950
Land transport
ADR/RID : Class : 2
Group : 5A
Sea transport
- IMO-IMDG code : Class 2
- EMS-Nr : 2-13
- IMDG-Marine pollution : No.
Air transport
- IATA - Class or division : Class 2.2
- IATA-Label : Non Flamm. Gas

15 REGULATORY INFORMATION

- Symbol(s) : None.
- R Phrase(s) : None.
- S Phrase(s) : S2 : Keep out of the reach of children.
S23 : Do not breathe spray.
S51 : Use only in well-ventilated areas.
Safety advises : Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use. 10.0 % by mass of the contents are flammable. Use this aerosol only for the applications for which it is intended.
France : Surveillance médicale spéciale (Arrêté du 11 juillet 1977) relative à la présence de composés fluorés.

16 OTHER INFORMATION

- Recommended uses and restrictions : See product bulletin for detailed information.
Text of R-Phrases in § 3 : R12 : Extremely flammable.

The contents and format of this SDS are in accordance with REGULATION (EC) No 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL



SAFETY DATA SHEET	Page : 4
	Revised edition no : 4
ISO 9001 version 2008	Date : 15/4/2009
AIR DUSTER NON FLAMMABLE	Supersedes : 29/3/2005
	006910 www.lisam.com

DISCLAIMER OF LIABILITY The information in this SDS was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This MSDS was prepared and is to be used only for this product. If the product is used as a component in another product, this MSDS information may not be applicable.

End of document