

97

97 Four-Mandrel Crimping Pliers for turned contacts



97 52 63 DG




97 52 64



97 52 65



97 52 65 DG



Locator for the contacts



97 52 63/65 DG: Pliers with locator and service tools in a plastic case with foam insert

- ▶ for crimping turned contacts
- ▶ for solder-free electrical connections
- ▶ four-mandrel crimping for exact crimping performance
- ▶ mandrel gauge to check the basic setting
- ▶ locator for positioning the contacts
- ▶ repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ optimum transmission of force due to lever action for fatigue-reduced operation
- ▶ high operation comfort thanks to handy shape
- ▶ all stressed parts are made of special steel, oil-hardened and tempered

Model 97 52 63:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, two-colour dual component handles

Model 97 52 64:

- ▶ pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- ▶ nickel plated head, two-colour dual component handles

Model 97 52 65:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ nickel plated head, plastic handles

Model 97 52 63 DG:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ with digital display of the preset crimping capacities
- ▶ display reversible between mm / inch and MIL numerical values
- ▶ nickel plated head; with two-colour dual component handles

Model 97 52 65 DG:

- ▶ fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- ▶ with digital display of the preset crimping capacities
- ▶ display reversible between mm / inch and MIL numerical values
- ▶ nickel plated head; with plastic handles

Article-No.	EAN-Code	Range of Application	Capacity		Length		Δ
			mm ²	AWG	mm	g	
97 52 63	4003773-050148	turned contacts	0.08 - 2.5	28 - 13	180	370	
97 52 63 DG	063209	terminales girados	0.08 - 2.5	28 - 13	195	380	
97 52 64	041481	turned contacts	0.08 - 2.5	28 - 13	180	415	
97 52 65	045236	turned contacts (Harting)	0.14 - 6.0	26 - 10	230	680	
97 52 65 DG	063216	terminales girados (Harting)	0.14 - 6.0	26 - 10	250	700	



Four-mandrel squeezing for exact crimping performance