

GSB + GDR 18V-Li DYNAMIC SERIES TWINPACK SPEC SHEET

Torque, max.	60 Nm
No-load speed (1st gear/2nd gear)	0 – 500 / 1.700 rpm
Max. impact rate	25.500 bpm
Chuck jaw width, min./max.	1,5 / 13 mm
Weight incl. battery	1,6 kg
Drilling diameter	
Max. drilling diameter in wood	32 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in masonry	13 mm

Technical data: GDR 18 V-LI Professional

No-load speed	0 – 2.800 rpm
Charging time	30 mins
Weight incl. battery	1,7 kg
Torque, max.	160 Nm
Rated impact rate	0 – 3.200 bpm
Toolholder	1/4" internal hexagon