

## MATERIAL SAFETY DATA SHEET

### AIRDUSTER PLUS

#### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**PRODUCT NAME** AIRDUSTER PLUS  
**PRODUCT NO.** EADP400 [EEADP400]  
**APPLICATION** Cleaning Product  
**SUPPLIER** H K WENTWORTH PTY LIMITED  
P.O. BOX 339  
BROOKVALE, NSW 2100  
AUSTRALIA  
TEL: 02 9938 1566  
FAX: 02 9938 1467  
GENERAL MANAGER  
**EMERGENCY TELEPHONE** Tel: 029938 1566 between 8.30am and 5.00pm EST  
**PROPER SHIPPING NAME** AEROSOLS

#### 2 HAZARDS IDENTIFICATION

##### RISK PHRASES

NC Not classified.

##### SAFETY PHRASES

A1 Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.  
A2 Do not spray on a naked flame or any incandescent material.  
S2 Keep out of the reach of children.  
S23 Do not breathe vapour/spray.

##### PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

##### STATEMENT OF HAZARDOUS NATURE

DANGEROUS GOODS (According to ADG Code). NON-HAZARDOUS SUBSTANCE (According to criteria of NOHSC).

##### DG CLASS

Class 2: Gases

**PACKING GROUP** N/A

**UN NO.** 1950

#### 3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification (NOHSC: 2011)
1,1,1,2-TETRAFLUOROETHANE R134A	212-377-0	811-97-2	80-100%	-
DIMETHYL ETHER	204-065-8	115-10-6	5-10%	F+;R12

The Full Text for all R-Phrases are Displayed in Section 16

##### COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels Ingredients are registered on AICS

#### 4 FIRST-AID MEASURES

##### NOTES TO THE PHYSICIAN

Treat symptomatically

## AIRDUSTER PLUS

### INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

### INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly.

### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

## 5 FIRE-FIGHTING MEASURES

### EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

### SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

## 6 ACCIDENTAL RELEASE MEASURES

### SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers.

## 7 HANDLING AND STORAGE

### USAGE PRECAUTIONS

Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

### STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

## 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
1,1,1,2-TETRAFLUOROETHANE R134A	ES-TWA	1000 ppm	4240 mg/m3			
DIMETHYL ETHER	ES-TWA				mg/m3	

### ENGINEERING MEASURES

No particular ventilation requirements.

### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

### HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

## 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid		
COLOUR	Colourless		
ODOUR	Characteristic Ether		
VOLATILITY DESCRIPTION	Volatile.		
SOLUBILITY	Insoluble in water		
BOILING POINT (°C)	-26.5 (-15.7 F)	RELATIVE DENSITY	1.176 @ 25 °c (77 F)
VAPOUR PRESSURE	62.82 kPa @ 20 °c (68 F)		

## 10 STABILITY AND REACTIVITY

## AIRDUSTER PLUS

### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

### HAZARDOUS DECOMPOSITION PRODUCTS

Fire or high temperatures create: Carbon monoxide (CO). Hydrogen fluoride (HF). Carbonyl fluoride

## 11 TOXICOLOGICAL INFORMATION

### TOXICOLOGICAL INFORMATION

No information available.

### GENERAL INFORMATION

No specific health warnings noted.

### INHALATION

High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting. Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

### INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly.

### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

### HEALTH WARNINGS

Contact with liquid form may cause frostbite.

### OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

## 12 ECOLOGICAL INFORMATION

### ECOTOXICITY

Not regarded as dangerous for the environment.

## 13 DISPOSAL CONSIDERATIONS

### DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

## 14 TRANSPORT INFORMATION



<b>PROPER SHIPPING NAME</b>	AEROSOLS		
<b>UDF Phrase 1</b>	Class 2.2: Non-flammable non-toxic gases		
	Class 2.2: Non-flammable non-toxic gases		
<b>UN NO.</b>	1950	<b>ADG CLASS NO.</b>	2
<b>DG CLASS</b>	Class 2: Gases	<b>PACKING GROUP</b>	N/A
<b>TUNNEL RESTRICTION CODE</b>	(E)	<b>ADG LABEL NO.</b>	2.2
<b>UN NO. SEA</b>	1950	<b>IMDG CLASS</b>	2.2
<b>IMDG PAGE NO.</b>	9022	<b>IMDG PACK GR.</b>	N/A
<b>EMS</b>	F-D, S-U	<b>MFAG</b>	See Guide
<b>MARINE POLLUTANT</b>	No.	<b>UN NO. AIR</b>	1950
<b>AIR CLASS</b>	2.2	<b>AIR PACK GR.</b>	N/A

## AIRDUSTER PLUS

### 15 REGULATORY INFORMATION

#### RISK PHRASES

NC Not classified.

#### SAFETY PHRASES

A1 Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.  
A2 Do not spray on a naked flame or any incandescent material.  
S2 Keep out of the reach of children.  
S23 Do not breathe vapour/spray.

POISONS SCHEDULE NUMBER none

#### NATIONAL REGULATIONS AND REFERENCES

National Model Regulations for the Control of Workplace Hazardous Substances.  
National Code of Practice for the Control of Workplace Hazardous Substances.  
National Code of Practice for the Preparation of Material Safety Data Sheets.  
Approved Criteria for Classifying Hazardous Substances.  
Exposure Standards for Atmospheric Contaminants in the Occupational Environment.  
Australian Dangerous Goods Code. The Standard for the Uniform Scheduling of Drugs and Poisons (SUSDP).

### 16 OTHER INFORMATION

#### ISSUED BY

Helen O'Reilly

REVISION DATE NOVEMBER 2010

REV. NO./REPL. SDS 5

#### GENERATED

SDS NO. 11006

#### RISK PHRASES IN FULL

R12 Extremely flammable.

#### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.