

DIN Rail Terminal Blocks

MIK25

12 mm - 600 Volts AC/DC


Specifications:

- Insulating Material, Nylon 6/6, Gray
- Wire Range #4-#8 AWG – 85 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR700930 - 70 Amps
- VDE – 108 Amps
- CE
- RoHS Compliant



MIK25

Catalog #	Description
MIK25	Center Section
MN35-2	DIN Rail symmetrical 35 X 7.5 mm slotted 2 m long, steel zinc-plated
MVB25	Jumpers 2-position
MVL25	Connecting straps- 2 position
MVL25-3	Connecting straps- 3 position
MVBU35	Supports for use under the MVL straps using M 6 X 15 screws
MSTB35	Plug sockets for test plugs of 4 mm Ø
MPST4	Test plugs- 4 mm Ø
MIW50	Insulating end sections for covering and insulating the last terminal in an assembly
MIW70	Insulating partition walls for visual and electrical separation of terminal groups
MKAW25	Safety covers with warning label for supply line terminals which cannot be disconnected
MSK35	End bracket used on both ends of the assembly to hold blocks in place



Dimensions:

H = 48 mm (1.89")
 W = 50 mm (1.97")
 T = 12 mm (.47")

For electronic drawings or 2D/3D CAD data,
 send request to drawings@marathonsp.com