

# SAFETY DATA SHEET

IPA Presaturated Wipes

## 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### Identification of the substance or mixture

**Product name** : IPA Presaturated Wipes  
**REACH Product name** : propan-2-ol  
**Chemical name** : Isopropyl Alcohol Saturated Wipes  
**Synonyms** : SIP100P, SIP100PE, SIP48P, SIP91P  
**Product type** : Liquid.

### Company/undertaking identification

**Manufacturer** : ITW Chemtronics  
8125 Cobb Center Drive  
Kennesaw, GA 30152  
  
Tel. 770-424-4888 or toll free 800-645-5244

**Distributor** :

**Importer** : ITW Contamination Control BV  
Saffierlaan 5  
VZ-2132 Hoofddorp  
The Netherlands

Tel: +31 88 1307 400  
FAX: +31 88 1307 499

**e-mail address of person responsible for this SDS** : askchemtronics@chemtronics.com

**Emergency telephone number (with hours of operation)** : Chemtrec - 1-800-424-9300 or collect 703-527-3887

## 2. HAZARDS IDENTIFICATION

The product is classified as dangerous according to Directive 1999/45/EC and its amendments.

**Classification** : F R11- Highly flammable.  
Xi; R36  
R67  
See Section 16 for the full text of the R-phrases declared above.

**Physical/chemical hazards** : Flammable liquid and vapour.

**Human health hazards** : Irritating to eyes. Vapours may cause drowsiness and dizziness.

See Section 11 for more detailed information on health effects and symptoms.

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

**Substance/preparation** : Multi-constituent substance

Ingredient name	CAS number	%	EC number	Classification
propan-2-ol	67-63-0	65 - 95	200-661-7	F; R11 Xi; R36 R67
See Section 16 for the full text of the R-phrases declared above.				

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

Occupational exposure limits, if available, are listed in Section 8.

## 4. FIRST AID MEASURES

### First-aid measures

**Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention. If necessary, call a poison center or physician. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

## 4. FIRST AID MEASURES

- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention. If necessary, call a poison center or physician. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.
- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

See Section 11 for more detailed information on health effects and symptoms.

## 5. FIRE-FIGHTING MEASURES

### Extinguishing media

- Suitable** : Use dry chemical, CO<sub>2</sub>, water spray (fog) or foam.
- Not suitable** : Do not use water jet.
- Special exposure hazards** : Extremely flammable liquid and vapour. In a fire or if heated, a pressure increase will occur and the container may burst, with the risk of a subsequent explosion. The vapour/gas is heavier than air and will spread along the ground. Vapours may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back. Runoff to sewer may create fire or explosion hazard.
- Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training. Move containers from fire area if this can be done without risk. Use water spray to keep fire-exposed containers cool.
- Hazardous thermal decomposition products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

## 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Shut off all ignition sources. No flares, smoking or flames in hazard area. Avoid breathing vapour or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment (see Section 8).
- Environmental precautions** : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).
- Methods for cleaning up**
- Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Use spark-proof tools and explosion-proof equipment. Dispose of via a licensed waste disposal contractor.
- Large spill** : Stop leak if without risk. Move containers from spill area. Approach the release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see section 13). Use spark-proof tools and explosion-proof equipment. Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilt product. Note: see section 1 for emergency contact information and section 13 for waste disposal.

## 7. HANDLING AND STORAGE

- Handling** : Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. Do not ingest. Avoid contact with eyes, skin and clothing. Avoid breathing vapour or mist. Use only with adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Do not enter storage areas and confined spaces unless adequately ventilated. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Store and use away from heat, sparks, open flame or any other ignition source. Use explosion-proof electrical (ventilating, lighting and material handling) equipment. Use non-sparking tools. Take precautionary measures against electrostatic discharges. To avoid fire or explosion, dissipate static electricity during transfer by earthing and bonding containers and equipment before transferring material. Empty containers retain product residue and can be hazardous. Do not reuse container.
- Storage** : Store in accordance with local regulations. Store in a segregated and approved area. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see section 10) and food and drink. Store locked up. Eliminate all ignition sources. Separate from oxidizing materials. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.
- Packaging materials**
- Recommended** : Use original container.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Exposure limit values

<u>Ingredient name</u>	<u>Occupational exposure limits</u>
propan-2-ol	<b>ACGIH TLV (United States, 1/2009).</b> STEL: 400 ppm 15 minute(s). TWA: 200 ppm 8 hour(s).

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to European Standard EN 689 for methods for the assessment of exposure by inhalation to chemical agents and national guidance documents for methods for the determination of hazardous substances.
- Exposure controls**
- Occupational exposure controls** : Use only with adequate ventilation. Use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. The engineering controls also need to keep gas, vapour or dust concentrations below any lower explosive limits. Use explosion-proof ventilation equipment.
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Respiratory protection** : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. disposable vinyl ,natural rubber (latex) ,neoprene ,neoprene rubber ,nitrile rubber ,polyethylene (PE) ,polyvinyl chloride (PVC)
- Eye protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts.
- Skin protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### General information

#### Appearance

- Physical state** : Liquid.  
**Colour** : Clear.White.Clear liquid in white wiper. [Light]  
**Odour** : Alcohol-like. [Strong]

### Important health, safety and environmental information

- Boiling point** : Lowest known value: 82.5°C (180.5°F) (propan-2-ol).  
**Melting point** : May start to solidify at the following temperature: -88.9°C (-128°F) This is based on data for the following ingredient: propan-2-ol.  
**Flash point** : Closed cup: 16°C (60.8°F). (Tagliabue.)  
**Explosive properties** : Not considered to be a product presenting a risk of explosion.  
**Explosion limits** : Lower: 1.2% Upper: 7.7%  
**Vapour pressure** : 26.4 kPa (198 mm Hg) (at 20°C)  
**Relative density** : 0.88 (Water = 1)  
**Vapour density** : 2.07 (Air = 1)  
**Evaporation rate (butyl acetate = 1)** : <1 compared with butyl acetate

### Other information

- Auto-ignition temperature** : Lowest known value: 399°C (750.2°F) (propan-2-ol).

## 10. STABILITY AND REACTIVITY

- Stability** : The product is stable.  
**Conditions to avoid** : Keep away from ignition sources such as heat/sparks/open flame. - No smoking.  
**Materials to avoid** : Oxidising agents  
**Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## 11. TOXICOLOGICAL INFORMATION

### Potential acute health effects

- Inhalation** : Can cause central nervous system (CNS) depression. May cause drowsiness or dizziness.  
**Ingestion** : Can cause central nervous system (CNS) depression. Irritating to mouth, throat and stomach.  
**Skin contact** : No known significant effects or critical hazards.  
**Eye contact** : Causes serious eye irritation.

### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure	
propan-2-ol	LD50 Dermal	Rabbit	12800 mg/kg	-	
	LD50 Intraperitoneal	Rat	2735 mg/kg	-	
	LD50 Intravenous	Rat	1088 mg/kg	-	
	LD50 Oral	Rat	5045 mg/kg	-	
	LD50 Oral	Rat	5000 mg/kg	-	
	TDL <sub>o</sub>	Rat	800 mg/kg	-	
	LC50 Inhalation Gas.	Rat	16000 ppm	8 hours	

### Potential chronic health effects

- Chronic effects** : No known significant effects or critical hazards.  
**Carcinogenicity** : No known significant effects or critical hazards.  
**Mutagenicity** : No known significant effects or critical hazards.  
**Teratogenicity** : No known significant effects or critical hazards.  
**Developmental effects** : No known significant effects or critical hazards.  
**Fertility effects** : No known significant effects or critical hazards.

### Over-exposure signs/symptoms

- Inhalation** : Adverse symptoms may include the following:  
nausea or vomiting  
headache  
drowsiness/fatigue  
dizziness/vertigo  
unconsciousness  
**Ingestion** : No specific data.  
**Skin** : No specific data.

**11. TOXICOLOGICAL INFORMATION**

- Eyes** : Adverse symptoms may include the following:  
pain or irritation  
watering  
redness
- Target organs** : Contains material which causes damage to the following organs: eye, lens or cornea.  
Contains material which may cause damage to the following organs: upper respiratory tract, skin, central nervous system (CNS).

**12. ECOLOGICAL INFORMATION**

**Environmental effects** : No known significant effects or critical hazards.

**Aquatic ecotoxicity**

Product/ingredient name	Test	Result	Species	Exposure
propan-2-ol	-	Acute LC50 11130000 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - Juvenile (Fledgling, Hatchling, Weanling) - 4 to 8 weeks - 1.1 to 3.1 cm	96 hours
	-	Acute LC50 10400000 to 10600000 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - 29 days - 20 mm - 0.103 g	96 hours
	-	Acute LC50 9640000 to 10000000 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - 31 days - 20.6 mm - 0.117 g	96 hours
	-	Acute LC50 6550000 to 7450000 ug/L Fresh water	Fish - Fathead minnow - Pimephales promelas - 31 days - 17.4 mm - 0.082 g	96 hours
	-	Acute LC50 4200000 ug/L Fresh water	Fish - Harlequinfish, red rasbora - Rasbora heteromorpha - 1 to 3 cm	96 hours
	-	Acute LC50 1400000 to 1950000 ug/L Marine water	Crustaceans - Common shrimp, sand shrimp - Crangon crangon	48 hours
	-	Acute LC50 >1400000 ug/L	Fish - Western mosquitofish - Gambusia affinis - 20 to 30 mm	96 hours

**Conclusion/Summary** : Not available.

**Biodegradability**

**Conclusion/Summary** : Not available.





**Other adverse effects** : No known significant effects or critical hazards.

**13. DISPOSAL CONSIDERATIONS**

- Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
- Hazardous waste** : The classification of the product may meet the criteria for a hazardous waste.

**14. TRANSPORT INFORMATION****International transport regulations**

**14. TRANSPORT INFORMATION**

Regulatory information	UN number	Proper shipping name	Classes	PG*	Label	Additional information
ADR/RID Class	1219	(propan-2-ol)	3	II		-
ADN/ADNR Class	1219	(propan-2-ol)	3	II		-
IMDG Class	1219	(2-Propanol)	3	II		-
IATA Class	1219	(2-Propanol)	3	II		- 095 Not acceptable for transport by aircraft.

PG\* : Packing group

**15. REGULATORY INFORMATION****EU regulations**

Classification and labeling have been determined according to EU Directives 67/548/EEC and 1999/45/EC (including amendments) and take into account the intended product use.

Hazard symbol or symbols :



Highly flammable, Irritant

Risk phrases

: R11- Highly flammable.  
R36- Irritating to eyes.  
R67- Vapours may cause drowsiness and dizziness.

Safety phrases

: S16- Keep away from sources of ignition - No smoking.  
S24/25- Avoid contact with skin and eyes.  
S26- In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.  
S2- Keep out of the reach of children.

Contains

: Isopropyl Alcohol Saturated Wipes

Product use

: Industrial applications, Professional applications.

Europe inventory

: All components are listed or exempted.

**16. OTHER INFORMATION**

Full text of R-phrases referred to in sections 2 and 3 - Europe : R11- Highly flammable.  
R36- Irritating to eyes.  
R67- Vapours may cause drowsiness and dizziness.

Full text of classifications referred to in sections 2 and 3 - Europe : F - Highly flammable  
Xi - Irritant

**History**

Date of printing : 10/25/2011.

Date of issue/Date of revision : 10/25/2011.

Date of previous issue : No previous validation.

Version : 1

Prepared by : Not available.

☑ Indicates information that has changed from previously issued version.

**Notice to reader**

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.