


STONTRONICS

THE POWER TO SUPPLY



Economical Multi-Output Power Supply with a 3 Year Warranty

Features:

- Low Cost
- High Quality & Reliability
- European Input voltage (200-240VAC)
- Class I Switch Mode Power Supply
- Small Footprint & Integrated Mounting Holes for easy installation.
- Metal box with detachable lid to enclose all components and discreetly keep from view to help avoid risk of electric shock.
- Suitable for CCTV & Security applications
- CE Compliant
- 3 Year Warranty

Specifications:

Image Disclaimer:
Unit pictured is a T4902AD and is for illustration purposes only.



Part Number	T4900AD	T4901AD	T4902AD	T4903AD	T4904AD	T4905AD	T4906AD	T4907AD	T4908AD	T4909AD	T4910AD	T4911AD
Output	Voltage 12Vdc											
No. of Outputs	4-way	4-way	4-way	9-way	9-way	9-way	9-way	9-way	18-way	18-way	18-way	18-way
Fuse Protection	PTC	PTC	PTC	PTC	PTC	PTC	PTC	PTC	PTC	PTC	PTC	PTC
Max. Total Current Rating	2.1A	4.2A	5A	4.2A	5A	8.5A	12.5A	16.5A	8.5A	12.5A	16.5A	25A
Current Min.	0 Amp (Unit Total)											
Power Rating	25Watt	50Watt	60Watt	50Watt	60Watt	102Watt	150Watt	200Watt	102Watt	150Watt	200Watt	300Watt
Voltage Adjustment	+/- 10% via built-in voltage trimmer (manual adjustment up to 13.2Vdc)											
Line Regulation	+/- 0.5%											
Load Regulation	+/- 2%											
Input	Voltage Range 176~264VAC											
Frequency	47~63Hz											
In-Rush Current	50A (220VAC)											
Input Current	1.2A Max.											
Leakage Current	Input-Output: 0.25A (no load)											
Efficiency	80% (typical)											
More	Protections Over Power, Over Current, Over Voltage & Short Circuit											
Operating Temp.	0 - 40°C											
Operating Hum.	20 - 90% RH No Condensing											
MTBF	>100K Hours											
PSU Approvals	Safety: EN/UL60950 EMC: EN55022 Class B & EN6100-4 (-2/-3/-4/-5/-6/-11)											
Dimensions	165 x 165 x 80 (max.) (L x W x H)						270 x 160 x 80 (max.) (L x W x H)					
Weight	approx. 1Kg						approx. 1.5Kg					

Download individual Data Sheet



Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.co.uk

Please Note: Image shown is for illustration purposes only. Actual PSU image &/or drawings available in the individual data sheets.
Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.