



## BA15d filament bulb, 24 V



Powering Business Worldwide™

**Part no.**  
**Article no.**

**SL-L24**  
**205348**

BA 15d, 5 ... 7 W

### Program

Range			SL signal towers
Basic function			Accessories
Basic function accessories			Filament bulbs
Single unit/Complete unit			Stand-alone device
			BA 15d 5 - 7 W
Lifespan to EN 60064 at $t_a = +25\text{ °C}$	$t_{\text{mean}}$ (AC)	h	2000
Rated operational voltage	$U_e$	V	24 V
Connection to SmartWire-DT			no

### Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified

### Technical data according to ETIM 4.0

Splitter protection			No
Type			Clear
Lamp voltage		V	24
Krypton			No
Color			-
Lamp voltage		W	7
Carbon filament			No
Average nominal lifespan		h	2000
Total length		mm	0
Diameter		mm	0
Suitable for baking oven			No
Multiple spiral-wound filament			YES
Lamp form			Pear-shape
Impact-resistant			No
Suitable for refrigerator			No
Special application			-
Luminous flux			0
Base			-

### Additional product information (links)

AWA1160-1685 (IL04716024Z) Pillar lamps	<a href="ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/16850900.pdf">ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/16850900.pdf</a>
<b>Engineering</b>	
Form for ordering customized complete units	<a href="ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf">ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf</a>