



MATERIAL SAFETY DATA SHEET UNIVERSAL ACRYLIC THINNERS

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME	UNIVERSAL ACRYLIC THINNERS
PRODUCT NO.	UAT EUAT2.5L EUAT05L ZE
APPLICATION	Manufacture of electrical equipment
SUPPLIER	ELECTROLUBE. A division of HK WENTWORTH LTD ASHBY PARK, COALFIELD WAY, ASHBY DE LA ZOUCH, LEICESTERSHIRE LE65 1JF UNITED KINGDOM +44 (0)844 375 9700 +44 (0)844 375 9799 info@hkw.co.uk
EMERGENCY TELEPHONE	Tel: 029938 1566 between 8.30am and 5.00pm EST
PROPER SHIPPING NAME	FLAMMABLE LIQUID, N.O.S. (TOLUENE, SOLVENT NAPHTHA (petroleum, light))

2 HAZARDS IDENTIFICATION

RISK PHRASES

R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R63	Possible risk of harm to the unborn child.
R65	Harmful: may cause lung damage if swallowed.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S24/25	Avoid contact with skin and eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S36/37	Wear suitable protective clothing and gloves.
S51	Use only in well-ventilated areas.
S62	If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.

The above phrases are the risks associated with the product

ENVIRONMENT

The product is not expected to be hazardous to the environment.

PHYSICAL AND CHEMICAL HAZARDS

The product is highly flammable, and explosive vapours/air mixtures may be formed even at normal room temperatures.

STATEMENT OF HAZARDOUS NATURE

HAZARDOUS SUBSTANCE (According to criteria of NOHSC). DANGEROUS GOODS (According to ADG Code).

DG CLASS

Class 3: Flammable liquids.

PACKING GROUP II

UNIVERSAL ACRYLIC THINNERS

UN NO. 1993
HAZCHEM CODE •3YE

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548)
TOLUENE	203-625-9	108-88-3	30-60%	F;R11 Repr.Cat.3;R63 Xn;R48/20,R65 Xi;R38 R67
METHYL ETHYL KETONE	201-159-0	78-93-3	30-60%	F;R11 Xi;R36 R66 R67
SOLVENT NAPHTHA (petroleum, light)	265-199-0	64742-95-6	<0.5%	Xn;R65. Xi;R37. N;R51/53. R10.

The Full Text for all R-Phrases is Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly. Get medical attention immediately!

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Contact physician if irritation persists. Use tepid water for rinsing

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Fire can be extinguished using: Foam. Dry chemicals, sand, dolomite etc.

SPECIAL FIRE FIGHTING PROCEDURES

Avoid breathing fire vapours. Cool containers exposed to flames with water until well after the fire is out.

HAZCHEM CODE •3YE

6 ACCIDENTAL RELEASE MEASURES

ENVIRONMENTAL PRECAUTIONS

Do not discharge into drains, water courses or onto the ground.

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Clean-up personnel should use respiratory and/or liquid contact protection. Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level. Use explosion proof electric equipment.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
METHYL ETHYL KETONE	ES-TWA	150 ppm	445 mg/m3	300 ppm	890 mg/m3	
TOLUENE	ES-TWA	50 ppm(Sk)	191 mg/m3(Sk)	150 ppm(Sk)	574 mg/m3(Sk)	

UNIVERSAL ACRYLIC THINNERS

INGREDIENT COMMENTS

Australian exposure limits are: LT= ES-TWA and ST= ES STEL

PROTECTIVE EQUIPMENT



ENGINEERING MEASURES

Provide adequate general and local exhaust ventilation.

RESPIRATORY EQUIPMENT

Respiratory protection must be used if air contamination exceeds acceptable level.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid Clear
COLOUR	Colourless
ODOUR	Organic solvents.
SOLUBILITY	Insoluble in water Soluble in: Acetone Miscible with: Alcohol Chloroform Ether.
RELATIVE DENSITY	0.850 @ 20 °c
VAPOUR PRESSURE	2.9 kPa
FLASH POINT (°C)	-7 (19.4F) CC (Closed cup).
AUTO IGNITION TEMPERATURE (°C)	>515 (959F)
FLAMMABILITY LIMIT - LOWER(%)	1.9
FLAMMABILITY LIMIT - UPPER(%)	10

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat. Avoid contact with oxidisers or reducing agents.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

11 TOXICOLOGICAL INFORMATION

INHALATION

Harmful by inhalation. May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea.

INGESTION

May cause discomfort if swallowed.

SKIN CONTACT

May cause sensitisation by skin contact. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

UNIVERSAL ACRYLIC THINNERS

EYE CONTACT

Irritating to eyes.

ROUTE OF ENTRY

Inhalation: Skin absorption.

Name	TOLUENE
Toxic Dose 1 - LD 50	5000 mg/kg (oral rat)
Name	METHYL ETHYL KETONE
Toxic Dose 1 - LD 50	2737 mg/kg (oral rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product is not expected to be hazardous to the environment.

Name	TOLUENE
LC 50, 96 Hrs, Fish mg/l	24
EC 50, 48 Hrs, Daphnia, mg/l	19.6
Name	METHYL ETHYL KETONE
LC 50, 96 Hrs, Fish mg/l	3200 - 5600
EC 50, 48 Hrs, Daphnia, mg/l	7060

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



PROPER SHIPPING NAME	FLAMMABLE LIQUID, N.O.S. (TOLUENE, SOLVENT NAPHTHA (petroleum, light))
ADG CLASS	Class 3: Flammable liquid
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.
UN NO.	1993
ADG CLASS NO.	3
DG CLASS	Class 3: Flammable liquids.
PACKING GROUP	II
TUNNEL RESTRICTION CODE	(D/E)
ADG LABEL NO.	3
HAZCHEM CODE	•3YE
UN NO. SEA	1993
IMDG CLASS	3
IMDG PACK GR.	II
EMS	F-E, S-E
UN NO. AIR	1993
AIR CLASS	3
AIR PACK GR.	II

15 REGULATORY INFORMATION

LABELLING

UNIVERSAL ACRYLIC THINNERS



Harmful



Highly Flammable

CONTAINS

TOLUENE

RISK PHRASES

R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R63	Possible risk of harm to the unborn child.
R65	Harmful: may cause lung damage if swallowed.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S24/25	Avoid contact with skin and eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S36/37	Wear suitable protective clothing and gloves.
S51	Use only in well-ventilated areas.
S62	If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.

EU DIRECTIVES

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EEC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

POISONS SCHEDULE NUMBER NONE

NATIONAL REGULATIONS AND REFERENCES

National Model Regulations for the Control of Workplace Hazardous Substances.

National Code of Practice for the Control of Workplace Hazardous Substances.

National Code of Practice for the Labelling of Workplace Substances.

National Code of Practice for the Preparation of Material Safety Data Sheets.

Approved Criteria for Classifying Hazardous Substances.

Exposure Standards for Atmospheric Contaminants in the Occupational Environment.

Australian Dangerous Goods Code. The Standard for the Uniform Scheduling of Drugs and Poisons (SUSDP).

16 OTHER INFORMATION

REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC NOTE: Lines within the margin indicate significant changes from the previous revision.

ISSUED BY

Helen O'Reilly

REVISION DATE

NOVEMBER 2010

REV. NO./REPL. SDS

6

GENERATED

SDS NO.

10611

UNIVERSAL ACRYLIC THINNERS

RISK PHRASES IN FULL

R10	Flammable.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R38	Irritating to skin.
R63	Possible risk of harm to the unborn child.
R66	Repeated exposure may cause skin dryness or cracking.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.