

# Current Transducer HTFS 200..800-P

For the electronic measurement of currents : DC, AC, pulsed, mixed, with galvanic isolation between the primary circuit (high power) and the secondary circuit (electronic circuit).







All Data are given with a  $R_L = 10 \text{ k}\Omega$ 

EI	ectrical data				
Primary nominal Prir		Primary current		Туре	
current rms		measuring range			
PN					
	200	± 300		S 200-P	
400		± 600	HTFS 400-P		
	600	± 900		S 600-P	
	800	± 1200	HTF	S 800-P	
V <sub>OUT</sub>	Output voltage	(Analog) @ I <sub>P</sub> I <sub>P</sub> = 0		V <sub>REF</sub> ± (1.23 V <sub>REF</sub> ± 0.02	
$V_{\text{REF}}$	Reference volt	age <sup>1)</sup> - Output voltage		$1/2V_{c} \pm 0.0$	
		V <sub>REF</sub> Output ir	npedance	typ. 200	Ω
		V <sub>REF</sub> Load imp		≥ 200	kΩ
RL	Load resistanc			≥ 2	kΩ
R <sub>OUT</sub>	Output internal			< 10	Ω
C	Capacitive load	-		< 1	μF
Vc	Supply voltage			5	V
I <sub>C</sub>	Current consur	mption @ $V_c$ = 5 V		22	mA
A	ccuracy - Dyi	namic performanc	e data		
x	Accuracy <sup>2)</sup> @	I <sub>PN</sub> , <b>Τ</b> <sub>A</sub> = 25°C		≤ ± 1	% of $\mathbf{I}_{_{\mathrm{PN}}}$
ε	Linearity error	(0 1.5 x I <sub>PN</sub> )		≤±0.5	% of ${\sf I}_{_{\sf PN}}$
TCV	Temperature c	oefficient of $V_{OE} @ I_{P} = 0$	D	≤±0.3	mV/K
$\mathbf{TCV}_{RE}$	F Temperature c	oefficient of $V_{_{REF}}$		≤ ± 0.01	%/K
$\text{TCV}_{\text{out}}/\text{V}_{\text{REF}}$ Temperature coefficient of $\text{V}_{\text{OUT}}/\text{V}_{\text{REF}}$ @ $\textbf{I}_{\text{P}} = 0$		@ I <sub>P</sub> = 0	≤ ± 0.2	mV/K	
TCV	<sub>лт</sub> Temperature c	oefficient of V <sub>OUT</sub>		≤±0.05% o	of reading/K
V <sub>OM</sub>	Magnetic offse	t voltage @ I <sub>P</sub> = 0,			
	after an overloa	ad of 3 x I <sub>PN DC</sub>		< ± 0.5	% of ${\sf I}_{_{\sf PN}}$
t <sub>ra</sub>	Reaction time	@ 10 % of I <sub>PN</sub>		< 3	μs
t,	Response time	e to 90 % of I <sub>PN</sub> step		< 7	μs
di/dt	di/dt accurately			> 100	A/µs
V <sub>no</sub>	Output voltage			< 15	mVpp
BW	Frequency bar	(DC 1 N ndwidth (- 3 dB) <sup>3)</sup>	1 <b>11</b> 2)	< 40 DC 50	mVpp kHz
G	eneral data				
T <sub>A</sub>	Ambient of	operating temperature		- 40 + 1	05 °C
<b>T</b> s	Ambient s	storage temperature		- 40 + 1	05 °C
m	Mass			60	g
	Standard			EN 50178	3: 1997
Notes :	<sup>1)</sup> It is possible to	overdrive $\mathbf{V}_{\text{REF}}$ with an ext	ernal referen	ce voltage	

It is possible to overdrive  $\mathbf{V}_{\mathsf{REF}}$  with an external reference voltage INOTES :

between 2 - 2.8 V providing its ability to sink or source approx. 2.5 mA.

<sup>2)</sup> Excluding offset and Magnetic offset voltage.

<sup>3)</sup> Small signal only to avoid excessive heatings of the magnetic core.

LEM reserves the right to carry out modifications on its transducers, in order to improve them, without prior notice.

## I<sub>PN</sub> = 200-400-600-800 A



## **Features**

- Hall effect measuring principle
- Galvanic isolation between primary and secondary circuit
- Low power consumption
- Single power supply +5V
- Ratiometric offset
- T<sub>A</sub> = -40..+105 °C
- Fixation by M3 nuts and screws
- Isolated plastic case recognized according to UL 94-V0.

#### **Advantages**

- Small size and space saving
- Only one design for wide current ratings range
- · High immunity to external interference.
- V<sub>REF.</sub> IN/OUT.

#### **Applications**

- Forklift drives
- AC variable speed drives
- Static converters for DC motor drives
- Battery supplied applications
- Uninterruptible Power Supplies (UPS)
- Switched Mode Power Supplies (SMPS)
- Power supplies for welding applications.

## **Application domain**

Industrial.

www.lem.com



## Current Transducer HTFS 200..800-P

#### **Isolation characteristics**

**V**<sub>b</sub> Rated isolation voltage rms with following conditions

- Over voltage category III
- Pollution degree 2
- Non-uniform field

	EN50178	IEC61010-1
Single insulation	300V	300V
Reinforced insulation	150V	150V

V <sub>d</sub>	Rms voltage for AC isolation test, 50 Hz, 1 min	2.5	kV
$V_{e}$	Partial discharge extinction voltage rms @ 10pC	> 1	kV
$V_{w}$	Impulse withstand voltage 1.2/50 µs	4	kV
dCp	Creepage distance	> 4	mm
dCl	Clearance distance	> 4	mm
СТІ	Comparative tracking index (Group IIIa)	> 220	

If insulated cable is used for the primary circuit, the

voltage category could be improved with the following table :

Cable insulation (primary)	Category
HAR 03	300V CAT III
HAR 05	400V CAT III
HAR 07	500V CAT III

#### Safety



This transducer must be used in electric/electronic equipment with respect to applicable standards and safety requirements in accordance with the manufacturer's operating instructions.



Caution! Risk of electrical shock

When operating the transducer, certain parts of the module can carry hazardous voltage (eg. primary busbar, power supply).

Ignoring this warning can lead to injury and/or cause serious damage.

This transducer is a built-in device, whose conducting parts must be inaccessible after installation.


A protective housing or additional shield could be used.

Main supply must be able to be disconnected.

Page 2/3



#### Dimensions HTFS 200..800-P (in mm. 1 mm = 0.0394 inch)



#### **Mechanical characteristics**

- General tolerance
- Fastening by

- ± 0.2 mm
- 4 x M3 (not supplied)

< 2.5 Nm

Ø 0.7 mm

4 pins 0.5 x 0.25

- Recommended fastening torque
- Fastening & connection of secondary
- Recommended PCB hole

#### Remarks

- $V_{\mbox{\scriptsize OUT}}$  is positive when  $I_{\mbox{\scriptsize P}}$  flows in the direction of the arrow.
- Temperature of the primary conductor should not exceed 120°C.

120201/9

Page 3/3