



### Details

Numatic wv750f-2 large wet or dry commercial vacuum cleaner, with a 1200w twinflo' motor housed in a super tough structofoam powerhead. for applications within the healthcare, medical, pharmaceutical and food industries where stainless steel remains the standard, the wv750f provides this superb standard with extensive use of austenitic grade stainless steel in the container, lower chassis and tube set. the large wheel construction ensures easy movement and also incorporated is the nucable plugged cable system ensuring easy replacement in the event of damage. the standard bb8 kit that comes in the larger 38mm diameter, and two 400mm multiflo tools, that are also constructed from structofoam, are supplied for both wet or dry use. \*please be aware that this machine use a 110 volt power supply\*

### Additional Information

**Weight (kg)**

21.5000

**Domain**

commercial, industrial

**Warranties**

2 years

**Air Flow (Litres per second)**

40

**Number of motors**

1

**Brand**

Numatic

<b>Extension Rods</b>	Stainless steel
<b>Suction</b>	2500
<b>Shipping Weight (kg)</b>	24
<b>Usages</b>	dry, wet
<b>oem_no</b>	833044 wv750-110v
<b>Width (millimeters)</b>	680
<b>Height (millimeters)</b>	940
<b>Length (millimeters)</b>	550
<b>Cable Colour</b>	Black
<b>Solution Capacity</b>	25
<b>Capacity (litres)</b>	35
<b>Voltage</b>	110v