•	PART NO.			REVISIONS						
multicomp			REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
mancomp	19-49-5-TGG	-	A	RELEASED	Shashi	16/1/12	Jagan	16/1/12		30/1/12
	Silver Brazing Silver Brazing (George	.35 (0.2		A Minimum mo (1) Ø1.5 (0.05 (4) Ø1.6 (0.06	unting 9) mini 3) mini	mum mum llimetres				

bers of the Frence France group of companies (the Group) of the free for the two	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
plied. The information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for all use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or ormitted. Liability for loss or damage resulting from any reliance on	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Shashi	16/01/12		d, Right Angle		
		CHECKED BY:	DATE:	SIZE DWG NO.	M10002506	ELECTRONIC FILE	REV
		Jagan	16/01/12	Δ		1169632-DWG	Α
		APPROVED BY:	DATE:				
ate to limit or restrict the Group's liability for death or personal injury resulting from its negli- gence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.			30/01/12	SCALE: NTS	U.O.M.: mm (Inches)	SHEET: 1 O	0F 2

multicomp	PART NO.	REVISIONS									
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
	19-49-5-TGG	-	А	RELEASED	Shashi	16/1/12	Jagan	16/1/12		30/1/12	

Specifications:

Electrical:

Frequency range Nominal impedance	: DC 12.4 GHz : 50 ohms
Maximum working voltage	: 500 volts
Proof voltage	: 1,000 volts
Maximum VSWR	: 1.23

Material:

Bodies	: Brass per JIS-C3604		
Centre contact : Brass per JIS-C3604			
	: Beryllium copper per ASTM B196 UNS C17300		
Insulation	: Teflon per ASTM D1457 and ASTM D1710		

Specification Table

ltem	Description	Material	Finish
1	Chassis	Brass	Gold 3 µ inches (minimum)
2	Insulation	Teflon	None
3	Centre Contact I	Beryllium Copper	Gold 50 μ inches (minimum)
4	Body	Brass	Gold 3 µ inches (minimum)
5	Insulation	Teflon	None
6	Centre Contact II	Brass	Gold 50 μ inches (minimum)
7	Сар	01055	Gold 3 µ inches (minimum)

Mechanical:

Interface in accordance with MIL-STD-348A

Environmental:

Operating temperature range : -65°C to +165°C

Part Number Table

Description	Part Number
Jack SMA, Bulkhead, Right Angle	19-49-5-TGG

www.element14.com www.farnell.com www.newark.com

bers of the Fremier Fameli gloup of companies (the Gloup) of are licensed to it. No	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
plied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or ornitted. Liability for loss or damage resulting from any reliance on	UNLESS OTHERWISE	Shashi	16/01/12	Jack SMA, Bulkhead, Right A			
	SPECIFIED, DIMENSIONS ARE FOR REFERENCE	CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV A
		Jagan	16/01/12	Δ	M10002506	1169632-DWG	
		APPROVED BY:	DATE:				
			30/01/12	SCALE: NTS	U.O.M.: mm (Inches)	SHEET: 2 O)F 2