




PART NO.



8FSM Series

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ashok	19/01/12	Jagan	19/01/12	Farnell	02/02/12



Recommended Panel Cut-out Dimensions



Dimensions : Millimetres (Inches)

Specifications:

Current rating	: 1 ampere
Minimum insulation resistance	: ≥1,000 MΩ (at 500 V dc)
Minimum dielectric withstanding voltage	: 500 V ac (for one minute)
Operating temperature	: -55°C to 105°C
Contact resistance	: ≤15 mΩ
Dielectric material	: PBT with glass-fibre reinforced
Colour	: Black, blue and grey (optional)
Contact material	: Phosphor bronze
Contact plating	: Gold over nickel
Wire size	: AWG 26 and 28 stranded, 1.27 mm conductor centre flat cable

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Ashok

DATE:

19/01/12

CHECKED BY:

Jagan

DATE:

19/01/12

APPROVED BY:

DATE:

02/02/12

DRAWING TITLE:

Metal D Type IDC Connectors - UnthreadedSIZE
A

DWG NO.

M10001972

ELECTRONIC FILE

50302_DWG

REV

A

SCALE: NTS

U.O.M.: mm (Inches)

SHEET: 1 OF 2



PART NO.

8FSM Series

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ashok	19/01/12	Jagan	19/01/12	Farnell	02/02/12

Specification Table

Number of Positions	A ± 0.13 (± 0.005)	B ± 0.25 (± 0.01)	C ± 0.13 (± 0.005)	D ± 0.13 (± 0.005)	E ± 0.25 (± 0.01)	F ± 0.25 (± 0.01)	H ± 0.25 (± 0.01)	I ± 0.13 (± 0.005) Rear Mounting	I ± 0.13 (± 0.005) Front Mounting	Part Number
9	24.99 (0.984)	30.8 (1.212)	11.08 (0.436)	8.31 (0.327)	16.1 (0.634)	18.6 (0.732)	16.33 (0.643)	20.47 (0.806)	22.2 (0.874)	8FSM09S-30N4-FEC
15	33.32 (1.312)	39.1 (1.539)	19.39 (0.763)	16.62 (0.654)	24 (0.945)	26.6 (1.047)	24.66 (0.971)	28.8 (1.134)	30.53 (1.202)	8FSM15S-30N4-FEC
37	63.5 (2.5)	69.4 (2.732)	49.86 (1.963)	47.09 (1.854)	54.6 (2.15)	57.1 (2.248)	54.84 (2.159)	59.08 (2.326)	60.73 (2.391)	8FSM37S-30N4-FEC

Dimensions : Millimetres (Inches)

Part Number Explanation:

8F	SM	09	S	-	3	0	N	4	-	FEC
Series	Housing Construction Types	Number of Positions	Contact Type		Colour Codes	Contact Finish	Strain Relief	Metal Shell Finish		Customer

Series	: 8F = D-SUB IDC Connector
Housing Construction Types	: SM = Standard Through Holes (With Metal Shell)
Number of Positions	: 09 = 9, 15, and 37 Positions
Contact Type	: S = Socket (Female)
Colour Codes	: 3 = Black
Contact Finish	: 0 = Selective Gold Flash Over 30 μ Inches Nickel
Strain Relief	: N = Without Strain Relief
Metal Shell Finish	: 4 = Tin Plated Shell (Without Grounding Indents)
Customer	: FEC = Inland

www.element14.com
www.farnell.com
www.newark.com

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Ashok

DATE:

19/01/12

CHECKED BY:

Veena

DATE:

19/01/12

APPROVED BY:

02/02/12

DRAWING TITLE:

Metal D Type IDC Connectors - Unthreaded

SIZE	DWG NO.	ELECTRONIC FILE	REV
A	M10001972	50302_DWG	A
SCALE: NTS		U.O.M.: mm (Inches)	SHEET: 2 OF 2