


Part Number : **1900XX5W**

Type	Size	IP Rating	Description
LED	M6	40	Flat bezel panel indicator

Dimensions(mm):



Part #	Colour	Voltage(V)	Current(mA nom)	Intensity(mcd nom)
1900X25W	Cool white	12Vdc	15mA	210
1900X35W	Cool white	24Vdc	15mA	210

Notes:

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Storage temperature -25 °C to +80°C
3. Application temperature -20 °C to +60°C
4. Voltage tolerance ±10%
5. Terminals: Brass +ve, Tinned brass -ve
6. Terminals not qualified for soldering
7. The plastic(polycarbonate) has limited chemical resistance
8. RoHS & REACH SVHC compliant

Issue # 1 : 8 Feb 12