Conforms to Regulation (EC) No. 1907/2006 (REACH), Annex II - Europe

# SAFETY DATA SHEET

ES1550E Freez-It(R)

## IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE **COMPANY/UNDERTAKING**

Identification of the substance or mixture

**Product name** : ES1550E Freez-It(R)

**Chemical name** : Refrigerant.

**Synonyms** : ES1550E Freez-It(R)

**Product type** : Aerosol Company/undertaking identification

Manufacturer : ITW Chemtronics

> 8125 Cobb Center Drive Kennesaw, GA 30152

Tel. 770-424-4888 or toll free 800-645-5244

**Distributor** 

**Importer** : ITW Contamination Control BV

> Saffierlaan 5 VZ-2132 Hoofddorp The Netherlands

Email: info@itw-cc.com

Tel: +31 88 1307 400 FAX: +31 88 1307 499

e-mail address of person responsible for this SDS

: askchemtronics@chemtronics.com

Emergency telephone number: Chemtrec - 1-800-424-9300 or collect 703-527-3887

(with hours of operation)

## HAZARDS IDENTIFICATION

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification Not classified.

**Additional hazards** : Dermal contact with rapidly evaporating liquid could result in freezing of the tissues or

frostbite. Ingestion of liquid can cause burns similar to frostbite.

See Section 11 for more detailed information on health effects and symptoms.

## COMPOSITION/INFORMATION ON INGREDIENTS

Substance/preparation : Mixture

Ingredient name	CAS number	%	EC number	Classification	
dimethyl ether	115-10-6	1 - 4	204-065-8	F+; R12 [2]	
See Section 16 for the full text of the R-phrases declared above.					

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

Occupational exposure limits, if available, are listed in Section 8.

## FIRST AID MEASURES

First-aid measures

Inhalation : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get

medical attention if symptoms occur.

Ingestion : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is

conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.

: If frostbite occurs, get medical attention. Flush contaminated skin with plenty of water. Skin contact Remove contaminated clothing and shoes. Get medical attention if symptoms occur.

> : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation

**Protection of first-aiders** Notes to physician

Eye contact

: No action shall be taken involving any personal risk or without suitable training.

Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

Date of issue/Date of : 12/6/2011. 1/5 revision

## 4. FIRST AID MEASURES

See Section 11 for more detailed information on health effects and symptoms.

### 5. FIRE-FIGHTING MEASURES

#### **Extinguishing media**

Suitable

: Use an extinguishing agent suitable for the surrounding fire.

Not suitable

: None known

Special exposure hazards

: In a fire or if heated, a pressure increase will occur and the container may burst. Bursting aerosol containers may be propelled from a fire at high speed.

Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training. Move containers from fire area if this can be done without risk. Use water spray to keep fire-exposed containers cool.

Hazardous thermal decomposition products

: Decomposition products may include the following materials:

carbon dioxide carbon monoxide halogenated compounds

Special protective equipment for fire-fighters

: Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

#### 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions** 

: No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. In the case of aerosols being ruptured, care should be taken due to the rapid escape of the pressurised contents and propellant. If a large number of containers are ruptured, treat as a bulk material spillage according to the instructions in the clean-up section. Do not touch or walk through spilt material. Put on appropriate personal protective equipment (see Section 8).

**Environmental precautions** 

: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

#### Methods for cleaning up

**Small spill** 

: Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

Large spill

: Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations. Dispose of via a licensed waste disposal contractor.

## 7. HANDLING AND STORAGE

Handling

Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. Pressurised container: protect from sunlight and do not expose to temperature exceeding 50°C. Do not pierce or burn, even after use. Avoid breathing gas. Avoid breathing vapour or mist.

Storage

: Store in accordance with local regulations. Store away from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see section 10) and food and drink. Use appropriate containment to avoid environmental contamination.

## Packaging materials

Recommended

: Use original container.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

## **Exposure limit values**

Ingredient name dimethyl ether

Occupational exposure limits

EU OEL (Europe, 4/2006). Notes: Indicative

Limit value: 1920 mg/m³ 8 hour(s). Limit value: 1000 ppm 8 hour(s).

Recommended monitoring procedures

If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to European Standard EN 689 for methods for the assessment of exposure by inhalation to chemical agents and national guidance documents for methods for the determination of hazardous substances.

#### **Exposure controls**

Date of issue/Date of revision

: 12/6/2011.

2/5

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Occupational exposure

controls

: Use only with adequate ventilation. If user operations generate dust, fumes, gas, vapour or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.

**Hygiene measures** 

: Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period.

Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Respiratory protection** 

: Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

**Hand protection** 

: Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Eye protection

: Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists or duete

**Skin protection** 

 Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Environmental exposure** 

controls

: Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

#### **General information**

**Appearance** 

Physical state : Gas.
Colour : Colourless.
Odour : Odourless.

Important health, safety and environmental information

**Boiling point** : -27°C (-16.6°F)

Melting point : -138.5°C (-217.3°F) This is based on data for the following ingredient: dimethyl ether.

Relative density : Only known value: 0.724 (Water = 1) (dimethyl ether).

Vapour density : 3.18 (Air = 1)

**Evaporation rate (butyl** 

acetate = 1)

: >1 compared with butyl acetate

## 10. STABILITY AND REACTIVITY

Stability : The product is stable.

Conditions to avoid : No specific data.

Materials to avoid : No specific data.

**Hazardous decomposition** 

products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## 11. TOXICOLOGICAL INFORMATION

Potential acute health effects

Inhalation: No known significant effects or critical hazards.Ingestion: No known significant effects or critical hazards.Skin contact: No known significant effects or critical hazards.Eye contact: No known significant effects or critical hazards.

**Acute toxicity** 

Product/ingredient nameResultSpeciesDoseExposuredimethyl etherLC50 Inhalation<br/>VapourRat309 g/m34 hours

### Potential chronic health effects

Chronic effects
 No known significant effects or critical hazards.
 Carcinogenicity
 No known significant effects or critical hazards.
 Mutagenicity
 No known significant effects or critical hazards.
 Teratogenicity
 No known significant effects or critical hazards.
 Developmental effects
 No known significant effects or critical hazards.
 Fertility effects
 No known significant effects or critical hazards.

Over-exposure signs/symptoms

Date of issue/Date of : 12/6/2011. 3/5

## 11. TOXICOLOGICAL INFORMATION

Inhalation : Adverse symptoms may include the following:

respiratory tract irritation

coughing

Ingestion : No specific data. : No specific data. Skin

**Eyes** Adverse symptoms may include the following:

redness

## 12. ECOLOGICAL INFORMATION

**Environmental effects** 

: No known significant effects or critical hazards.

**Aquatic ecotoxicity** 

Conclusion/Summary : Not available.

**Biodegradability** 

**Conclusion/Summary** : Not available.

Other adverse effects : No known significant effects or critical hazards.

## 13. DISPOSAL CONSIDERATIONS

Methods of disposal

The generation of waste should be avoided or minimised wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Do not puncture or incinerate container.

**Hazardous waste** Within the present knowledge of the supplier, this product is not regarded as hazardous

waste, as defined by EU Directive 91/689/EEC.

#### 14. TRANSPORT INFORMATION

#### International transport regulations

Regulatory information	UN number	Proper shipping name	Classes	PG*	Label	Additional information
ADR/RID Class	UN1950	AEROSOLS (1,1,1,2- TETRAFLUOROETHANE)	2	-		Tunnel code (E)
ADN/ADNR Class	UN1950	AEROSOLS (dimethyl ether)	2	-		-
IMDG Class	UN1950	AEROSOLS (1,1,1,2- TETRAFLUOROETHANE)	2.2	-		-
IATA Class	UN1950	Aerosols, non- flammable (1,1,1,2- TETRAFLUOROETHANE)	2.2	-	2	-

PG\*: Packing group

## 15. REGULATORY INFORMATION

Classification and labeling have been determined according to EU Directives 67/548/EEC and 1999/45/EC (including amendments) and take into account the intended product use.

Risk phrases : This product is not classified according to EU legislation.

**Product use** Professional applications.

**Europe inventory** : Not determined.

Other EU regulations

Additional warning phrases : Pressurised container: protect from sunlight and do not expose to temperature exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children. Safety data sheet available for professional user on request.

Date of issue/Date of : 12/6/2011. 4/5 revision

## **16. OTHER INFORMATION**

Full text of R-phrases : R12- Extremely flammable. referred to in sections 2 and

3 - Europe

Full text of classifications : F+ - Extremely flammable

referred to in sections 2 and

3 - Europe

**History** 

Date of printing : 12/6/2011.

Date of issue/Date of : 12/6/2011.

revision

Date of previous issue : No previous validation.

Version : '

Prepared by : Not available.

 $\ensuremath{\mathbb{F}}$  Indicates information that has changed from previously issued version.

#### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Date of issue/Date of : 12/6/2011. 5/5