

F

E

D

C

B

A

10

9

8

7

6

5


4

3

2

1


3 POL. MM



OBUDOWA MESKA 3 POLOWA
WIDOK OD STRONY DRUTOW
MALE INSERT 3P
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	-	-
3	Niebieski	BU
4	Czarny	BK


4 POL. MM



OBUDOWA MESKA 4 POLOWA
WIDOK OD STRONY DRUTOW
MALE INSERT 4P
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Bialy	WH
3	Niebieski	BU
4	Czarny	BK


5 POL. MM



OBUDOWA MESKA 5 POLOWA
WIDOK OD STRONY DRUTOW
MALE INSERT 5P
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Brazowy	BN
2	Bialy	WH
3	Niebieski	BU
4	Czarny	BK
5	Szary	GY

8 POL. MM



OBUDOWA MESKA 8 POLOWA
WIDOK OD STRONY DRUTOW
MALE INSERT 8P
VIEW FROM WIRES SIDE


Pin	Kolor przew.	Wire color
1	Bialy	WH
2	Brazowy	BN
3	Zielony	GN
4	Zolty	YE
5	Szary	GY
6	Rozowy	PK
7	Niebieski	BU
8	Czerwony	RD

TABELA 1
CHART 1


STARY P/N	MOLEX P/N	WOODHEAD NO	L[MM]	TYP KONEKTORA
1200110215	1200704002	8R4J46E03C3003	300	4 POLE
	1200110622	8R8J46E02M0153	1500	8 POLE
1200110736	1200700234	8R5J46E03C3003	300	5 POLE
	1200700278	8R8J46E02C3003	300	8 POLE
	1200708017	8R4J46E03C300	300	4 POLE
	1200708032	8R5J46E03C300	300	5 POLE
	1200708038	8R8J46E02C300	300	8 POLE
	1200708073	8R8J46E02M015	1500	8 POLE
	1200705181	8R8J46E03C200	200	8 POLE

PART No MATRIX

8	R	*	J	4	6	*	*	*	X	*	*	*	*
8=Micro Change	R=Receptacle	3=3 Core 4=4 Core 5=5 Core 6=8 Core	Male Contact Male thread M12 PG9 Mounting Thread			E02=0.25 PVC E03=0.34 PVC			C= CENTIMETRES	LENGTH 300=30cm (300mm) 1500=50cm (500mm)			Shell Material 3=Brass Nickel Plated (Standard)



Widok od strony czola
FACE VIEW



UWAGI:

- 1 DŁUGOŚCI CIECIA PRZEWODOW I SPECYFIKACJE NABIJANIA W LISCIE CIECIA.
2. PO OSADZENIU TERMINALI ZALAC KLEJEM.

NOTES:

1. FOR WIRES CUTTING LENGTHS AND CRIMPING SPECIFICATION SEE THE CUTTING LIST.
- 2.AFTRE ASSEMBLED TERMINALS THE CONNECTOR MUST BE FLOOD BY GLUE.

ADD PART NO EC NO: WEU2012-0145 DRWN:HWALCZAK 2011/06/02 CHKD: APPR:MDYSZEWSKA 2011/12/09		DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION												
				4 PLACES	mm	INCH	DRAWN BY DWARWAS		DATE 2008/05/09	TITLE MMC-XP-MM REC- P/MTG-XXM-PVC													
					3 PLACES	± ---	± ---	CHECKED BY			DATE												
					2 PLACES	± ---	± ---	APPROVED BY			DATE												
B		REV		1 PLACE	± ---	± ---	APPROVED BY		DATE	molex MOLEX INCORPORATED													
				ANGULAR ± ---°			MATERIAL NO.		DOCUMENT NO.				SHEET NO.										
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART 1			E-120070-215			1 OF 1										
SIZE A3												THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											

9

8

7

6

5

4

3

2

1